




B07D932BC2-0348 Product Details

[Share](#) [Print](#) [Email](#)


B07D932BC2-0348
(4-1617004-0)

TE Internal Number: 4-1617004-0

 Active

Military/Aerospace High Performance Relays

Not EU RoHS or ELV Compliant

Product Highlights:

- 07 Full Size Relay Series
- Input Voltage = 26.5 VDC
- Contact - Arrangement = 2 Form C, DPDT, 2 C/O
- Contact - Rated Current = 10 A
- Non Polarized, Monostable Coil - Magnetic System

[View all Features](#)

Quick Links

- ▶ [Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- [RELAY](#) (PDF, English)

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Series](#) = 07 Full Size Relay
- MOSFET Driver = Without
- Termination Type = Solder Hook Terminals

Mechanical Attachment:

- Mounting Options = Panel Mount

Electrical Characteristics:

- Input Voltage (VDC) = 26.5
- Contact - Rated Current (A) = 10
- Coil Suppression Diode = Without
- Coil Polarity Protection Diode = Without
- Transistor Driver = Without
- Coil - Resistance (Ω) = 300
- Coil Power Measurement = Milliwatts
- Coil - Rated Power, DC (mW) = 2341
- Actuating System = DC
- Shock = 100G's, 6ms
- Vibration = 20G's, 10 to 2000Hz

Body Features:

- Enclosure Type = Hermetically Sealed

Configuration Features:

- [Contact - Arrangement](#) = 2 Form C, DPDT, 2 C/O
- Coil - Magnetic System = Non Polarized, Monostable

Industry Standards:

- Government/Industry Qualification = Yes
- Government/Industry Part Number = M5757/23-031
- [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- [Lead Free Solder Processes](#) = Not suitable for lead free processing
- Approved Standards = M5757 Qualified

Conditions for Usage:

- Temperature Range ($^{\circ}\text{C}$) = -65 - +125

Other:

- Brand = CII

Corporate Information

[About TE](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)
[Terms & Conditions](#)
[Privacy Policy](#)

Quick Links

[Distributor Inventory](#)
[Product Cross Reference](#)
[Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Knowledge Base](#)
[Manage Your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

