


1-390261-5 Product Details

[Live Product Chat](#)



1-390261-5

TE Part Number: 1-390261-5

[Active](#)

[Add to Part List](#)

DIP Sockets

[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- DIP Socket
- Number of Positions = 18
- Row-to-Row Spacing = 7.62 mm
- Thru Hole
- Mount Style = Vertical

[View all Features](#) | [Find Similar Products](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- [DIP SOCKET, .300 CENTER LINE LADDER STYLE \(PDF, English\)](#)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Product Type](#) = DIP Socket
- [Number of Positions](#) = 18
- Profile = Standard
- [Frame Style](#) = Ladder
- [Leg Style](#) = Straight
- PCB Mount Angle = Horizontal

Electrical Characteristics:

- Insulation Resistance (MΩ) = 10,000
- Contact Resistance (mΩ) = 30

Termination Related Features:

- [Termination \(Solder\) Post Length \(mm \[in\]\)](#) = 3.00 [0.118]

Body Related Features:

- [Row-to-Row Spacing \(mm \[in\]\)](#) = 7.62 [0.300]
- [Mount Style](#) = Vertical
- [Centerline \(mm \[in\]\)](#) = 2.54 [0.100]

Contact Related Features:

- [Contact Mount](#) = Thru Hole
- [Contact Material](#) = Phosphor Bronze
- [Contact Mating Area Plating Material](#) = Tin
- [Contact Style](#) = Stamped + Formed
- [Mating Contact Type](#) = Dual Leaf

Configuration Related Features:

- [Height Above PC Board \(mm \[in\]\)](#) = 5.10 [0.200]

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- Temperature Range (°C) = -40 - +105

Packaging Related Features:

- [Packaging Method](#) = Tube

Other:

- Brand = AMP