

Catalog: 1654001 Issue Date: 06.2011

Smallest Power Entry Module with Metric Fuse Holders

GG & HG Series



UL Recognized CSA Certified VDE Approved




GG Series

- Power entry module with enhanced EMI filter
- Single or dual fusing
- Two element circuit provides basic attenuation
- Available with an internal ground-circuit inductor (C versions) to isolate equipment chassis from power line ground at radio frequencies
- Multiple termination and mounting styles

HG Series

- Medical version of our GG Series
- Mechanically identical to GG Series
- · Available only with dual fusing

Ordering Information



Specifications

Maximum leakage current each Line to Ground: HG Models GG Models

@ 120 VAC 60 Hz: @250 VAC 50 Hz:	2 μA 5 μA	.25 mA .42 mA
Hipot rating (one minute) Line to Ground: Line to Line:):	2250 VDC 1450 VDC
Rated Voltage (max.):		250 VAC
Operating Frequency:		50/60 Hz
Rated Current:		1 to 10A
Required Fuse(s):		5 x 20mm (not included)

Available Part Numbers

Filtered modules						
1EGG1-1	3EGG1-1	6EGG1-1	10EGG1-1			
1EGG1-2	3EGG1-2	6EGG1-2	10EGG1-2			
1EGG8-1	3EGG8-1	6EGG8-1	10EGG8-1			
1EGG8-2	3EGG8-2	6EGG8-2	10EGG8-2			
1EGS1-1	3EGS1-1	6EGS1-1	10EGS1-1			
1EGS1-2	3EGS1-2	6EGS1-2	10EGS1-2			
Filtered modules with ground circuit inductor						
1EGG1C-1	3EGG1C-1	6EGG1C-1				
1EGG1C-2	3EGG1C-2	6EGG1C-2				
1EGG8C-1	3EGG8C-1	6EGG8C-1				
1EGG8C-2	3EGG8C-2	6EGG8C-2				
Medical filter modules						
1EHG1-2	3EHG1-2	6EHG1-2	10EHG1-2			
1EHG8-2	3EHG8-2	6EHG8-2	10EHG8-2			
1EHGS1-2	3EHGS1-2	6EHGS1-2	10EHGS1-2			
	-					


Filtered modules

Catalog: 1654001 Issue Date: 06.2011

Smallest Power Entry Module with Metric Fuse Holders (continued)

GG & HG Series

Electrical Schematic



Note 1: Second fuse only in -2 version


Note 2: C versions only

Note 3: Not present in HG versions

Warning: Do not attempt to operate a single-fused model without the fuse door in place.


Accessories

GA400: NEMA 5-15P to IEC 60320-1 C-13 line cord



Case Styles

GG1, GG1C & HG1




Typical Dimensions:

Mounting holes (2):

Line Inlet (1): Load Terminals (2): Ground Terminal (1): .132 [3.35] Dia. with .236 [5.99] Dia. x 90° countersink for #4 flathead screw IEC 60320-1 C14 .250 [6.3] with .07 [1.8] Dia. hole .250 [6.3] with .07 x .16 [1.8 x 3.8] slot

GS1 & HGS1




Typical Dimensions:

Line Inlet (1): Load Terminals (2): Ground Terminal (1): IEC 60320-1 C14

.250 [6.3] with .07 [1.8] Dia. hole .250 [6.3] with .07 x .16 [1.8 x 3.8] slot

GG8 & HG8



Typical Dimensions:

Mounting holes (2):

.132 [3.35] Dia. with .236 [5.99] Dia. x 90° countersink for #4 flathead screw

IEC 60320-1 C14

Line Inlet (1): Wire Leads:

5.0 [127.0] Min., 18AWG, UL1015

Case Dimensions


Part No.	Α	В	С	D	E
Fait No.	(max.)	(max.)	(max.)	± .015 ± .38	(max.)
GG1 & HG1	2.13	1.13	1.29	1.417	1.76
	54.5	28.7	32.8	36.0	44.7
GG1C	2.45	1.13	1.28	1.417	1.76
	62.23	28.7	32.5	36.0	44.7
CC1 LICC1	2.13	1.13	1.28	1.46*	1.42
GS1, HGS1	54.0	28.7	32.5	36.0*	36.1
GG8, HG8	2.02	1.13	1.29	1.417	1.76
	51.1	28.7	32.8	36.0	44.7

*max. dimension

Recommended Panel Cutouts

GG / HG

GS / HGS



Front or Back Mount

Front Mount Only

Typical Dimensions:

GS / HGS panel thickness: 0.032 – 0.080 [0.81 – 2.03] Corner radius: 0.138 [0.35] **Power Inlet Filters & Power Entry Modules**



Catalog: 1654001 Issue Date: 06.2011


Smallest Power Entry Module with Metric Fuse Holders (continued)


GG & HG Series


Performance Data


Typical Insertion Loss Measured in closed 50 Ohm system


GG & GS Models


















Common Mode / Asymmetrical (L-G)
Differential Mode / Symmetrical (L-L)

HG Models









Minimum Insertion Loss Measured in closed 50 Ohm system

Common Mode / Asymmetrical (Line to Ground)

Current Frequency - MHz Rating .01 .05 .10 .15 .5 GG & GS Models 1A ЗА 6A

10A **HG Models** 1A 3A 6A

3 5

Differential Mode / Symmetrical (Line to Line)

Current	Frequency – MHz							
Rating	.10	.15	.5	1	3	5	10	30
GG & GS Mod	els							
1A	1	3	14	23	41	47	50	44
3A	1	2	11	14	25	38	44	40
6A	1	2	10	13	23	33	39	42
10A	4	7	17	23	-	22	43	38
HG Models								
1A	2	6	19	26	30	35	35	20
3A	1	7	16	23	30	30	30	30
6A	4	7	16	23	30	30	30	30
10A	-	8	16	22	-	37	43	28

10A