


## 504-AG11D Product Details

[Live Product Chat](#)



### 504-AG11D

TE Part Number: 6-1437529-1

[Active](#)

[Add to Part List](#)

### DIP Sockets

[Not EU RoHS or ELV Compliant](#) ([Find RoHS Compliant Alternates](#))

#### Product Highlights:

- Crystal Oscillator DIP Socket
- Number of Positions = 4
- Row-to-Row Spacing = 7.62 mm
- Thru Hole
- Mount Style = Vertical

[View all Features](#) | [Find Similar Products](#)

### Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)
- ▶ [Request Samples](#)

**NEW!**

## Documentation & Additional Information

### Product Drawings:

- None Available

### Catalog Pages/Data Sheets:

- None Available

### Product Specifications:

- None Available

### Application Specifications:

- None Available

### Instruction Sheets:

- None Available

### CAD Files:

- None Available

### Additional Information:

- [Product Line Information](#)

### Related Products:

- [Tooling](#)

## Product Features (Please use the Product Drawing for all design activity)

### Product Type Features:

- [Product Type](#) = Crystal Oscillator DIP Socket
- [Number of Positions](#) = 4
- [Profile](#) = Low
- [Frame Style](#) = Closed
- [Leg Style](#) = Straight
- Sleeve Material = Brass
- Product Series = 500 Series

### Electrical Characteristics:

- Insulation Resistance (MΩ) = 5,000
- Contact Resistance (mΩ) = 10
- Contact Rating = 3A

### Termination Related Features:

- [Termination \(Solder\) Post Length \(mm \[in\]\)](#) = 2.79 [0.110]
- Solder Tail Contact Plating = Tin-Lead

### Body Related Features:

- [Row-to-Row Spacing \(mm \[in\]\)](#) = 7.62 [0.300]
- [Mount Style](#) = Vertical
- [Centerline \(mm \[in\]\)](#) = 2.54 [0.100]

### Contact Related Features:

- [Contact Mount](#) = Thru Hole
- [Contact Material](#) = Beryllium Copper
- [Contact Mating Area Plating Material](#) = Gold
- [Contact Style](#) = Screw Machine
- [Mating Contact Type](#) = Four-Fingered

### Housing Related Features:

- Housing Material = Thermoplastic Polyester
- Housing Flammability Rating = UL 94V-0

### Configuration Related Features:

- [Height Above PC Board \(mm \[in\]\)](#) = 3.43 [0.135]
- Lead Size Accepted (mm [in]) = 0.41 [0.016]

### Industry Standards:

- [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C

### Conditions for Usage:

- Temperature Range (°C) = -55 - +125

### Packaging Related Features:

- [Packaging Method](#) = Tube

### Other:

- Brand = AMP