BBULGIN

BUCCANEER

Ethernet Buccaneer®





Coupling ring, screw thread provides secure cable coupling


Shroud for RJ45 provides protection against damage through mis-use and positive alignment for mating of connectors

> Panel gasket maintains IP68 seal to panel

Sealing gland and cage optimised to maintain IP68 seal and provide secure cable restraint without disrupting signal

Shielded Cat 5e coupler maintains screening

'O' ring maintains IP68 seal at connector interface



Over moulded assembly provides IP68 cable seal

Coupling ring, screw thread provides secure cable coupling

Sealing Cap Clip

Shroud for RJ45 provides protection against damage through mis-use and positive alignment for mating of connectors

'O' ring maintains IP68 seal at connector interface

Panel gasket maintains IP68 seal to panel

Retaining Nut

- IP68 rated
- Cat 5e compliant
- PE or PUR jacket on cable
- Shielded system
- Cat 5e shielded coupler
- Shroud on RJ45
- Screw coupling
- Rewireable flex connector
- PCB mounted panel connector
- IDC termination panel connector
- Earth lead version of panel adaptor

- Dust and waterproof sealing when mated
- Data rate up to 100MHz
- Good chemical and water resistance
- High noise immunity and EMI protection
- Maintains shielding
- Protection from abuse and mis-mating
- Secure, proven locking system
- Ability to 'field' terminate
- Direct PCB mount panel connector
- Simple termination
- Continuous screening of panel mount connector



77.5

Ethernet Buccaneer®

Ø 38 LENGTH +20.0 Mates with panel mounting 77 5 connector (PX0833) Patchcords with IP68 connector Supplied with shielded RJ45 plug PX0830 - wire ended Single or double end PX0830 terminated Standard lengths: 2m, 3m & LENGTH ±20.0 Ø 38. I 5m 77.5 S-FTP cable construction PE jacket cable Wiring configuration to 568-B Exceeds EIA/TIA Cat 5e PX0831- single ended

Ø 38.


PX0832 - double ended

Part no.	Туре	Length	Description
PX0830/2M00	Wire end	2m	IP68 RJ Buccaneer to bare end
PX0830/3M00	Wire end	3m	IP68 RJ Buccaneer to bare end
PX0830/5M00	Wire end	5m	IP68 RJ Buccaneer to bare end
PX0831/2M00	Single ended	2m	IP68 RJ Buccaneer to Shielded RJ45
PX0831/3M00	Single ended	3m	IP68 RJ Buccaneer to Shielded RJ45
PX0831/5M00	Single ended	5m	IP68 RJ Buccaneer to Shielded RJ45
PX0832/2M00	Double ended	2m	IP68 RJ Buccaneer to IP68 RJ Buccaneer
PX0832/3M00	Double ended	3m	IP68 RJ Buccaneer to IP68 RJ Buccaneer
PX0832/5M00	Double ended	5m	IP68 RJ Buccaneer to IP68 RJ Buccaneer



- Mates with panel mounting connector (PX0833)
- Patchcords with IP68 connector
- Supplied with shielded RJ45
- Single or double end terminated
- Standard lengths: 2m, 3m & 5m
- S-FTP cable construction
- PUR jacket cable
- Wiring configuration to 568-B
- Exceeds EIA/TIA Cat 5e

Part no.	Туре	Length	Description
PX0836/2M00 PX0836/3M00 PX0836/5M00 PX0837/2M00 PX0837/3M00 PX0837/5M00 PX0838/2M00 PX0838/3M00	Wire end Wire end Single ended Single ended Single ended Double ended Double ended	2m 3m 5m 2m 3m 5m 2m 3m	IP68 RJ Buccaneer to bare end IP68 RJ Buccaneer to bare end IP68 RJ Buccaneer to bare end IP68 RJ Buccaneer to Shielded RJ45 IP68 RJ Buccaneer to Shielded RJ45 IP68 RJ Buccaneer to IP68 RJ Buccaneer IP68 RJ Buccaneer to IP68 RJ Buccaneer
PX0838/5M00	Double ended	5m	IP68 RJ Buccaneer to IP68 RJ Buccaneer




LENGTH ±20.0



Ethernet Buccaneer®




- Mates with panel mounting connector (PX0833)
- Supplied with shielded RJ45 plug
- Two versions: for PE and PUR jacket cable (Cat 5e) for other cable sizes from 3.5 to 8mm dia.



Part no.	Description
PX0834/A	Cable glands optimised for PE and PUR jacket cable to maintain Cat 5e performance
PX0834/B	Suitable for use with cables from 3.5 to 8mm diameter







Part no.	Description	Fixing
PX0833	Cat 5e coupler	Front panel mounted
PX0833/E	Cat 5e coupler + earth wire	Front panel mounted

PCB MOUNTING CONNECTOR	
	Cat 5e shielded RJ45 interface
	Rear of panel mounted
E CA	 Mates with PX0830, PX0836 and PX0834 flex connectors
	For direct mounting to PCB
	 Complete with panel sealing gasket
PX0839/PC	

5.20 Max Panel 0.8 Min Panel 7.75
H4.45±0.10 ±0.05 ±0.

Part no.	Description	Fixing	
PX0839/PC	Cat 5e coupler	Rear panel mounted	







Ø42.0

P X 0 7

PANEL MOUNTING CONNECTOR		 Cat 5e shielded RJ45 interface Rear of panel mounted Mates with PX0830, PX0836 and PX0834 flex connectors IDC blocks for discreet termination Complete with panel sealing gasket 	Ø 45.00 12.5 25.2 Ø 35.70 Ø 35.25 Fixing Details 5.2 Max Panel 0.8 Min Panel
Part no.	Description	Fixing	
PX0839/IDC	Cat 5e coupler	Rear panel mounted	
ACCESSOR	RIES	 Sealing caps to maintain IP68 rating when connectors are not in use Replacement shielded RJ45s 	PX0835

Hand crimp tool for shielded

Patch cord cable available in

Hanc
 RJ45

Sealing Cap for flex connectors (PX0830-832, PX0834, PX0836-838)

Sealing Cap for nex connectors (FX0830-032, FX0834, F7 Sealing Cap for panel mounting connector (PX0833) Sealing Cap for rear panel mounting connector (PX0839) Hand crimp tooling + die set PE Jacket Cable - 500 reel

Sealing Caps

PUR Jacket Cable - 50m reel

Replacement shielded RJ45

Description

50m reels

Part no.

PX0835

PX0733 PX0711 14151 14152 14199

14150

www.bulgin.co.uk

BBULGIN

BUCCANEER


Ethernet Buccaneer®

Stranded S-FTP Patch cord cable - PE and PUR Jacket

A choice of two cables with internal construction exceeding Cat 5e performance levels. The Polyethylene (PE) jacket is designed to cope with the rigours that applications in external environments demand. The outer sheath provides good levels of resistance to water, oils and chemicals, will not crack with prolonged exposure to water or UV, and provides good abrasion resistance. The Polyurethane (PUR) jacket has excellent abrasion, chemical and ozone resistance, low smoke, low halogen flame retardant construction suitable for internal and external industrial environments.

Construction	Polyethylene (PE) Jacket	Polyurethane (PUR) Jacket	
Conductors	26AWG (7/0.16mm) bare copper	24AWG (7/0.2mm) bare copper	
Insulation	Polyeolefin (0.94mm nominal)	HD-PE	
Pair	2 of the above cores twisted	2 of the above cores twisted	
Core	4 of the above cores	4 of the above cores	
Таре	1 lap PEPT tape	1 lap mylar tape	
Screen	1 layer PEPT and aluminium tape. 0.1mm tinned copper braid	1 layer mylar and aluminium tape, tape, 0.12mm tinned copper braid	
Sheath	PE Jacket Black	PUR Jacket Black	
Op Temperature	–25°C to +60°C	−25°C to +85°C	
Min. bend radius	8 x o/d (installation)	10 x o/d (installation)	
Min. bend radius	4 x o/d (installed)	6 x o/d (installed)	
Diameter	5.6mm nominal	6.1mm nominal	
Electrical @ 20°C			
Characteristic		1000 - 150 - 100000	
Impedance	$100\Omega \pm 15\Omega$ @ $100MHz$	100Ω ±15Ω @ 100MHz	
Capacitance	1600pF/km	330pF/km	
Conductor Loop resistance	$29\Omega/100$ m maximum	29 Ω /100m maximum	
Skew	40 nsec/100m @ 100MHz	45 nsec/100m @ 100MHz	
TIA/EIA Rating	Cat 5e	Cat 5e	

Cable constructions



Polyurethane (PUR) Jacket

Re-wireable and Panel mounted connectors

Mechanical		
Sealing	IP68, EN60529	
Materials		
Connector Body	Polyester	
Flammability rating	UL94V-0	
'O' rings	Silicon	
Panel Gasket	Silicon	
Operating Temperature	-20°C to +70°C	
RoHS	Compliant	

Polycarbonate

Phosphor Bronze

50 micron gold

-40°C to +70°C

30V ac, 42V dc $10 \text{m}\Omega$ max.

1,000 cycles

Compliant

8

1.5A

Cat 5e

UL94V-0

RJ45 Plug

Materials Moulding Flammability Contact material Contact plating Operating Temperature Mating cycles RoHS


Electrical

No. Conductors Current rating Voltage rating Contact resistance Performance

RJ45 Coupler

Materials

Coupler Shell Copper Alloy Coupler Plating Nickel Moulding ABS UL94V-0 Flammability Contact material Phosphor Bronze Contact plating 50 micron gold $-40^{\circ}C$ to $+70^{\circ}C$ Operating Temperature Mating cycles 1,000 cycles RoHS Compliant Electrical No. Conductors 8 1.5A Current rating Voltage rating 30V ac, 42V dc Contact resistance $10 \text{m}\Omega$ max. Performance Cat 5e







CABLE JOINER IP68 Rating 60 Connections Coupler (UTP) versions

PX0777

- For Sealed In-Line RJ45
- Supplied Complete with
- Shielded (STP) & Unshielded
- Cat5e Shielded Coupler also available
- Cable Range 3.5 - 8mm (with glands supplied)





Specification	PX0777/UTP	PX0777/STP	PX0777/CAT5ESTP
Rating:	1.5A, 30V a.c., 42V d.c.	1.5A, 30V a.c., 42V d.c.	1.5A, 30V a.c., 42V d.c.
No. of Conductors:	8	8	8
Coupler Type:	Unshielded	Shielded	Shielded CAT5e performance
Cable Range:	3.5 - 8mm (with glands supplied)	3.5 - 8mm (with glands supplied)	3.5 - 8mm (with glands supplied)
Material:	Glass Filled Polyamide UL94V-0	Glass Filled Polyamide UL94V0	Glass Filled Polyamide UL94V-0
Sealing:	IP68 to BSEN 60529 : 1977	IP68 to BSEN 60529 : 1977	IP68 to BSEN 60529 : 1977
Operating Temp. Range:	-20°C to +70°C	-20°C to +70°C	-20°C to +70°C
Colour:	Black	Black	Black
RoHS	Compliant	Compliant	Compliant