

## MINISMDC110F/16-2 Product Details



**MINISMDC110F/16-2**  
(RF1338-000)

TE Internal Number: RF1338-000

 [Active](#)

### PolySwitch Resettable Devices

 [Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

#### Product Highlights:

- Surface Mount Application
- Vmax = 16 V
- Imax = 100 A
- Family Name = miniSMD
- Surface Mount Construction

[View all Features](#)

### Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

 [Add to My Part List](#)  [Request Sample](#)  [Find Similar Products](#)  [Buy Product](#)

### Documentation & Additional Information

#### Product Drawings:

- None Available

#### Catalog Pages/Data Sheets:

- [CP CATALOG 2011 - SURFACE-MOUNT](#) (PDF, English)

#### Product Specifications:

- [miniSMDC110F/16](#) (PDF, English)

#### Application Specifications:

- None Available

#### Instruction Sheets:

- None Available

#### CAD Files:

- None Available

#### Additional Information:

- [Product Line Information](#)

#### Related Products:

- [Tooling](#)

[List all Documents](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- UL File Number = E74889
- CSA File Number = CA78165

#### Electrical Characteristics:

- Vmax (V) = 16
- Imax (A) = 100
- [IH \(Room Temperature\) \(A\)](#) = 1.1
- [IT \(Room Temperature\) \(A\)](#) = 2.20
- [Rmin \(Ω\)](#) = 0.06
- [R1 Max \[Post Trip\] \(Ω\)](#) = 0.18

#### Termination Features:

- Construction = Surface Mount

#### Contact Features:

- Family Name = miniSMD

#### Configuration Features:

- [Form Factor \(inches\)](#) = 1812
- [Form Factor \(mm\)](#) = 4532

#### Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Reflow solder capable to 245°C, Reflow solder capable to 260°C
- RoHS/ELV Compliance History = Always was RoHS compliant
- TUV Certificate No. = R72041438

#### Environmental:

- [Operating Temperature \(Max.\) \(°C\)](#) = 85

#### Operation/Application:

- Application = Surface Mount

#### Packaging Features:

- Packaging Method = Tape & Reel

#### Other:

- Brand = Raychem

### Corporate Information

[Who We Are](#)  
[Investors](#)  
[News Room](#)  
[Supplier Portal](#)  
[Careers](#)

### Quick Links

[Check Distributor Inventory](#)  
[Cross Reference](#)  
[Find Documents & Drawings](#)  
[Product Compliance Support Center](#)  
[Site Map](#)

### Customer Support

[Email or Chat With Us](#)  
[Find a Phone Number](#)  
[Search Knowledge Base](#)  
[Manage your Account](#)

### Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

