

November 2010

P6KE6V8(C)A - P6KE440(C)A 600 Watt Transient Voltage Suppressors

Features

- · Glass passivated junction.
- 600W Peak Pulse Power capability at 1.0ms.
- · Excellent clamping capability.
- · Low incremental surge resistance.
- Fast response time; typically less than 1.0ps from 0 volts to BV for unidirectional and 5.0ns for bidirectional.
- Typical I_R less than 1.0μA above 10V.



DO-15
COLOR BAND DENOTES CATHODE
ON UNIDIRECTIONAL DEVICES ONLY. NO

Applications

- Devices For Bipolar Applications.
- · Bidirectional types use CA suffix.
- Electrical Characteristics apply in both directions.

Absolute Maximum Ratings* T_A = 25°C unless otherwise noted

| Symbol | Parameter | Value | Units |
|------------------|--|-------------|-------|
| P _{PPM} | Peak Pulse Power Dissipation at T _P =1ms | 600 | W |
| I _{PPM} | Peak Pulse Current | see table | Α |
| P _D | Power Dissipation .375 " lead length @ T _A = 75°C | 5.0 | W |
| I _{FSM} | Non-repetitive Peak Forward Surge Current superimposed on rated load (JEDEC method) (Note 1) | 100 | А |
| T _{stg} | Storage Temperature Range | -65 to +175 | °C |
| TJ | Operating Junction Temperature | 175 | °C |

^{*} These ratings are limiting values above which the serviceability of any semiconductor device may be impaired. **Note 1**: Measured on 8.3 ms single half-sine wave; Duty cycle = 4 pulses per minute maximum.

Electrical Characteristics $T_A = 25^{\circ}C$ unless otherwise noted

| Uni-directional Bi-directional (C) Device | Reverse Stand-off Voltage V _{RWM} (V) | Volt | down age (V) | Test Current I _T (mA) | Clamping Voltage @I _{PPM} V _C (V) | Peak Pulse Current I _{PPM} (A) | Reverse Leakage V _{RWM} | Temperature Coefficient V _{BR} (%/°C) |
|---|--|-------|--------------------|--|---|---|--|--|
| | | Min. | Max. | | | | I_R (μΑ) * | |
| P6KE6V8(C)A | 5.80 | 6.45 | 7.14 | 10 | 10.5 | 57.1 | 1000 | 0.057 |
| P6KE7V5(C)A | 6.40 | 7.13 | 7.88 | 10 | 11.3 | 53.1 | 500 | 0.061 |
| P6KE8V2(C)A | 7.02 | 7.79 | 8.61 | 10 | 12.1 | 50.0 | 200 | 0.065 |
| P6KE9V1(C)A | 7.78 | 8.65 | 9.55 | 1 | 13.4 | 45.0 | 50 | 0.068 |
| P6KE10(C)A | 8.55 | 9.50 | 10.5 | 1 | 14.5 | 41.0 | 10 | 0.073 |
| P6KE11(C)A | 9.40 | 10.5 | 11.6 | 1 | 15.6 | 38.0 | 5 | 0.075 |
| P6KE12(C)A | 10.2 | 11.4 | 12.6 | 1 | 16.7 | 36.0 | 5 | 0.078 |
| P6KE13(C)A | 11.1 | 12.4 | 13.7 | 1 | 18.2 | 33.0 | 5 | 0.081 |
| P6KE15(C)A | 12.8 | 14.3 | 15.8 | 1 | 21.2 | 28.0 | 5 | 0.084 |
| P6KE16(C)A | 13.6 | 15.2 | 16.8 | 1 | 22.5 | 27.0 | 5 | 0.086 |
| P6KE18(C)A | 15.3 | 17.1 | 18.9 | 1 | 25.2 | 24.0 | 5 | 0.088 |
| P6KE20(C)A | 17.1 | 19.0 | 21.0 | 1 | 27.7 | 22.0 | 5 | 0.090 |
| P6KE22(C)A | 18.8 | 20.9 | 23.1 | 1 | 30.6 | 20.0 | 5 | 0.092 |
| P6KE24(C)A | 20.5 | 22.8 | 25.2 | 1 | 33.2 | 18.1 | 5 | 0.094 |
| P6KE27(C)A | 23.1 | 25.7 | 28.4 | 1 | 37.5 | 16.0 | 5 | 0.096 |
| P6KE30(C)A | 25.6 | 28.5 | 31.5 | 1 | 41.4 | 14.5 | 5 | 0.097 |
| P6KE33(C)A | 28.2 | 31.4 | 34.7 | 1 | 45.7 | 13.2 | 5 | 0.098 |
| P6KE36(C)A | 30.8 | 34.2 | 37.8 | 1 | 49.9 | 12.0 | 5 | 0.099 |
| P6KE39(C)A | 33.3 | 37.1 | 41.0 | 1 | 53.9 | 11.2 | 5 | 0.100 |
| P6KE43(C)A | 36.8 | 40.9 | 45.2 | 1 | 59.3 | 10.1 | 5 | 0.101 |
| P6KE47(C)A | 40.2 | 44.7 | 49.4 | 1 | 64.8 | 9.3 | 5 | 0.101 |
| P6KE51(C)A | 43.6 | 48.5 | 53.6 | 1 | 70.1 | 8.6 | 5 | 0.102 |
| P6KE56(C)A | 47.8 | 53.2 | 58.8 | 1 | 77.0 | 7.8 | 5 | 0.103 |
| P6KE62(C)A | 53.0 | 58.9 | 65.1 | 1 | 85.0 | 7.1 | 5 | 0.104 |
| P6KE68(C)A | 58.1 | 64.6 | 71.4 | 1 | 92.0 | 6.5 | 5 | 0.104 |
| P6KE75(C)A | 64.1 | 71.3 | 78.8 | 1 | 103.0 | 5.8 | 5 | 0.105 |
| P6KE82(C)A | 70.1 | 77.9 | 86.1 | 1 | 113.0 | 5.3 | 5 | 0.105 |
| P6KE91(C)A | 77.8 | 86.5 | 95.5 | 1 | 125.0 | 4.8 | 5 | 0.106 |
| P6KE100(C)A | 85.5 | 95.0 | 105.0 | 1 | 137.0 | 4.4 | 5 | 0.106 |
| P6KE110(C)A | 94.0 | 105.0 | 116.0 | 1 | 152.0 | 4.0 | 5 | 0.107 |
| P6KE120(C)A | 102.0 | 114.0 | 126.0 | 1 | 165.0 | 3.6 | 5 | 0.107 |
| P6KE130(C)A | 111.0 | 124.0 | 137.0 | 1 | 179.0 | 3.4 | 5 | 0.107 |
| P6KE150(C)A | 128.0 | 143.0 | 158.0 | 1 | 207.0 | 2.9 | 5 | 0.108 |
| P6KE160(C)A | 136.0 | 152.0 | 168.0 | 1 | 219.0 | 2.7 | 5 | 0.108 |
| P6KE170(C)A | 145.0 | 162.0 | 179.0 | 1 | 234.0 | 2.6 | 5 | 0.108 |
| P6KE180(C)A | 154.0 | 171.0 | 189.0 | 1 | 246.0 | 2.4 | 5 | 0.108 |
| P6KE200(C)A | 171.0 | 190.0 | 210.0 | 1 | 274.0 | 2.2 | 5 | 0.108 |
| P6KE220(C)A | 185.0 | 209.0 | 231.0 | 1 | 328.0 | 1.9 | 5 | 0.108 |
| P6KE250(C)A | 214.0 | 237.0 | 263.0 | 1 | 344.0 | 1.8 | 5 | 0.110 |
| P6KE300(C)A | 256.0 | 285.0 | 315.0 | 1 | 414.0 | 1.5 | 5 | 0.110 |
| P6KE350(C)A | 300.0 | 332.0 | 368.0 | 1 | 482.0 | 1.3 | 5 | 0.110 |
| P6KE400(C)A | 342.0 | 380.0 | 420.0 | 1 | 548.0 | 1.1 | 5 | 0.110 |
| P6KE440(C)A | 376.0 | 418.0 | 462.0 | 1 | 602.0 | 1.0 | 5 | 0.110 |
| | | | | | 302.0 | | | 30 |

 $^{^{\}star}$ For bidirectional parts with V_{RWM}<10V, the I_R max limit is doubled.

Typical Performance Characteristics




Figure 1. Peak Pulse Power Rating Curve




Figure 2. Pulse Derating Curve




Figure 3. Pulse Waveform




Figure 4. Total Capacitance - Unidirectional




Figure 5. Steady State Power Derating Curve




Figure 6. Non-Repetitive Surge Current





TRADEMARKS

The following includes registered and unregistered trademarks and service marks, owned by Fairchild Semiconductor and/or its global subsidiaries, and is not intended to be an exhaustive list of all such trademarks.

 AccuPower™
 F-PFS™

 Auto-SPM™
 FRFET®

 Build it Now™
 Global Power Resource SM

 CorePLUS™
 Green FPS™

 CorePOWER™
 Green FPS™ e-Series™

 CROSSVOLT™
 Gmax™

 CTL™
 GTO™

Current Transfer Logic™

DEUXPEED®

Dual Cool™

EcoSPARK®

EfficientMax™

MicroFET™

ESBC™

MicroPak™

MicroPak™

Fairchild® MillerDrive™ MotionNax™ Motion-SPM™ OptoHiT™ OPTOLOGIC® FAST® OPTOLOGIC® OPTOPLANAR®

FlashWriter®* PDP SPM™

Power-SPM™ PowerTrench® PowerXS™

Programmable Active Droop™

QFET[®] QS™

Quiet Series™ RapidConfigure™

Saving our world, 1mW/W/kW at a time™ SignalWise™

SmartMax™
SMART START™
SPM®
STEALTH™
SuperFET®
SuperSOT™-3
SuperSOT™-6
SuperSOT™-8
SuperMOS®
SyncFET™

Sync-Lock™

The Power Franchise®

the Wer
franchise

TinyBoost™
TinyBuck™
TinyCalc™
TinyCogic®
TiNYOPTO™
TinyPower™
TinyPower™
TinyPWM™
TinyWire™
TriFault Detect™
TRUECURRENT™*

µSerDes™

SYSTEM ®

SerDes*
UHC®
Ultra FRFET™
UniFET™
VCX™
VisualMax™
XS™

DISCLAIMER

FETBench™

FAIRCHILD SEMICONDUCTOR RESERVES THE RIGHT TO MAKE CHANGES WITHOUT FURTHER NOTICE TO ANY PRODUCTS HEREIN TO IMPROVE RELIABILITY, FUNCTION, OR DESIGN. FAIRCHILD DOES NOT ASSUME ANY LIABILITY ARISING OUT OF THE APPLICATION OR USE OF ANY PRODUCT OR CIRCUIT DESCRIBED HEREIN; NEITHER DOES IT CONVEY ANY LICENSE UNDER ITS PATENT RIGHTS, NOR THE RIGHTS OF OTHERS. THESE SPECIFICATIONS DO NOT EXPAND THE TERMS OF FAIRCHILD'S WORLDWIDE TERMS AND CONDITIONS, SPECIFICALLY THE WARRANTY THEREIN, WHICH COVERS THESE PRODUCTS.

LIFE SUPPORT POLICY

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF FAIRCHILD SEMICONDUCTOR CORPORATION.

As used herein:

- Life support devices or systems are devices or systems which, (a) are
 intended for surgical implant into the body or (b) support or sustain life,
 and (c) whose failure to perform when properly used in accordance
 with instructions for use provided in the labeling, can be reasonably
 expected to result in a significant injury of the user.
- A critical component in any component of a life support, device, or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

ANTI-COUNTERFEITING POLICY

Fairchild Semiconductor Corporation's Anti-Counterfeiting Policy. Fairchild's Anti-Counterfeiting Policy is also stated on our external website, www.fairchildsemi.com, under Sales Support.

Counterfeiting of semiconductor parts is a growing problem in the industry. All manufacturers of semiconductor products are experiencing counterfeiting of their parts. Customers who inadvertently purchase counterfeit parts experience many problems such as loss of brand reputation, substandard performance, failed applications, and increased cost of production and manufacturing delays. Fairchild is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. Fairchild strongly encourages customers to purchase Fairchild parts either directly from Fairchild or from Authorized Fairchild Distributors who are listed by country on our web page cited above. Products customers buy either from Fairchild directly or from Authorized Fairchild Distributors are genuine parts, have full traceability, meet Fairchild's quality standards for handling and storage and provide access to Fairchild's full range of up-to-date technical and product information. Fairchild and our Authorized Distributors will stand behind all warranties and will appropriately address any warranty issues that may arise. Fairchild will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources. Fairchild is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.

PRODUCT STATUS DEFINITIONS

Definition of Terms

| Definition of Terms | | | | | |
|--------------------------|-----------------------|---|--|--|--|
| Datasheet Identification | Product Status | Definition | | | |
| Advance Information | Formative / In Design | Datasheet contains the design specifications for product development. Specifications may change in any manner without notice. | | | |
| Preliminary | First Production | Datasheet contains preliminary data; supplementary data will be published at a later date. Fairchild Semiconductor reserves the right to make changes at any time without notice to improve design. | | | |
| No Identification Needed | Full Production | Datasheet contains final specifications. Fairchild Semiconductor reserves the right to make changes at any time without notice to improve the design. | | | |
| Obsolete | Not In Production | Datasheet contains specifications on a product that is discontinued by Fairchild Semiconductor. The datasheet is for reference information only. | | | |

Rev I50

^{*} Trademarks of System General Corporation, used under license by Fairchild Semiconductor,