

SMD300F-2 Product Details

[Share](#) [Print](#) [Email](#)


SMD300F-2
(RF0322-000)

TE Internal Number: RF0322-000

 [Active](#)

PolySwitch Resettable Devices

 [Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Surface Mount Application
- Vmax Operating = 6 V
- Vmax = 6 V
- Imax = 40 A
- Family Name = SMD

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#)  [Request Sample](#)  [Find Similar Products](#)  [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- [CP CATALOG 2011 - SURFACE-MOUNT](#) (PDF, English)

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- UL File Number = E74889
- CSA File Number = CA78165

Electrical Characteristics:

- [Vmax Operating \(V\)](#) = 6
- Vmax (V) = 6
- Imax (A) = 40
- [IH \(Room Temperature\) \(A\)](#) = 3
- [IT \(Room Temperature\) \(A\)](#) = 6.00
- [Rmin \(Ω\)](#) = 0.015
- [R1 Max \[Post Trip\] \(Ω\)](#) = 0.048
- Power Dissipation (Max) (W) = 1.5

Termination Features:

- Construction = Surface Mount

Contact Features:

- [Family Name](#) = SMD

Configuration Features:

- [Form Factor \(inches\)](#) = 2920
- [Form Factor \(mm\)](#) = 7555

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Reflow solder capable to 245°C, Reflow solder capable to 260°C
- RoHS/ELV Compliance History = Always was RoHS compliant
- TUV Certificate No. = R72041427

Environmental:

- [Operating Temperature \(Max.\) \(°C\)](#) = 85

Operation/Application:

- Application = Surface Mount

Packaging Features:

- Packaging Method = Tape & Reel

Other:

- Brand = Raychem

Corporate Information

[Who We Are](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)

Quick Links

[Check Distributor Inventory](#)
[Cross Reference](#)
[Find Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Search Knowledge Base](#)
[Manage your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

