



### FEATURES

- Transient Protection: Meets the requirements of IEEE 472, "Surge Withstanding Capability Test"
- SPST, Normally Open
- UL, CSA, CE, TÜV Certified
- Optical Isolation
- OpenLine<sup>®</sup> and G5 Modules Provide Replaceable 5x20mm Glass Fuses
- Built-in Status LED
- Lifetime Warranty



70L-ODC 70G-ODC

70M-ODC

## DIMENSIONS


For complete dimensional drawings, see pages L-4 or L-5.

### FUSES

G5 Fuses are 5 Amp Littelfuse part number 217005 or equivalent. OpenLine® fuses are 3.15 Amp Littelfuse part number 2173.15.

Fuse kits available, see page L-104.


## CIRCUITRY



### Maximum Current Versus Ambient Temperature

The chart indicates continuous current to limit the junction temperatures to 115°C. Information is based on steady state heat transfer in a 2 cubic foot sealed enclosure.

70-ODC



# SPECIFICATIONS: By Package Style

Package Style		Std (70-)	Mini (70M-)	G5 (70G-)	OL (70L-)
Specifications	Units				
Load Current Range <sup>1</sup>	А	0.02-3.5	0.02-3.0	0.02-3.5	0.02-2.0/CH
Surge Current for 1 Sec.	A	5	5	5	5
Maximum Reverse Logic Voltage	Vdc	-5	-5	-5	-5
Isolation Voltage <sup>2</sup>	Vrms	4000	4000	4000	2500
Vibration <sup>3</sup>		MIL-STD-202	MIL-STD-202	MIL-STD-202	IEC68-2-6
Mechanical Shock <sup>4</sup>		MIL-STD-202	MIL-STD-202	MIL-STD-202	IEC68-2-27
Storage Temp. Range	°C	-40 to 125	-40 to 125	-40 to 125	-40 to 100
Operating Temp. Range	°C	-40 to 100	-40 to 100	-40 to 100	-40 to 85
Warranty		Lifetime	Lifetime	Lifetime	Lifetime

<sup>1</sup> See Figure 1 for derating.

<sup>2</sup> Field to logic and channel-to-channel if Grayhill racks are used.

<sup>3</sup> MIL-STD-202, Method 204, 20 G, 10-2000 Hz or IEC68-2-6, 0.15 mm/sec<sup>2</sup>, 10-150 Hz.

<sup>4</sup> MIL-STD-202, Method 213, Condition F, 1500 G or IEC68-2-27, 11 mS, 15g.



### SPECIFICATIONS: By Part Number Standard and Miniature Modules

Type/Function	Grayhill Part Number							
Miniature, Normally Open	70M-ODC5	70M-ODC5A	70M-ODC5B	70M-ODC15	70M-ODC15B	70M-ODC24	70M-ODC24B	
Standard, Normally Open		70-ODC5	70-ODC5A	70-ODC5B	70-ODC15	70-ODC15B	70-ODC24	70-ODC24B
Specifications	Units							
Maximum Line Voltage Load Voltage Range	Vdc Vdc	60 3-60	200 4-200	60 3-60	60 3-60	60 3-60	60 3-60	60 3-60
Max. Off-State Leakage @ Max. Line Maximum Turn-On Time	mA uSec	1.5 20	0.01 75	0.01 75	1.5 20	0.01 75	1.5 20	0.01 75
Maximum Turn-Off Time Typ. Power Dissipation	µSec W/A	50	750 1.5	500	50	500	50	500 1
Clamping Voltage Nominal Logic Voltage (Vcc)	Vdc Vdc	80 5	360	80 5	80 15	80 15	80 24	80 24
Logic Voltage Range Maximum Logic Supply Current	Vdc	2.5-10	2.5-9	2.5-10	10-18	10-18	15-30	15-30
@ Nominal Vcc	mA Ω	14 300	18	14 300	9 1800	9	9 2700	9 2700
Nominal Input Resistance (Rx) Minimum Drop Out Voltage	Vdc	1	220 1	1	1	1800 1	1	1

### G5 and OpenLine® Modules

Type/Function	Grayhill Part Number							
Fusible, Normally Open		70G-ODC5	70G-ODC5A	70G-ODC5B	70G-ODC15	70G-ODC15B	70G-ODC24	70G-ODC24B
Specifications	Units							
Maximum Line Voltage	Vdc	60	200	60	60	60	60	60
Load Voltage Range	Vdc	3-60	4-200	3-60	3-60	3-60	3-60	3-60
Max. Off-State Leakage @ Max. Line	mA	1.5	0.01	0.01	1.5	0.01	1.5	0.01
Maximum Turn-On Time	µSec	20	75	75	20	75	20	75
Maximum Turn-Off Time	µSec	50	750	500	50	500	50	500
Typ. Power Dissipation	W/A	1	1.5	1	1	1	1	1
Clamping Voltage	Vdc	80	360	80	80	80	80	80
Nominal Logic Voltage (Vcc)	Vdc	5	5	5	15	15	24	24
Logic Voltage Range	Vdc	4-6	4-6	4-6	10-20	10-20	18-32	18-32
Maximum Logic Supply Current								
@ Nominal Vcc	mA	13	13	13	9	9	9	9
Nominal Input Resistance (Rx)	Ω	150	150	150	1500	1500	2700	2700
Minimum Drop Out Voltage	Vdc	1	1	1	1	1	1	1

### **OpenLine® Modules**

Type/Function	Grayhill Part Number			
Dual, Fusible, Normally Open		70L-ODC	70L-ODCA	70L-ODCB
Specifications	Units			
Maximum Line Voltage Load Voltage Range Max. Off-State Leakage @ Max. Line Maximum Turn-On Time Maximum Turn-Off Time Typ. Power Dissipation Clamping Voltage Nominal Logic Voltage (Vcc) Logic Voltage Range Maximum Logic Supply Current @ Nominal Vcc Module ID Resistance to Logic Ground	Vdc Vdc mA µSec WA Vdc Vdc Vdc Vdc MA	60 3-60 1.5 20 50 1 80 5 4.5-28 7/CH 2.15K	200 4-200 .01 75 750 1.5 360 5 4.5-28 7/CH 2.15K	60 3-60 .01 75 500 1 80 5 4.5-28 7/CH 2.15K
Minimum Drop Out Voltage	Vdc	1	1	1

#### **Available from your local Grayhill Distributor.** For prices and discounts, contact a local Sales Office, an authorized local Distributor or Grayhill.