

## 0603SFS200F/32 - 2 Product Details



**0603SFS200F/32** -  
**2**

TE Part Number: RF0339 - 000

 [Active](#)

 [Add to Part List](#)

### Fuses

[Always EU RoHS/ELV Compliant](#) ( [Statement of Compliance](#) )

#### Product Highlights:

- ? Type = DC Slow Blow Fuse
- ? Surface Mount Construction
- ? Form Factor (inches) = 0603
- ? Form Factor (mm) = 1608
- ? Rated Current = 2 Amps.

[View all Features](#) | [Find Similar Products](#)

### Quick Links

[Check Pricing & Availability](#)  
[Search for Tooling Product Feature Selector](#)  
[Contact Us About This Product](#)

### Documentation & Additional Information

#### Product Drawings:

- ? None Available

#### Catalog Pages/Data Sheets:

- ? None Available

#### Product Specifications:

- ? None Available

#### Application Specifications:

- ? None Available

#### Instruction Sheets:

- ? None Available

#### CAD Files:

- ? None Available

#### Additional Information:

- ? [Product Line Information](#)

#### Additional Product Images:

- ? [Reflow Profile](#)

#### Related Products:

- ? [Tooling](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- ? UL Listed = File No. E197536

#### Electrical Characteristics:

- ? Rated Current (Amps.) = 2
- ? Cold DCR (Nominal) (?) = 0.052
- ?  $I^2 t$  (A<sup>2</sup> sec)<sup>2</sup> (Nominal) (?) = 0.32
- ? Interrupt Voltage, Max. (VDC) = 32
- ? Interrupt Current, Max. (Amps.) = 40

#### Termination Related Features:

- ? Construction = Surface Mount

#### Body Related Features:

- ? Type = DC Slow Blow Fuse

#### Contact Related Features:

- ? Family Name = SFS

#### Configuration Related Features:

- ? Form Factor (inches) = 0603
- ? Form Factor (mm) = 1608

#### Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Reflow solder capable to 245°C, Reflow solder capable to 260°C
- ? RoHS/ELV Compliance History = Always was RoHS compliant

#### Conditions for Usage:

- ? Operating Temperature (Max.) (°C) = 125
- ? Min Clear Time @ 100% Rated Current (Hr) = 8
- ? Min Clear Time @ 200% Rated Current (Seconds) = 5
- ? Min Clear Time @ 300% Rated Current (Seconds) = 4.1
- ? Min Clear Time @ 800% Rated Current (Seconds) = 0.0005 - 0.001

#### Other:

- ? Brand = Raychem