



MINISMDC260F/13.2-2 Product Details

[Share](#) | [Print](#) | [Email](#)


MINISMDC260F/13.2-2

TE Internal Number: RF1185-000

Active

PolySwitch Resettable Devices

[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Surface Mount Application
- Vmax Operating = 13.2 V
- Vmax = 13.2 V
- Imax = 100 A
- Family Name = miniSMD

[View all Features](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- [miniSMDC260F/13.2](#) (PDF, English)

Catalog Pages/Data Sheets:

- [CP CATALOG 2011 - SURFACE-MOUNT](#) (PDF, English)

Product Specifications:

- [miniSMDC260F/13.2](#) (PDF, English)

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- UL File Number = E74889
- CSA File Number = CA78165

Electrical Characteristics:

- [Vmax Operating \(V\)](#) = 13.2
- Vmax (V) = 13.2
- Imax (A) = 100
- [IH \(Room Temperature\) \(A\)](#) = 2.6
- [IT \(Room Temperature\) \(A\)](#) = 5.00
- [Rmin \(Ω\)](#) = 0.015
- [R1 Max \[Post Trip\] \(Ω\)](#) = 0.05
- Power Dissipation (Max) (W) = 1.2

Termination Features:

- Construction = Surface Mount

Contact Features:

- Family Name = miniSMD

Configuration Features:

- [Form Factor \(inches\)](#) = 1812
- [Form Factor \(mm\)](#) = 4532

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Reflow solder capable to 245°C, Reflow solder capable to 260°C
- RoHS/ELV Compliance History = Always was RoHS compliant
- TUV Certificate No. = R72111045

Environmental:

- [Operating Temperature \(Max.\) \(°C\)](#) = 85

Operation/Application:

- Application = Surface Mount

Packaging Features:

- Packaging Method = Tape & Reel

Other:

- Brand = Raychem

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)

Quick Links

- [Check Distributor Inventory](#)
- [Cross Reference Products](#)
- [Find Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Search Knowledge Base](#)
- [Manage Your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

