




MINISMDC260F/16-2 Product Details

[Share](#) | [Print](#) | [Email](#)


MINISMDC260F/16-2

TE Internal Number: RF1184-000

Active

PolySwitch Resettable Devices

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Surface Mount Application
- Vmax = 16 V
- Imax = 100 A
- Family Name = miniSMD
- Surface Mount Construction

[View all Features](#)

Quick Links

- ▶ [Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [miniSMDC260F/16 \(PDF, English\)](#)

Catalog Pages/Data Sheets:

- [CP CATALOG 2011 - SURFACE-MOUNT \(PDF, English\)](#)

Product Specifications:

- [miniSMDC260F/16 \(PDF, English\)](#)

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Family Name = miniSMD
- UL File Number = E74889
- CSA File Number = CA78165

Electrical Characteristics:

- Vmax (V) = 16
- Imax (A) = 100
- IH (Room Temperature) (A) = 2.6
- IT (Room Temperature) (A) = 5.00
- Rmin (Ω) = 0.015
- R1 Max [Post Trip] (Ω) = 0.05

Termination Features:

- Construction = Surface Mount

Configuration Features:

- Form Factor (inches) = 1812
- Form Factor (mm) = 4532

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Reflow solder capable to 245°C, Reflow solder capable to 260°C
- [RoHS/ELV Compliance History](#) = Always was RoHS compliant
- TUV Certificate No. = R72111045

Environmental:

- [Operating Temperature \(Max.\) \(°C\)](#) = 85

Operation/Application:

- Application = Surface Mount

Packaging Features:

- Packaging Method = Tape & Reel

Other:

- Brand = Raychem

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)

Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

[▶](#)

