

## Axial Lead and Cartridge Fuses

#### Designed to IEC Standard

## 5 x 20 mm Fast-Acting Fuse 216 Series

• Designed to International (IEC) Standards for use globally.

- Meets the IEC 60127-2, Sheet 1 specification for Fast Acting Fuses.
- Available in Cartridge and Axial Lead Form.
- Available in ratings of 0.050 to 10 amperes.
- High breaking capacity.

#### **ELECTRICAL CHARACTERISTICS:**


| % of Ampere<br>Rating | Ampere<br>Rating | Opening<br>Time                |
|-----------------------|------------------|--------------------------------|
| 150%                  | .05-6.3          | 60 minutes, <b>Min</b> imum    |
| 15078                 | 8-16             | 30 minutes, <b>Min</b> imum    |
| 210%                  | .05-16           | 30 minutes, <b>Max</b> imum    |
| 275%                  | .05-4            | 0.01 sec., Min.; 2 sec. Max.   |
| 215/0                 | 5–6.3            | 0.01 sec., Min.; 3 sec. Max.   |
|                       | 8-16             | 0.04 sec., Min.; 20 sec. Max.  |
| 400%                  | .05-6.3          | .003 sec., Min.; 0.3 sec. Max. |
|                       | 8-16             | .01 sec., Min.; 1.0 sec. Max.  |
| 1000%                 | .05-6.3          | .02 seconds, Maximum           |
|                       | 8-16             | .03 seconds, Maximum           |

#### INTERRUPTING RATING:

0.05 - 10A

1500A @ 250 VAC, 0.7-0.8 power factor

# 🐼 🔍 "N 🕼 📿 (E 🖉 👘



#### **ENVIRONMENTAL SPECIFICATIONS:**

Operating temperature: -55°C to 125°C Thermal Shock: MIL-STD-202F Method 107G, Test Condition B: (5 cycles -65°C to +125°C) Vibration: MIL-STD-202F Method 201A Humidity: MIL-STD-202F Method 103B, Test Condition A. high relative humidity (95%) and elevated temperature (40°C) for 240 hours. Salt Spray: MIL-STD-202F Method 101D, Test Condition B PHYSICAL SPECIFICATIONS:

Material: Body: Ceramic

Cap: Nickel Plated Brass Leads: Tin Plated Copper Filler Sand (160mA – 10A) Terminal Strength: MIL-STD-202F Method 211A,

Test Condition A Solderability: Reference IEC 60127 Second Edition 2003-01 Annex A

Product Marking: Cap 1: current and voltage rating. Cap 2: Agency approval markings. Packaging: Available in Bulk (V=5, H=100, M=1000 pcs/pkg) or on Tape/Reel (MRET1=1000 pcs/reel).

# AXIAL LEAD AND CARTRIDGE FUSES

11

#### **ORDERING INFORMATION:**

| Cartridge<br>Catalog<br>Number | Ampere<br>Rating | Voltage<br>Rating | Nominal<br>Resistance<br>Cold Ohms | Nominal<br>Melting I <sup>2</sup> t<br>A <sup>2</sup> Sec. |
|--------------------------------|------------------|-------------------|------------------------------------|--|
| <b>216</b> .050                | .050             | 250               | 15.900                             | 0.00019  |
| <b>216</b> .063                | .063             | 250               | 10.450                             | 0.00054  |
| <b>216</b> .080                | .080<br>.100     | 250               | 7.885<br>5.793                     | 0.00084<br>0.00450   |
| 216.100<br>216.125             | .100             | 250<br>250        | 3.675                              | 0.00450  |
| 210.125<br>216.160             | .160             | 250               | 5.349                              | 0.00576  |
| <b>216</b> .200                | .200             | 250               | 3.350                              | 0.00438  |
| <b>216</b> .250                | .250             | 250               | 2.350                              | 0.00891  |
| <b>216</b> .315                | .315             | 250               | 1.850                              | 0.015  |
| <b>216</b> .400                | .400             | 250               | 0.903                              | 0.036  |
| <b>216</b> .500                | .500             | 250               | 0.847                              | 0.169  |
| <b>216</b> .630                | .630             | 250               | 0.466                              | 0.179  |
| <b>216</b> .800                | .800             | 250               | 0.295                              | 0.288  |
| 216 001<br>216 1.25            | 1<br>1.25        | 250<br>250        | 0.237<br>0.153                     | 0.180<br>0.477   |
|                                |                  |                   |                                    | -  |
| 216 01.6<br>216 002            | 1.6<br>2         | 250<br>250        | 0.111<br>0.076                     | 1.008<br>1.870   |
| <b>216</b> 02.5                | 2.5              | 250               | 0.058                              | 2.697  |
| 216 3.15                       | 3.15             | 250               | 0.037                              | 6.700  |
| <b>216</b> 004                 | 4                | 250               | 0.025                              | 14.996   |
| <b>216</b> 005                 | 5                | 250               | 0.018                              | 27.460   |
| <b>216</b> 06.3                | 6.3              | 250               | 0.014                              | 56.429   |
| <b>216</b> 008                 | 8*               | 250               | 0.010                              | 64.316   |
| <b>216</b> 010                 | 10*              | 250               | 0.008                              | 154.339  |




### 5 x 20 mm Fast-Acting Fuse 216 Series

(€) (€) (€) (€) (€) (€)

#### Agency Approvals

|              | Agency Ap                        | Ampere Range  |                           |
|--------------|----------------------------------|---|---------------------------|
| PSE          | Certificate No.                  | Cartridge<br>NBK250702-E10480 A & C<br>NBK250702-E10480 E<br>Leaded<br>NBK250702-E10480 B & D<br>NBK250702-E10480 F | 1A – 10A                  |
|              | Certificate No.                  | 2003010207079960<br>2002010207007594  | 50mA – 800mA<br>1A – 6.3A |
| $\odot$      | Certificate No.                  | SU05001-2013  | 1A – 10A                  |
| .••          | Recognised File No.<br>Guide No. | E10480<br>JDYX2   |                           |
| <b>()</b> .  | File No.<br>Acc. Class No.       | 029862<br>LR1422-30   | 50mA – 10A                |
| $\heartsuit$ | Licence No.                      | KM41462   | 1A – 6.3A                 |
| (2)          | File No.                         | 9848103, 9931059<br>304518 & 304555   | 32mA – 6.3A               |
| Œ            |                                  |   | 50mA – 10A                |



\* Ratings above 6.3A have 0.8 mm dia lead

Have 0.6 min ula leau

#### Average Time Current Curves

