

TRF600-150-2 Product Details



TRF600-150-2

TE Part Number: F30347-000

 [Active](#)

 [Add to Part List](#)

PolySwitch Resettable Devices

 [Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Telecom Application
- Family Name = TRF600
- Through Hole Construction
- IH (Room Temperature) = .15 Amps.
- IT (Room Temperature) = .30 Amps.

[View all Features](#) | [Find Similar Products](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)
- ▶ [Request Samples](#)

NEW!

Documentation & Additional Information

Product Drawings:

- [TRF600-150 \(PDF, English\)](#)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- UL Recognized = File No. E74889
- CSA File No. = 78165C
- Comment = Devices are available with 0.5 ohm resistance matching.; Designed for equipment required to meet UL60950 and TIA968; can be used for ITU applications.

Electrical Characteristics:

- [IH \(Room Temperature\) \(Amps.\)](#) = 0.15
- [IT \(Room Temperature\) \(Amps.\)](#) = 0.30
- [Vmax Operating \(V\)](#) = 250
- [Rmin \(Ω\)](#) = 6.00
- [Rmax \(Ω\)](#) = 10.000
- [R1 Max \[Post Trip\] \(Ω\)](#) = 17.00
- [Vmax Interrupt \(V rms\)](#) = 600
- [UL Rated Current \(Amps.\)](#) = 3
- Tripped Power Dissipation (Typical) (W) = 1.00
- R (Typical) (Ω) = 8.00
- UL Rated Voltage (V) = 250

Termination Related Features:

- Construction = Through Hole

Body Related Features:

- Lead Type = Kinked

Contact Related Features:

- Family Name = TRF600

Configuration Related Features:

- Coating = Coated

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- [Operating Temperature \(Max.\) \(°C\)](#) = 85

Operation/Application:

- Application = Telecom

Packaging Related Features:

- Packaging Method = Bulk, Tape & Reel

Other:

- Brand = Raychem