MALLORY Mallory Sonalert Products Inc. Sales Outline Drawing	Part #	PT-2726PQ
Sales Outline Drawing	Revision	В

Specifications:

Resonant Frequency (Hz)
Operating Voltage (Vp-p/max)

Rated Voltage (Vp-p)

Current Consumption (mA/max) Sound Pressure Level (dB/min)

Capacitance (pF)

Operating Temperature (°C) Storage Temperature (°C)

Housing

Lead Pins

Weight (Grams)

Condition by wave soldering (°C)

Condition by hand soldering (°C)

Options

 2500 ± 500

30

5.0

1.5 at Rated Voltage 90 at 10cm at Rated voltage

 $30,000 \pm 30\%$ at 120 Hz

 $-20 \sim +70$

 $-30 \sim +80$

ABS 757 UL94HB plastic resin

(Color: Black)

Tin Plated Brass


4.4

 $245 \pm 5 / 3 \pm 0.5 \text{ sec}$

 350 ± 20 / within 5 sec

For other options contact factory

Dimensions: (units: mm) ROHS Compliant



PT-2726PQ

Direct Drive Transducer Operation:

Direct drive transducer devices do not have any included DC circuitry, so the user must apply a sine or square wave with the appropriate rated frequency. A square wave will typically result in more sound level than a sine wave. The higher the peak-to-peak voltage applied (up to the maximum rated voltage), the higher the resulting sound level.

Frequency Response:

