

HIGH PRECISION DC/DC CONVERTER CONTROL IC

■ GENERAL DESCRIPTION

The NJM2360A is a control circuit containing the primary functions required for DC to DC CONVERTOR.

This device consist of high precision reference, comparator controlled duty cycle oscillator with an active current limit circuit, driver and high current output switch.

This IC was specifically designed to be incorporated in step-up, step-down and inverting applications with a minimum number of external components. This IC is designed to be $\pm 5\%$ output voltage by using precision 1% resistance on external detected resistance.


■ FEATURES

Precision Reference
 Output Switch Current
 Operating Voltage
 1.25V±2%
 1.5A (MAX)
 2.5V* to 40V

• Internal Over Current Limit Circuit

Supply Voltage V⁺ 2.5V* to 40V
 Output Voltage V_{OR} 1.25V to 40V
 Oscillator Frequency f_{OSC} 100Hz to 100kHz
 Package Outline DIP8, DMP8

■ PIN CONFIGURATION



NJM2360AD NJM2360AM

■ PACKAGE OUTLINE






NJM2360AD

NJM2360AM

■ BLOCK DIAGRAM



PIN FUNCTION

 $\mathbf{E}_{\mathbf{S}}$

5. INV_{IN}
6. V⁺
7. S_I
8. C_D

 $\begin{array}{ll} \textbf{3.} & C_T \\ \textbf{4.} & GND \end{array}$

^{*}Ta =25°C. At low temperature, the minimum voltage is 3.0V.

■ ABSOLUTE MAXIMUM RATINGS

 $(T_a = 25^{\circ}C)$

PARAMETER	SYMBOL	RATINGS	UNIT	
Supply Voltage	V ⁺	40	V	
Comparator Input Voltage Range	V_{IR}	-0.3 to 40	V	
Power Dissipation	P_D	(DIP8) 875 (DMP8) 750 (note1)	mW mW	
Switch Current	I _{SW}	1.5	Α	
Operating Temperature Range	T _{opr}	-40 to + 85	℃	
Storage Temperature Range	T _{stg}	-40 to +150	℃	


(note 1) At on PC board

■ ELECTRICAL CHARACTERISTICS

• DC Characteristics (V⁺ = 5V, T_a = 25°C)

PARAMETER	SYMBOL	TEST CONDITION	MIN.	TYP.	MAX.	UNIT
Operating Current	Icc	$5V \le V^{+} \le 40V$, CT = 0.001 μ F S ₁ = V ⁺ , INV _{IN} > V _{th} , E _S = GND	-	2.4	3.5	mA
Oscillator						
Charge Current	I _{chg}	5V ≤ V ⁺ ≤ 40V	20	35	50	μΑ
Discharge Current	Idischg	5V ≤ V ⁺ ≤ 40V	150	200	250	μA
Voltage Swing	V_{OSC}		-	0.5	-	V_{P-P}
Discharge to Charge Current Ratio	I _{dischg} /I _{chg}	$S_I = V^+$	-	6	-	-
Peak Current Sense Voltage	V _{IPK(sense)}	I _{chg} = I _{dischg}	250	300	350	mV
Output Switch (Note 2)						
Saturation Voltage 1	V _{CE(sat)} 1	Darlington Connection (C _S = C _D) I _{SW} = 1.0A	-	1.0	1.3	V
Saturation Voltage 2	V _{CE(sat)} 2	I_{SW} = 1.0A, I_C (driver) = 50mA (Forced β =20)	-	0.5	0.7	V
DC Current Gain	h _{FE}	$I_{SW} = 1.0A, V_{CE} = 5.0V$	35	120	-	-
Collector Off-State Current	$I_{C(off)}$	V _{CE} = 40V	-	10	-	nA
Comparator						
Threshold Voltage	V_{th}		1.225	1.250	1.275	V
Input Bias Current	I _{IB}	V _{IN} = OV	-	40	400	nA

Note 2: Output switch tests are performed under pulsed conditions to minimize power dissipation.



[CAUTION]

The specifications on this databook are only given for information, without any guarantee as regards either mistakes or omissions. The application circuits in this databook are described only to show representative usages of the product and not intended for the guarantee or permission of any right including the industrial rights.