




203 Series Fuse



Description

Fast-Acting and Slo-Blo® Fuse versions of the Flat-Pak Fuse designs are available. Both designs are available in either a gull-wing surface mount package or a DIP configuration for through-hole mounting. These fuse designs feature a 250 VAC rating in a low profile, rectangular package.

Agency Approvals

AGENCY	AGENCY FILE NUMBER	AMPERE RANGE
	E10480	1/4mA - 5A
	LR29862	1/4mA - 5A

Additional Information



Datasheet



Resources





Samples


Electrical Characteristics for Series

% of Ampere Rating	Opening Time
100%	4 hours, Minimum
200%	1 second, Min; 30 seconds Max.

Electrical Specifications by Item

Ampere Rating (A)	Amp Code	Max Voltage Rating (V)	Interrupting Rating	Nominal Cold Resistance (Ohms)	Nominal Melting I ² t (A ² sec)	Agency Approvals	
							
0.25	.250	250	50 amperes @250 VAC	1.36	0.0126	x	x
0.50	.500	250		0.433	0.112	x	x
0.75	.750	250		0.158	0.327	x	x
1.00	001.	250		0.0755	0.328	x	x
1.50	015.	250		0.0390	0.850	x	x
2.00	002.	250		0.0345	1.70	x	x
2.50	02.5	250		0.0237	2.87	x	x
3.00	003.	250		0.0197	4.40	x	x
4.00	004.	250		0.0148	8.75	x	x
5.00	005.	250		0.0124	14.7	x	x

Temperature Derating Curve




Note:

- Derating depicted in this curve is in addition to the standard derating of 25% for continuous operation.

Soldering Parameters

Wave Soldering	260°C, 3 seconds max.
Reflow Soldering	215°C, 30 seconds max.

Dimensions



Packaging

Packaging Option	Packaging Specification	Quantity	Quantity & Packaging Code
------------------	-------------------------	----------	---------------------------


Surface Mount Fuses

Bulk	-	100	HXG
24mm Tape and Reel	EIA 481 (IEC60286, part 3)	500	URG

Through Hole Fuses

Antistatic Magazine	-	100	H
---------------------	---	-----	---

Average Time Current Curves



Product Characteristics

Materials	Body: Thermoplastic Terminations: Tin/Lead Plated Copper
Solderability	MIL-STD-202, Method 208.
Cleaning	Board washable in most common solvents.
Operating Temperature	-55°C to 125°C

Part Numbering System

Surface Mount Fuses:

0203 002. HXG

Series

Amp Code

Refer to Amp Code column of Electrical Characteristics Table

Quantity Code

HXG = 100
URG = 500

Through Hole Fuses:

0203 002. H

Series

Amp Code

Refer to Amp Code column of Electrical Characteristics Table

Quantity Code

H = 100