

DS1488 Quad Line Driver

Check for Samples: [DS1488](#)

FEATURES

- **Current Limited output:** ± 10 mA Typ
- **Power-Off Source Impedance:** 300 Ω Min
- **Simple Slew Rate Control with External Capacitor**
- **Flexible Operating Supply Range**
- **Inputs are TTL/LS Compatible**

DESCRIPTION

The DS1488 is a quad line driver which converts standard TTL input logic levels through one stage of inversion to output levels which meet EIA Standard RS-232D and CCITT Recommendation V.24.

Schematic and Connection Diagrams




Figure 1. 1/4 Circuit




Figure 2. Small-Outline or Dual-In-Line Package (Top View)
SOIC Package, See Package Number D
PDIP Package, See Package Number NFF



These devices have limited built-in ESD protection. The leads should be shorted together or the device placed in conductive foam during storage or handling to prevent electrostatic damage to the MOS gates.



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

All trademarks are the property of their respective owners.

Absolute Maximum Ratings⁽¹⁾⁽²⁾

| | | |
|--|---------------------|-------------------------------|
| Supply Voltage | V ⁺ | +15V |
| | V ⁻ | -15V |
| Input Voltage (V _{IN}) | | -15V ≤ V _{IN} ≤ 7.0V |
| Output Voltage | | ±15V |
| Operating Temperature Range | | 0°C to +75°C |
| Storage Temperature Range | | -65°C to +150°C |
| Maximum Power Dissipation at 25°C ⁽³⁾ | Molded PDIP Package | 1280 mW |
| | SOIC Package | 974 mW |
| Lead Temperature (Soldering, 4 sec.) | | 260°C |

- (1) Absolute Maximum Ratings are those values beyond which the safety of the device cannot be ensured. Except for "Operating Temperature Range" they are not meant to imply that the devices should be operated at these limits. The table of "Electrical Characteristics" provides conditions for actual device operation.
- (2) If Military/Aerospace specified devices are required, please contact the Texas Instruments Sales Office/Distributors for availability and specifications.
- (3) Derate molded PDIP package 10.2 mW/°C above 25°C; derate SOIC package 7.8 mW/°C above 25°C.

Electrical Characteristics⁽¹⁾⁽²⁾V_{CC+} = 9V, V_{CC-} = -9V unless otherwise specified

| Symbol | Parameter | Conditions | Min | Typ | Max | Units |
|------------------|---|--|---|-------|--------|-------|
| I _{IL} | Logical "0" Input Current | V _{IN} = 0V | | -0.8 | -1.3 | mA |
| I _{IH} | Logical "1" Input Current | V _{IN} = +5.0V | | 0.005 | 10.0 | μA |
| V _{OH} | High Level Output Voltage | R _L = 3.0 kΩ, V _{IN} = 0.8V | V ⁺ = 9.0V, V ⁻ = -9.0V | 6.0 | 7.1 | V |
| | | | V ⁺ = 13.2V, V ⁻ = -13.2V | 9.0 | 10.7 | V |
| V _{OL} | Low Level Output Voltage | R _L = 3.0 kΩ, V _{IN} = 1.9V | V ⁺ = 9.0V, V ⁻ = -9.0V | -6.0 | 7.0 | V |
| | | | V ⁺ = 13.2V, V ⁻ = -13.2V | -9.0 | -10.6 | V |
| I _{OS+} | High Level Output Short-Circuit Current | V _{OUT} = 0V, V _{IN} = 0.8V | | -6.0 | -10.0 | mA |
| | Low Level Output Short-Circuit Current | | | 6.0 | 10.0 | mA |
| I _{CC+} | Positive Supply Current (Output Open) | V _{IN} = 1.9V | V ⁺ = 9.0V, V ⁻ = -9.0V | | 11.6 | mA |
| | | | V ⁺ = 12V, V ⁻ = -12V | | 15.7 | mA |
| | | | V ⁺ = 15V, V ⁻ = -15V | | 19.4 | mA |
| | | V _{IN} = 0.8V | V ⁺ = 9.0V, V ⁻ = -9.0V | | 3.4 | mA |
| | | | V ⁺ = 12V, V ⁻ = -12V | | 4.1 | mA |
| | | | V ⁺ = 15V, V ⁻ = -15V | | 9.1 | mA |
| I _{CC-} | Negative Supply Current (Output Open) | V _{IN} = 1.9V | V ⁺ = 9.0V, V ⁻ = -9.0V | | -10.8 | mA |
| | | | V ⁺ = 12V, V ⁻ = -12V | | -14.6 | mA |
| | | | V ⁺ = 15V, V ⁻ = -15V | | -18.3 | mA |
| | | V _{IN} = 0.8V | V ⁺ = 9.0V, V ⁻ = -9.0V | | -0.001 | mA |
| | | | V ⁺ = 12V, V ⁻ = -12V | | -0.001 | mA |
| | | | V ⁺ = 15V, V ⁻ = -15V | | -0.01 | mA |
| P _d | Power Dissipation | V ⁺ = 9.0V, V ⁻ = -9.0V | | 252 | 333 | mW |
| | | V ⁺ = 12V, V ⁻ = -12V | | 444 | 576 | mW |

- (1) Unless otherwise specified min/max limits apply across the 0°C to +75°C temperature range for the DS1488.
- (2) All currents into device pins shown as positive, out of device pins as negative, all voltages referenced to ground unless otherwise noted. All values shown as max or min on absolute value basis.

Switching Characteristics

($V_{CC} = 9V$, $V_{EE} = -9V$, $T_A = 25^\circ C$)

| Symbol | Parameter | Conditions | Min | Typ | Max | Units |
|-----------|------------------------------------|--|-----|-----|-----|-------|
| t_{pd1} | Propagation Delay to a Logical "1" | $R_L = 3.0\text{ k}\Omega$, $C_L = 15\text{ pF}$, $T_A = 25^\circ C$ | | 187 | 350 | ns |
| t_{pd0} | Propagation Delay to a Logical "0" | $R_L = 3.0\text{ k}\Omega$, $C_L = 15\text{ pF}$, $T_A = 25^\circ C$ | | 45 | 175 | ns |
| t_r | Rise Time | $R_L = 3.0\text{ k}\Omega$, $C_L = 15\text{ pF}$, $T_A = 25^\circ C$ | | 63 | 100 | ns |
| t_f | Fall Time | $R_L = 3.0\text{ k}\Omega$, $C_L = 15\text{ pF}$, $T_A = 25^\circ C$ | | 33 | 75 | ns |

Applications

By connecting a capacitor to each driver output the slew rate can be controlled utilizing the output current limiting characteristics of the DS1488. For a set slew rate the appropriate capacitor value may be calculated using the following relationship


$$C = I_{SC} (\Delta T / \Delta V) \quad (1)$$

where C is the required capacitor, I_{SC} is the short circuit current value, and $\Delta V / \Delta T$ is the slew rate.

RS-232C specifies that the output slew rate must not exceed 30V per microsecond. Using the worst case output short circuit current of 12 mA in the above equation, calculations result in a required capacitor of 400 pF connected to each output.

See [Typical Performance Characteristics](#).

Typical Applications



Optional for noise filtering

Figure 3. RS-232C Data Transmission




Figure 4. DTL/TTL-to-MOS Translator




Figure 5. DTL/TTL-to-HTL Translator






Figure 6. DTL/TTL-to-RTL Translator

AC Load Circuit and Switching Time Waveforms



* C_L includes probe and jig capacitance.



t_r and t_f are measured between 10% and 90% of the output waveform.

Typical Performance Characteristics

$T_A = +25^\circ\text{C}$ unless otherwise noted




Figure 7.




Figure 8.




Figure 9.




Figure 10.

REVISION HISTORY

Changes from Revision B (April 2013) to Revision C

Page

- Changed layout of National Data Sheet to TI format [5](#)

IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products (also referred to herein as "components") are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of significant portions of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI components or services with statements different from or beyond the parameters stated by TI for that component or service voids all express and any implied warranties for the associated TI component or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards which anticipate dangerous consequences of failures, monitor failures and their consequences, lessen the likelihood of failures that might cause harm and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed a special agreement specifically governing such use.

Only those TI components which TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components which have **not** been so designated is solely at the Buyer's risk, and that Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.

Products

| | |
|------------------------------|--|
| Audio | www.ti.com/audio |
| Amplifiers | amplifier.ti.com |
| Data Converters | dataconverter.ti.com |
| DLP® Products | www.dlp.com |
| DSP | dsp.ti.com |
| Clocks and Timers | www.ti.com/clocks |
| Interface | interface.ti.com |
| Logic | logic.ti.com |
| Power Mgmt | power.ti.com |
| Microcontrollers | microcontroller.ti.com |
| RFID | www.ti-rfid.com |
| OMAP Applications Processors | www.ti.com/omap |
| Wireless Connectivity | www.ti.com/wirelessconnectivity |

Applications

| | |
|-------------------------------|--|
| Automotive and Transportation | www.ti.com/automotive |
| Communications and Telecom | www.ti.com/communications |
| Computers and Peripherals | www.ti.com/computers |
| Consumer Electronics | www.ti.com/consumer-apps |
| Energy and Lighting | www.ti.com/energy |
| Industrial | www.ti.com/industrial |
| Medical | www.ti.com/medical |
| Security | www.ti.com/security |
| Space, Avionics and Defense | www.ti.com/space-avionics-defense |
| Video and Imaging | www.ti.com/video |

TI E2E Community

e2e.ti.com