


## RoHS

## P6) 2

# 216 Series, 5 x 20 mm, Fast-Acting Fuse





#### **Agency Approvals**

Agency	Agency File Number	Ampere Range
PS	Cartridge Certificates:  1-5A NBK 080205-E10480A 6.3A-10A NBK 250702-E10480E 12.5A NBK 240108-JP1021C 16A NBK 240108-JP1021E Leaded Certificates: 1-5A NBK 080205-E10480B 6.3A-10A NBK 250702-E10480F 12.5A NBK 240108-JP1021D 16A NBK 240108-JP1021F	1A – 16A
<b>@</b>	Certificates: 2003010207079960	50mA – 6.3A
	Certificates: SU05001-2013	1A – 10A
<b>7U</b>	Recognised File: E10480 Guide: JDYX2	50mA – 10A
<b>(</b>	File: 029862 Acc. Class: LR1422-30	12.5A, 16A
	File: 1027156 8117 45 1117973 1020822 1027014	50mA – 125mA 160mA – 800mA 1A – 6.3A 8A – 10A 16A
DVE	License: 40013834	50mA – 6.3A *8A, *10A
VDE	License: 40016442	*12.5A
$\nabla$	License: KM41462	1A – 6.3A
Œ		50mA – 16A

<sup>\*</sup>Approval for Cartridge versions only

#### Description

5x20mm fast-acting ceramic body cartridge fuse designed to IEC specification.

#### **Features**

- Designed to International (IEC) Standards for use globally
- Meets the IEC 60127-2, sheet 1 specification
- for fast-acting fuses
- Available in cartridge and axial lead form
- RoHS compliant and lead-free

#### **Applications**

Used as supplementary protection in appliance or utilization equipment to provide individual protection for components or internal circuits.

#### **Electrical Characteristics for Series**

% of Ampere Rating	Ampere Rating	OpeningTime				
	50mA – 4A	60 minutes, Minimum				
150%	5A – 6.3A	60 minutes, Minimum				
	8A – 16A	30 minutes, Minimum				
	50mA – 4A	30 minutes, Maximum				
210%	5A – 6.3A	30 minutes, Maximum				
	8A – 16A	30 minutes, Maximum				
	50mA – 4A	0.01 sec, Min.; 2 sec. Max.				
275%	5A – 6.3A	0.01 sec, Min.; 3 sec. Max.				
	8A – 16A	0.04 sec., Min.; 20 sec. Max.				
	50mA – 4A	.003 sec., Min.; 0.3 sec. Max.				
400%	5A – 6.3A	.003 sec., Min.; 0.3 sec. Max.				
	8A – 16A	.01 sec, Min.; 1.0 sec. Max.				
	50mA – 4A	.02 seconds, Maximum				
1000%	5A – 6.3A	.02 seconds, Maximum				
	8A – 16A	.03 sec.onds, Maximum				

# Axial Lead & Cartridge Fuses 5×20 mm > Fast-Acting > 216 Series




#### **Electrical Characteristics Specifications by Item**

						Nominal	Nominal		Agency Approvals								
Amp Code	Amp Rating (A)	Voltage Rating (V)	Interrupting Rating	Nominal Cold Resistance (Ohms)	Nominal Melting I²t (A² sec)	g Bated at Rated	ኞ	<b>S</b>	<b>((()</b>	<i>91</i>	<b>(3P</b> .	$\bigcirc$	Œ	<u></u>	<b>√</b> DE	PS E	
.050	0.05	250		15.9000	0.00019	10000	1.6			Х	Х	Х	Х	Х	Х		
.063	0.063	250		10.4500	0.00054	8800	1.6			х	Х	Х	Х	Х	Х		
.080	0.08	250		7.8850	0.00084	7600	1.6			x	X	X	X	X	Х		
.100	0.1	250		5.7925	0.00450	7000	1.6			X	Х	X	Х	X	Х		
.125	0.125	250		3.6750	0.00546	5000	1.6			Х	X	Х	X	Х	Х		
.160	0.16	250		5.3490	0.00576	4300	1.6			X	Х	X	Х	X	Х		
.200	0.2	250		3.3500	0.00439	3500	1.6			Х	X	Х	X	Х	Х		
.250	0.25	250		2.3500	0.00891	2800	2.5			X	Х	X	Х	X	Х		
.315	0.315	250		1.8500	0.01000	2500	2.5			Х	X	Х	X	Х	Х		
.500	0.5	250		0.8660	0.16500	1800	2.5			Х	Х	Х	Х	Х	Х		
.630	0.63	250		0.4650	0.17500	1500	2.5			Х	х	Х	х	Х	Х		
.800	0.8	250	1500A@ 250Vac	0.2950	0.28500	1200	2.5			Х	X	Х	X	Х	Х		
001.	1	250	250 vac	0.2370	0.18000	1000	2.5	Х	Х	X	Х	Х	Х	X	Х		X
1.25	1.25	250		0.1530	0.48000	800	4	Х	Х	х	X	Х	X	Х	Х		Х
01.6	1.6	250		0.1112	1.00500	600	4	Х	Х	Х	X	Х	X	Х	Х		Х
002.	2	250		0.0764	1.87000	500	4	Х	Х	Х	х	Х	х	Х	Х		Х
02.5	2.5	250		0.0584	2.69500	400	4	Х	Х	Х	X	Х	X	Х	Х		Х
3.15	3.15	250		0.0368	6.70000	350	4	Х	Х	Х	X	Х	X	Х	Х		Х
004.	4	250		0.0247	14.99500	300	4	Х	Х	Х	X	Х	X	Х	Х		X
005.	5	250		0.0183	27.46000	250	4	Х	Х	Х	X	Х	X	Х	Х		Х
06.3	6.3	250		0.0137	56.43000	200	4	Х	Х	х	X	X	X	Х	Х		X
008.	8	250		0.0123	64.31500	200	4		Х		Х	Х	Х	Х	x*		Х
010.	10	250		0.0079	154.34000	200	4		Х		Х	Х	Х	Х	x*		Х
12.5	12.5	250		0.0057	235.00000	200	4				х	Х		Х		х*	Х
016.	16	250	750A@ 250Vac	0.0040	462.50000	200	4.5				х	х	х	х			Х


<sup>\*</sup> Approval for cartidge versions only.

I2t test at 10x rated current


## **Temperature Rerating Curve**



## **Average Time Current Curves**



## **Soldering Parameters - Wave Soldering**



#### **Recommended Process Parameters:**

Wave Parameter	Lead-Free Recommendation			
Preheat:				
(Depends on Flux Activation Temperature)	(Typical Industry Recommendation)			
Temperature Minimum:	100° C			
Temperature Maximum:	150° C			
Preheat Time:	60-180 seconds			
Solder Pot Temperature:	260° C Maximum			
Solder DwellTime:	2-5 seconds			

#### **Recommended Hand-Solder Parameters:**

Solder Iron Temperature:  $350^{\circ}$  C +/-  $5^{\circ}$ C

Heating Time: 5 seconds max.

Note: These devices are not recommended for IR or Convection Reflow process.

#### **Product Characteristics**


Material	Body: Ceramic Cap: Nickel–plated brass Leads: Tin–plated Copper Filler (160mA-16A): Sand		
Terminal Strength	MIL-STD-202G, Method 211A, Test Condition A		
Solderability	Reference IEC 60127 Second Edition 2003-01 Annex A		
Product Marking	Cap 1: Brand logo, current and voLage rating Cap 2: Agency approval markings		
Packaging	Available in Bulk (M=1000 pcs/pkg) or on Tape/Reel (MRET1=1000 pcs/reel)		

Operating Temperature	−55°C to +125°C	
Thermal Shock	MIL-STD-202G, Method 107G, Test Condition B: (5 cycles –65°C to +125°C)	
Vibration	MIL-STD-202G, Method 201A	
Humidity	MIL-STD-202G, Method 103B, Test Condition A. high RH (95%) and elevated temperature (40°C) for 240 hours.	
Salt Spray	MIL-STD-202G, Method 101D, Test Condition B	


# Axial Lead & Cartridge Fuses 5×20 mm > Fast-Acting > 216 Series



#### **Dimensions**



## **Part Numbering System**



## \*\* Ratings above 6.3A have 0.8 mm diameter lead

## **Packaging**

Packaging Option	Packaging Specification	Quantity	Quantity & Packaging Code	Taping Width		
216 Series						
Bulk	N/A	1000	MX	N/A		
Bulk	N/A	1000	MXE	N/A		
Reel and Tape	EIA 296-E	1000	MRET1	T1=53mm (2.087")		
Bulk	N/A	1000	MXG	N/A		
Bulk	N/A	1000	MXB	N/A		
Bulk	N/A	100	HX	N/A		