



NUMBER OF TERMINALS	UNITS	
		5
ELECTRICAL RATING		
Nominal Voltage Rating:	Volts	
Nominal Current Rating:	Amps	300
		15
DIELECTRIC STRENGTH		
Output to Adjacent output Terminals:	V rms	
Output to Input Terminals:	V rms	2500
Terminals to Rail Chassis:	V rms	2500
CONSTRUCTION		
Protection Category (Finger Safe):	IEC	IP20
Internal Metal Tracks:		Copper Alloy, Zinc Plated
Screws Terminals:		Steel, Zinc Plated
Screw Style and Size:	mm	Combination Head, M3.5 x 0.06 x 6.35
Screw Terminal Torque Maximum:	Lb-in / Nm	8 / 0.90
TEMPERATURE		
Operating, Lower:	°C	-40
Operating, Upper:	°C	+80
MISCELLANEOUS		
Chassis Mount Screw Torque:	Lb-in / Nm	7 - 8 / 0.79 - 0.90
Flammability Rating:		94V-0
Wire Size:	AWG/mm2	20 - 12 / 0.5 - 3.0
Body Color:		Light gray
DIN Locking Clip Color:		Red
Weight:	grams	32



PHONE: (843) 393-5778 FAX: (843) 393-4123 EMAIL: inf@magnecraft.com



STANDARD PART NUMBER	DESCRIPTION
70 - 781D -1	5 PIN SOCKET, FINGER SAFE, DIN / PANEL MOUNT WITH SCREW TERMINALS & CLAMPING PLATES.

9/04