



3M Worldwide : United States : Utilities & Telecommunication

Return to Solutions for Electrical

Product Catalog for Solutions for Electrical

- 3M™ Diagnostic and Detection Products
- 3M™ Fire Protection Products
- 3M™ Safety and Protection Products
- Aerosols, Sprays and Coatings
- Insulating, Jacketing and Repair
- Low Voltage Splicing (0-1000V)
- Medium Voltage Splicing and Terminating (5-46kV)
- Moisture Sealing and Corrosion Protection
- **Wire Connecting**
- Wire Management

Other Tools

- Online Product Catalog
- Download Literature
- MSDS Search
- Training
- Warranty Information
- Where to Buy

[Product Catalog for Solutions for Electrical](#) > [Wire Connecting](#) > [3M™ Wire Connectors](#) > [3M™ Insulation Displacement Connectors and Tools](#) > [3M™ Scotchlok™ IDC Connectors for Electrical Applications](#) > [3M™ Scotchlok™ 953 Electrical IDC, Female T-Tap Quick Slide](#) >

[Printer-friendly format](#) **3M™ Scotchlok™ T-Tap Nylon Insulated Self-Stripping Female QuickSlide Disconnect 953K, 12 AWG**



This female disconnect accepts a 12 AWG and has case quantities of 1000.

[\[click to enlarge\]](#)

3M Id : 80-0040-0053-7

GTIN(UPC/EAN) : 0 00 54007 12315 6

Additional Information

Use to electrically tap into a wire in mid-span without cutting or stripping the wire. Connector then mates with a .250 inch (6.35 millimeter) male tab, making a reusable quick-connect wiring termination. T-tap disconnect.

Maximum insulation O.D.diameter of 0.150 inches (3,81 mm) and a operating temperature of 221°F (105°C). The suggested application tool for this connector is the E-9BM

[Full Text . . .](#)

Learn More . . .

[Packaging Data](#)

[901,951,952,953 Connection Type - Illustration/Line Art-\(TIFF\)](#)

Characteristics

Primary Trademark Name	Scotchlok
-------------------------------	-----------