# **Complementary Plastic Power Transistors**

# NPN/PNP Silicon DPAK For Surface Mount Applications

Designed for low voltage, low-power, high-gain audio amplifier applications.

#### **Features**

- High DC Current Gain
- Lead Formed for Surface Mount Applications in Plastic Sleeves (No Suffix)
- Low Collector-Emitter Saturation Voltage
- High Current-Gain Bandwidth Product
- Annular Construction for Low Leakage
- Epoxy Meets UL 94 V-0 @ 0.125 in
- NJV Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC-Q101 Qualified and PPAP Capable
- These Devices are Pb-Free and are RoHS Compliant

# **MAXIMUM RATINGS**

Rating	Symbol	Max	Unit
Collector-Base Voltage	$V_{CB}$	40	Vdc
Collector-Emitter Voltage	V <sub>CEO</sub>	25	Vdc
Emitter-Base Voltage	V <sub>EB</sub>	8.0	Vdc
Collector Current – Continuous	I <sub>C</sub>	5.0	Adc
Collector Current – Peak	I <sub>CM</sub>	10	Adc
Base Current	Ι <sub>Β</sub>	1.0	Adc
Total Power Dissipation @ T <sub>C</sub> = 25°C Derate above 25°C	P <sub>D</sub>	12.5 0.1	W W/°C
Total Power Dissipation (Note 1)  @ T <sub>A</sub> = 25°C Derate above 25°C	P <sub>D</sub>	1.4 0.011	W W/°C
Operating and Storage Junction Temperature Range	T <sub>J</sub> , T <sub>stg</sub>	-65 to +150	°C
ESD – Human Body Model	HBM	3B	V
ESD – Machine Model	MM	С	V

Stresses exceeding Maximum Ratings may damage the device. Maximum Ratings are stress ratings only. Functional operation above the Recommended Operating Conditions is not implied. Extended exposure to stresses above the Recommended Operating Conditions may affect device reliability.


 These ratings are applicable when surface mounted on the minimum pad sizes recommended.



# ON Semiconductor®

http://onsemi.com

# SILICON POWER TRANSISTORS 5 AMPERES 25 VOLTS, 12.5 WATTS





#### **MARKING DIAGRAM**



A = Assembly Location

Y = Year

WW = Work Week

x = 1 or 0

G = Pb-Free Package

#### **ORDERING INFORMATION**

See detailed ordering and shipping information in the package dimensions section on page 6 of this data sheet.

# THERMAL CHARACTERISTICS


Characteristic	Symbol	Max	Unit
Thermal Resistance, Junction-to-Case	$R_{\theta JC}$	10	°C/W
Thermal Resistance, Junction-to-Ambient (Note 2)	$R_{ heta JA}$	89.3	°C/W

<sup>2.</sup> These ratings are applicable when surface mounted on the minimum pad sizes recommended.

# **ELECTRICAL CHARACTERISTICS** (T<sub>C</sub> = 25°C unless otherwise noted)

Characteristic	Symbol	Min	Max	Unit
OFF CHARACTERISTICS	-		•	•
Collector–Emitter Sustaining Voltage (Note 3) (I <sub>C</sub> = 10 mAdc, I <sub>B</sub> = 0)	V <sub>CEO(sus)</sub>	25	_	Vdc
Collector Cutoff Current $(V_{CB} = 40 \text{ Vdc}, I_E = 0)$ $(V_{CB} = 40 \text{ Vdc}, I_E = 0, T_J = 125^{\circ}\text{C})$	V <sub>CBO</sub>	- -	100 100	nAdc μAdc
Emitter Cutoff Current (V <sub>BE</sub> = 8 Vdc, I <sub>C</sub> = 0)	V <sub>EBO</sub>	-	100	nAdc
ON CHARACTERISTICS			•	•
C Current Gain (Note 3), $ \begin{aligned} &(I_C=500 \text{ mAdc}, V_{CE}=1 \text{ Vdc}) \\ &(I_C=2 \text{ Adc}, V_{CE}=1 \text{ Vdc}) \\ &(I_C=5 \text{ Adc}, V_{CE}=2 \text{ Vdc}) \end{aligned} $	h <sub>FE</sub>	70 45 10	- 180 -	-
	V <sub>CE(sat)</sub>	- - -	0.3 0.75 1.8	Vdc
Base–Emitter Saturation Voltage (Note 3) (I <sub>C</sub> = 5 Adc, I <sub>B</sub> = 1 Adc)	V <sub>BE(sat)</sub>	-	2.5	Vdc
Base–Emitter On Voltage (Note 3) (I <sub>C</sub> = 2 Adc, V <sub>CE</sub> = 1 Vdc)	V <sub>BE(on)</sub>	-	1.6	Vdc
DYNAMIC CHARACTERISTICS				
Current–Gain – Bandwidth Product (Note 4) (I <sub>C</sub> = 100 mAdc, V <sub>CE</sub> = 10 Vdc, f <sub>test</sub> = 10 MHz)	f <sub>T</sub>	65	_	MHz
Output Capacitance ( $V_{CB} = 10 \text{ Vdc}$ , $I_E = 0$ , $f = 0.1 \text{ MHz}$ ) MJD200 MJD210, NJVMJD210T4G	C <sub>ob</sub>	- -	80 120	pF

<sup>3.</sup> Pulse Test: Pulse Width = 300  $\mu$ s, Duty Cycle  $\approx$  2%. 4. f<sub>T</sub> =  $|h_{fe}| \bullet f_{test}$ .




R<sub>B</sub> and R<sub>C</sub> VARIED TO OBTAIN DESIRED CURRENT LEVELS

D<sub>1</sub> MUST BE FAST RECOVERY TYPE, e.g.: 1N5825 USED ABOVE I<sub>B</sub>  $\approx$  100 mA MSD6100 USED BELOW I<sub>B</sub>  $\approx$  100 mA

FOR PNP TEST CIRCUIT, REVERSE ALL POLARITIES

Figure 1. Power Derating

Figure 2. Switching Time Test Circuit






Figure 3. Turn-On Time

Figure 4. Turn-Off Time




Figure 5. DC Current Gain





Figure 6. "On" Voltage



**Figure 7. Temperature Coefficients** 




Figure 8. Thermal Response




Figure 9. Active Region Safe Operating Area

There are two limitations on the power handling ability of a transistor: average junction temperature and second breakdown. Safe operating area curves indicate  $I_C - V_{CE}$  limits of the transistor that must be observed for reliable operation; i.e., the transistor must not be subjected to greater dissipation than the curves indicate.

The data of Figure 9 is based on  $T_{J(pk)} = 150^{\circ}C$ ;  $T_C$  is variable depending on conditions. Second breakdown pulse limits are valid for duty cycles to 10% provided  $T_{J(pk)} \le 150^{\circ}C$ .  $T_{J(pk)}$  may be calculated from the data in Figure 8. At high case temperatures, thermal limitations will reduce the power that can be handled to values less than the limitations imposed by second breakdown.




Figure 10. Capacitance

# **ORDERING INFORMATION**


Device	Package Type	Shipping <sup>†</sup>
MJD200G	DPAK (Pb-Free)	75 Units / Rail
MJD200RLG	DPAK (Pb-Free)	1,800 / Tape & Reel
MJD200T4G	DPAK (Pb-Free)	2,500 / Tape & Reel
MJD210G	DPAK (Pb-Free)	75 Units / Rail
MJD210RLG	DPAK (Pb-Free)	1,800 / Tape & Reel
MJD210T4G	DPAK (Pb-Free)	2,500 / Tape & Reel
NJVMJD210T4G*	DPAK (Pb-Free)	2,500 / Tape & Reel

<sup>†</sup>For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.
\*NJV Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC–Q101 Qualified and PPAP

Capable

#### PACKAGE DIMENSIONS

# DPAK CASE 369C ISSUE D



#### NOTES:

- 1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994.
- 2. CONTROLLING DIMENSION: INCHES.
- THERMAL PAD CONTOUR OPTIONAL WITHIN DI-MENSIONS b3, L3 and Z.
- MENSIONS D. AND E DO NOT INCLUDE MOLD FLASH, PROTRUSIONS, OR BURRS. MOLD FLASH, PROTRUSIONS, OR GATE BURRS SHALL NOT EXCEED 0.006 INCHES PER SIDE.
- DIMENSIONS D AND E ARE DETERMINED AT THE OUTERMOST EXTREMES OF THE PLASTIC BODY.
- DATUMS A AND B ARE DETERMINED AT DATUM PLANE H

	INCHES		MILLIMETERS	
DIM	MIN	MAX	MIN	MAX
Α	0.086	0.094	2.18	2.38
A1	0.000	0.005	0.00	0.13
b	0.025	0.035	0.63	0.89
b2	0.030	0.045	0.76	1.14
b3	0.180	0.215	4.57	5.46
С	0.018	0.024	0.46	0.61
c2	0.018	0.024	0.46	0.61
D	0.235	0.245	5.97	6.22
Е	0.250	0.265	6.35	6.73
е	0.090 BSC		2.29 BSC	
Н	0.370	0.410	9.40	10.41
L	0.055	0.070	1.40	1.78
L1	0.108 REF		2.74 REF	
L2	0.020 BSC		0.51 BSC	
L3	0.035	0.050	0.89	1.27
L4		0.040		1.01
Z	0.155		3.93	

3. EMITTER

4 COLLECTOR

# **SOLDERING FOOTPRINT\***

# STYLE 1: PIN 1. BASE 2. COLLECTOR 6.20 3.0 0.244 0.118 2.58 0.101 5.80 1.6 6.172 0.228 0.063 0.243

(mm inches) SCALE 3:1

\*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

ON Semiconductor and (III) are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of SCILLC's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent–Marking, pdf. SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

# **PUBLICATION ORDERING INFORMATION**

#### LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor P.O. Box 5163, Denver, Colorado 80217 USA

**Phone**: 303–675–2175 or 800–344–3860 Toll Free USA/Canada **Fax**: 303–675–2176 or 800–344–3867 Toll Free USA/Canada Email: orderlit@onsemi.com

N. American Technical Support: 800-282-9855 Toll Free USA/Canada

Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910

Japan Customer Focus Center Phone: 81–3–5817–1050

ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative