



See full Datasheet below...



masterelectronics.com & onlinecomponents.com are **authorized** e-commerce distributors of electronic components.



## 350W Single Output Switching Power Supply

## NES-350 series



Features :

- AC input range selectable by switch
- Protections: Short circuit / Overload / Over voltage/ Over temperature
- Forced air cooling by built-in DC fan
- Withstand 300vac surge input for 5 second
- Built-in cooling Fan ON-OFF control
- Built-in constant current limiting circuit
- 100% full load burn-in test
- LED indicator for power on
- Fixed switching frequency at 90KHz
- Low cost, high reliability
- 2 years warranty

S	PI	EC	IF	IC	AT	10	Ν
---	----	----	----	----	----	----	---

MODEL		NES-350-3.3	NES-350-5	NES-350-7.5	NES-350-12	NES-350-15	NES-350-24	NES-350-27	NES-350-36	NES-350-48	
OUTPUT	DC VOLTAGE	3.3V	5V	7.5V	12V	15V	24V	27V	36V	48V	
	RATED CURRENT	60A	60A	46A	29A	23.2A	14.6A	13A	9.7A	7.3A	
	CURRENT RANGE	0~60A	0~60A	0~46A	0~29A	0~23.2A	0~14.6A	0~13A	0~9.7A	0~7.3A	
	RATED POWER	198W	300W	345W	348W	348W	350.4W	351W	349.2W	350.4W	
	RIPPLE & NOISE (max.) Note.2	150mVp-p	150mVp-p	150mVp-p	150mVp-p	150mVp-p	150mVp-p	200mVp-p	240mVp-p	240mVp-p	
	VOLTAGE ADJ. RANGE	2.97 ~ 3.7V	4.5 ~ 5.6V	6~9V	10~13.5V	13.5 ~ 18V	20~26.4V	26~32V	32~40V	41~56V	
	VOLTAGE TOLERANCE Note.3	+3%,-4.5%	±3.0%	±2.0%	±1.5%	±1.0%	±1.0%	±1.0%	±1.0%	±1.0%	
	LINE REGULATION	±0.5%	±0.5%	±0.5%	±0.5%	±0.5%	±0.5%	±0.5%	±0.5%	±0.5%	
	LOAD REGULATION	±2.5%	±2.0%	±2.0%	±1.0%	±0.5%	±0.5%	±0.5%	±0.5%	±0.5%	
	SETUP, RISE TIME	1000ms, 50ms/230VAC 1000ms,50ms/115VAC at full load									
	HOLD UP TIME (Typ.) 20ms/230VAC 16ms/115VAC at full load										
INPUT	VOLTAGE RANGE Note.4	90 ~ 132VAC	90 ~ 132VAC / 180 ~ 264VAC by switch 254 ~ 370VDC								
	FREQUENCY RANGE										
	EFFICIENCY (Typ.)	74%	78%	80%	83%	84%	87%	88%	87.5%	87.5%	
	AC CURRENT (Typ.)	7A/115VAC	4A/230VA			0170	01.10	0070			
	INRUSH CURRENT (Typ.)	40A/115VAC 60A/230VAC 60A/230VAC									
	LEAKAGE CURRENT	<3.5mA/240VAC									
PROTECTION	OVER LOAD	105 ~ 135% rated output power									
		Protection type : Constant current limiting, recovers automatically after fault condition is removed									
	OVER VOLTAGE	3.8~4.6V	5.75~7.5V	9.4 ~ 11.25V		18~21V	27.6 ~ 32.4V	33.7 ~ 39.2V	41.4~46.8V	57.6~67.2	
				•	e-power on to re						
	OVER TEMPERATURE	90°C ±5°C (3.3~7.5V); 85°C ±5°C (12~15V); 80°C ±5°C (24V);75°C ±5°C (27~48V) (TSW1) Detect on case									
		Protection type : Shut down O/P voltage, recovers automatically after temperature goes down									
FUNCTION	FAN ON/OFF CONTROL(Typ.)	$\label{eq:RTH2} \ensuremath{RTH2} \geqq 50^\circ \ensuremath{\mathbb{C}}\ \ensuremath{FAN ON}\ \ensuremath{\leqslant} \ensuremath{\leqslant} \ensuremath{SAN OFF}\ \ensuremath{(3.3\mbox{-}7.5\mbox{V})}$									
FUNCTION		$ R H2 \ge 55 \ C \ FAN \ ON, \ \le 50 \ C \ FAN \ OFF \ (12 \sim 48 \forall)$									
	WORKING TEMP.	-20 ~ +60 $^\circ \rm C$ (Refer to output load derating curve)									
	WORKING HUMIDITY	20 ~ 90% RH non-condensing									
ENVIRONMENT	STORAGE TEMP., HUMIDITY	-20 ~ +85°C , 10 ~ 95% RH									
	TEMP. COEFFICIENT	±0.03%/°C (0~50°C)									
	VIBRATION	10 ~ 500Hz, 3G 10min./1cycle, 60min. each along X, Y, Z axes									
	SAFETY STANDARDS	UL60950-1 approved									
SAFETY	WITHSTAND VOLTAGE	I/P-O/P:3KVA	C I/P-FG:2	KVAC O/P-F	G:0.5KVAC						
	ISOLATION RESISTANCE	I/P-O/P, I/P-FG, O/P-FG:100M Ohms/500VDC / 25°C/ 70% RH									
OTHERS	MTBF	234.3K hrs min. MIL-HDBK-217F (25℃)									
	DIMENSION	215*115*50mm (L*W*H)									
	PACKING	1.07Kg; 12pc	s/13.5Kg/0.92	CUFT							
NOTE	<ol> <li>2. Ripple &amp; noise are mease</li> <li>3. Tolerance : includes set</li> <li>4. Please connect positive</li> </ol>	specially mentioned are measured at 230VAC input, rated load and 25℃ of ambient temperature. neasured at 20MHz of bandwidth by using a 12" twisted pair-wire terminated with a 0.1uf & 47uf parallel capacitor. s set up tolerance, line regulation and load regulation. itive pole of input voltage with mark "L" of terminal block, connect negative pole of input voltage minal block, using DC voltage for input voltage.									

File Name:NES-350-SPEC 2013-08-19



## NES-350 series



