Silicon Hot-Carrier Diodes

SCHOTTKY Barrier Diodes

These devices are designed primarily for high-efficiency UHF and VHF detector applications. They are readily adaptable to many other fast switching RF and digital applications. They are supplied in an inexpensive plastic package for low-cost, high-volume consumer and industrial/commercial requirements. They are also available in a Surface Mount package.

Features

- Extremely Low Minority Carrier Lifetime 15 ps (Typ)
- Very Low Capacitance 1.5 pF (Max) @ $V_R = 15 \text{ V}$
- Low Reverse Leakage I_R = 13 nAdc (Typ) MBD301, MMBD301
- These Devices are Pb-Free, Halogen Free/BFR Free and are RoHS Compliant

MAXIMUM RATINGS

		MBD301	MMBD301LT1	
Rating	Symbol	Value		Unit
Reverse Voltage	V _R	30		V
Total Device Dissipation @ T _A = 25°C Derate above 25°C	P _F	280 2.8	200 2.0	mW mW/°C
Operating Junction Temperature Range	TJ	-55 to +125		°C
Storage Temperature Range	T _{stg}	-55 to +150		°C

Stresses exceeding Maximum Ratings may damage the device. Maximum Ratings are stress ratings only. Functional operation above the Recommended Operating Conditions is not implied. Extended exposure to stresses above the Recommended Operating Conditions may affect device reliability.



ON Semiconductor®

http://onsemi.com


30 VOLTS SILICON HOT-CARRIER DETECTOR AND SWITCHING DIODES



MARKING DIAGRAM



TO-92 (TO-226AC) CASE 182 STYLE 1





MMBD301LT1

MARKING DIAGRAM



1

SOT-23 (TO-236) CASE 318 STYLE 8



M = Date Code= Pb-Free Package

(Note: Microdot may be in either location)



ORDERING INFORMATION

See detailed ordering and shipping information in the package dimensions section on page 2 of this data sheet.

ELECTRICAL CHARACTERISTICS ($T_A = 25^{\circ}C$ unless otherwise noted)

Characteristic	Symbol	Min	Тур	Max	Unit
Reverse Breakdown Voltage (I _R = 10 μA)	V _{(BR)R}	30	-	-	V
Total Capacitance (V _R = 15 V, f = 1.0 MHz) Figure 1	C _T	-	0.9	1.5	pF
Reverse Leakage (V _R = 25 V) Figure 3	I _R	-	13	200	nAdc
Forward Voltage (I _F = 1.0 mAdc) Figure 4	V _F	-	0.38	0.45	Vdc
Forward Voltage (I _F = 10 mAdc) Figure 4	V _F	-	0.52	0.6	Vdc

ORDERING INFORMATION

Device	Package	Shipping [†]		
MBD301G	TO-92 (Pb-Free)	5000 Units / Bulk		
MMBD301LT1G	SOT-23 (Pb-Free)	3000 / Tape & Reel		
MMBD301LT3G	SOT-23 (Pb-Free)	10,000 / Tape & Reel		

[†]For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

TYPICAL ELECTRICAL CHARACTERISTICS




Figure 1. Total Capacitance

Figure 2. Minority Carrier Lifetime




Figure 3. Reverse Leakage

Figure 4. Forward Voltage





Figure 5. Krakauer Method of Measuring Lifetime

PACKAGE DIMENSIONS

TO-92 (TO-226AC) CASE 182-06

ISSUE L





SECTION X-X


- NOTES:
 1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
 2. CONTROLLING DIMENSION: INCH.
 3. CONTOUR OF PACKAGE BEYOND ZONE R IS UNCONTROLLED.
 4. LEAD DIMENSION IS UNCONTROLLED IN P AND BEYOND DIMENSION K MINIMUM.

	INCHES		MILLIMETERS		
DIM	MIN	MAX	MIN	MAX	
Α	0.175	0.205	4.45	5.21	
В	0.170	0.210	4.32	5.33	
С	0.125	0.165	3.18	4.19	
D	0.016	0.021	0.407	0.533	
G	0.050 BSC		1.27 BSC		
Н	0.100 BSC		2.54 BSC		
J	0.014	0.016	0.36	0.41	
K	0.500		12.70		
L	0.250		6.35		
N	0.080	0.105	2.03	2.66	
P		0.050		1.27	
R	0.115		2.93		
٧	0.135		3.43		

STYLE 1: PIN 1. ANODE 2. CATHODE

PACKAGE DIMENSIONS

SOT-23 (TO-236) CASE 318-08 ISSUE AN



NOTES


- 1. DIMENSIONING AND TOLERANCING PER ANSI
- Y14.5M, 1982.
- 2. CONTROLLING DIMENSION: INCH.
- 3. MAXIMUM LEAD THICKNESS INCLUDES LEAD FINISH THICKNESS. MINIMUM LEAD THICKNESS IS THE MINIMUM THICKNESS OF BASE MATERIAL.
- 318–01 THRU -07 AND -09 OBSOLETE, NEW STANDARD 318-08.

	MILLIMETERS			INCHES		
DIM	MIN	NOM	MAX	MIN	NOM	MAX
Α	0.89	1.00	1.11	0.035	0.040	0.044
A1	0.01	0.06	0.10	0.001	0.002	0.004
b	0.37	0.44	0.50	0.015	0.018	0.020
С	0.09	0.13	0.18	0.003	0.005	0.007
D	2.80	2.90	3.04	0.110	0.114	0.120
E	1.20	1.30	1.40	0.047	0.051	0.055
е	1.78	1.90	2.04	0.070	0.075	0.081
L	0.10	0.20	0.30	0.004	0.008	0.012
L1	0.35	0.54	0.69	0.014	0.021	0.029
HE	2.10	2.40	2.64	0.083	0.094	0.104

STYLE 8:

- PIN 1. ANODE
 - 2. NO CONNECTION
 - 3. CATHODE

SOLDERING FOOTPRINT*



*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

ON Semiconductor and IIII are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and exasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor
P.O. Box 5163, Denver, Colorado 80217 USA
Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada
Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada

Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800–282–9855 Toll Free USA/Canada

Furnoe Middle Fast and Africa Technical Support:

Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910

Japan Customer Focus Center Phone: 81–3–5773–3850 ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your loca Sales Representative