


Search Results

- Evaluate
 - Approvals
 - PDFFDA Complian
 - FAQ's
 - Product Bulletins
 - PDFMetal Detect..
- Design a Solution
 - Catalog Cut Sheet
 - PDFPLT1MC86 Pr
 - Part Drawings
 - PDFPan-Ty Metal..
- How to Buy
 - Bill of Material
 - Favorite Products List
 - Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click  to remove) Search Tips


 Text Search: 'PLT1M-C186'

Your search criteria matched only one product, shown below

PLT1M-C186



- Metal impregnated material allows identification by metal detectors or x -ray inspection to meet food, beverage and pharmaceutical safety standards by helping to reduce product contamination
- One-piece design with locking wedge provides low thread force and reliable installation to improve productivity and reduce operator fatigue
- Distinct blue color per common industry practices provides easy identification on conveyor belts and in finished products, reducing waste due to product contamination
- Excellent chemical resistance for food and pharmaceutical processing equipment manufacturing applications
- For use in processing and packaging areas where aggressive acid and alkaline chemicals are used to clean the equipment
- For indoor use

Part Number	PLT1MC186
RoHS Compliancy Status	Compliant
Part Description	Cable Tie, 3.9"L (100mm), Metal Detectable Polypropylene, Miniature cross section, Dark Blue
Product Type	Cable Ties
Material	Metal Impregnated Polypropylene
Color	Dark Blue
CSA Certified	No
UL Listed (File #E56854)	No
UL Recognized (File #E56854)	No
Length (In.)	3.9
Length (mm)	100
Width (In.)	0.098
Width (mm)	2.5
CE Compliant	No
Cross Section	Miniature
Head Height (In.)	0.186
Head Height (mm)	4.8
Head Width (In.)	0.188
Head Width (mm)	4.8
Locking Style	Locking
Material Flammability Rating	HB
Max. Bundle Diameter (In.)	0.87
Max. Bundle Diameter (mm)	22
Max. Continuous Use Temperature	239°F (115°C)
Min. Bundle Diameter (In.)	0.13
Min. Bundle Diameter (mm)	3.3
Min. Loop Tensile Strength (Lbs.)	15
Min. Loop Tensile Strength (N)	67
PlenumRated	No
Pricing Description	Cable Tie, 3.9"L (100mm), Miniature, Metal Detectable Polypropylene, Dark Blue
Thickness (In.)	0.044
Thickness (mm)	1.1
Tool	GTS, GTSL, GS2B, STS2
Min. Order UOM	PC
Min. Order Qty.	100
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.