




1-OF-8 DECODER/DEMULTIPLEXER

DESCRIPTION

The T54LS138/T74LS138 is a high speed 1-of-8 Decoder/Demultiplexer. This device is ideally suited for high speed bipolar memory chip select address decoding. The multiple input enables allow parallel expansion to a 1-of-24 decoder using just three LS138 devices or to a 1-of-32 decoder using four LS138s and one inverter. The LS138 is fabricated with the Schottky barrier diode process for high speed and is compatible with all SGS TTL families.



- DEMULTIPLEXING CAPABILITY
- MULTIPLE INPUT ENABLE FOR EASY EXPANSION
- TYPICAL POWER DISSIPATION OF 32mW
- ACTIVE LOW MUTUALLY EXCLUSIVE OUTPUTS
- INPUT CLAMP DIODES LIMIT HIGH SPEED TERMINATION EFFECTS
- FULLY TTL AND CMOS COMPATIBLE


PIN CONNECTION (top view) DUAL IN LINE v_{cc} ō, 15 Õ, 14 ŏ, Ē, ō, 12 E3 ō۷ 11 Ō, Ōς 10 GND Õ, Pr-onse **CHIP CARRIER** 4 4 7 7 7 8 3 2 1 20 19 Ē, NC Ē, Ē2 Ō3 E3 NC = No Internal Connection

PIN NAMES

A ₀ -A ₂	Address Inputs
Ē₁-Ē₂	Enable (Active LOW) Inputs
E ₃	Enable (Active HIGH) Input
\overline{O}_0 - \overline{O}_7	Active LOW Outputs



LOGIC SYMBOL AND LOGIC DIAGRAM



ABSOLUTE MAXIMUM RATINGS

Symbol	Parameter	Value	Unit	
V _{CC}	Supply Voltage	- 0.5 to 7		
V ₁	Input Voltage, Applied to Input	-0.5 to 5.5	٧	
V _O	Output Voltage, Applied to Output	-0.5 to 10	V	
lı lı	Input Current, Into Inputs	-30 to 5	mA	
-lo	Output Current, Into Outputs	50	mA	

Stresses in excess of those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. This is a stress rating only and functional operation of the device at these or any other conditions in excess of those indicated in the operational sections of this specification is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

GUARANTEED OPERATING RANGES

		Temperature			
Part Numbers	Min	Тур	Max	remperature	
T54LS138D2	4.5 V	5.0 V	5.5 V	-55°C to +125°C	
T74LS138XX	4.75 V	5.0 V	5.25 V	0°C to +70°C	

XX = package type.

234



FUNCTIONAL DESCRIPTION

The LS138 is a high speed 1-of-8 Decoder/Demultiplexer fabricated with the low power Schottky barrier diode process. The decoder accepts three binary weighted inputs (A_0 , A_1 , A_2) and when enable provides eight mutually exclusive active LOW outputs ($\overline{O_0}$ - $\overline{O_7}$). The LS138 features three Enable inputs two active LOW (\overline{E}_1 , \overline{E}_2) and one active HIGH (E_3). All outputs will be HIGH unless \overline{E}_1 and \overline{E}_2 are LOW and E_3 is HIGH. This multiple enable

function allows easy parallel expansion of the device of a 1-of-32 (5 lines to 32) decoded with just four LS138s and one inverter. (See Figure 1). The LS138 can be used as an 8-output demultiple-

xer by using one of the active LOW Enable Inputs as the data input and the other Enable inputs strobes. The Enable inputs which are not used must be permanently tied to their appropriate active HIGH or active LOW state.

TRUTH TABLE


	INPUTS								OUT	PUTS			
Ē ₁	Ē ₂	E ₃	A ₀	A ₁	A ₂	ō₀	Ō ₁	Ō ₂	Ō ₃	O ₄	Ō₅	Ō ₆	Ō ₇
Н	. x	Х	х	X	X	н	н	н	н	Н	Н	н	Н
X	Н	Х	X	Х	Х	H	Н	Н	Н	Н	Н	Н	Н
X	Х	L	x	Х	Х	H	Н	Н	н	Н	Н	н	Н
L	L	Н	L	L	L	L	Н	Н	Н	Н	Н	н	Н
L	L	Н	н	L	L	Н	L	н	Н	Н	Н	Н	Н
L	L	н	L	Н	L	H	Н	L	Н	н	Н	Н	Н
L	L	н	н	Н	L	Н	Н	н	L	Н	Н	Н	н
L	L	Н	L	L	Н	Н	Н	Н	Н	L	н	н	Н
L	L	Н	н	L	Н	H	н	Н	Н	Н	L	Н	Н
L	L	Н	L	Н	Н	Н	Н	Н	H	Н	Н	L	Н
L	L	Н	Н	Н	Н	Н	н	н	н	н	н	Н	L

H = HIGH Voltage Level

L = LOW Voltage Level

X = Don't Care

Fig. 1





DC CHARACTERISTICS OVER OPERATING TEMPERATURE RANGE

			Limits			Te	Harita	
Symbol	Parameter	Min. Ty 2.0	Тур.	Max.		Units		
V _{IH}	Input HIGH Voltage				Guaranteed in Voltage for al	٧		
V _{IL}	Input LOW Voltage 54				0.7	Guaranteed in	v	
		74			0.8	Voltage for al		
V _{CD}	Input Clamp Diode Vo	Itage		-0.65	- 1.5	V _{CC} = MIN,I _{IN}	٧	
V _{OH}	Output HIGH Voltage	54	2.5	3.4		V _{CC} = MIN,I _{OI}	V	
		74	2.7	3.4		V _{IL} per Truth		
V _{OL}	Output LOW Voltage	54,74		0.25	0.4	I _{OL} = 4.0mA V _{CC} = MIN V _{IN} = V _{IH} (
		74		0.35	0.5	I _{OL} = 8.0mA	V _{IL} per Truth Table	V
l _{IH}	Input HIGH Current			1.0	20 0.1	V _{CC} = MAX, V _{IN} = 2.7V V _{CC} = MAX, V _{IN} = 7.0V		μA mA
I _{IL}	Input LOW Current				-0.4	V _{CC} = MAX, \	/ _{IN} = 0.4V	mA
los	Output Short Circuit Current (Note 2)		- 20		- 100	V _{CC} = MAX, \	/ _{OUT} = 0V	mA
Icc	Power Supply Current		6.0	10	V _{CC} = MAX		mA	

AC CHARACTERISTICS: (TA = 25°C)

Symbol		Level		Limits		Test Conditions	Units
	Parameter	of Delay	Min.	Тур.	Max.		
t _{PLH}	Propagation Delay, Address to Output	2 2		13 27	20 41		ns
t _{PLH}	Propagation Delay, Address to Output	3 3		18 26	27 39	V _{CC} = 5.0V	ns
t _{PLH}	Propagation Delay, E to Any Output	2 2		12 21	18 32	C _L = 15pF	ns
t _{PLH}	Propagation Delay, E to Any Output	3		17 25	26 38		ns

Notes:

- 1) Conditions shown as MIN or MAX, use the appropriate value specified under guaranteed operating ranges.
- 2) Not more than one output should be shorted at a time.
- 3) Typical Values are V_{CC} = 5,0V, T_A = 25°C

AC WAVEFORMS

