Preferred Device

Small Signal MOSFET 500 mA, 60 Volts

N-Channel TO-92 (TO-226)

Features

• Pb-Free Package is Available*

MAXIMUM RATINGS

Rating	Symbol	Value	Unit
Drain – Source Voltage	V _{DS}	60	Vdc
Gate-Source Voltage - Continuous - Non-repetitive (t _p ≤ 50 μs)	V _{GS} V _{GSM}	±20 ±40	Vdc Vpk
Drain Current (Note)	I _D	0.5	Adc
Total Device Dissipation @ T _A = 25°C	P _D	350	mW
Operating and Storage Junction Temperature Range	T _J , T _{stg}	-55 to +150	°C

Maximum ratings are those values beyond which device damage can occur. Maximum ratings applied to the device are individual stress limit values (not normal operating conditions) and are not valid simultaneously. If these limits are exceeded, device functional operation is not implied, damage may occur and reliability may be affected.

NOTE: The Power Dissipation of the package may result in a lower continuous drain current




ON Semiconductor®

http://onsemi.com


500 mA, 60 Volts $R_{DS(on)} = 5.0 \Omega$

N-Channel





MARKING DIAGRAM & PIN ASSIGNMENT



BS170 = Device Code A = Assembly Location

Y = Year WW = Work Week Pb-Free Package

(Note: Microdot may be in either location)

ORDERING INFORMATION

See detailed ordering and shipping information in the package dimensions section on page 2 of this data sheet.

Preferred devices are recommended choices for future use and best overall value.

^{*}For additional information on our Pb–Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

BS170

ELECTRICAL CHARACTERISTICS ($T_A = 25^{\circ}C$ unless otherwise noted)

Characteristic	Symbol	Min	Тур	Max	Unit
OFF CHARACTERISTICS	•		•	•	•
Gate Reverse Current (V _{GS} = 15 Vdc, V _{DS} = 0)	I _{GSS}	-	0.01	10	nAdc
Drain-Source Breakdown Voltage (V _{GS} = 0, I _D = 100 μAdc)	V _{(BR)DSS}	60	90	-	Vdc
ON CHARACTERISTICS (Note 1)					
Gate Threshold Voltage $(V_{DS} = V_{GS}, I_D = 1.0 \text{ mAdc})$	V _{GS(Th)}	0.8	2.0	3.0	Vdc
Static Drain–Source On Resistance (V _{GS} = 10 Vdc, I _D = 200 mAdc)	r _{DS(on)}	-	1.8	5.0	Ω
Drain Cutoff Current (V _{DS} = 25 Vdc, V _{GS} = 0 Vdc)	I _{D(off)}	-	-	0.5	μΑ
Forward Transconductance (V _{DS} = 10 Vdc, I _D = 250 mAdc)	9 _{fs}	-	200	-	mmhos
SMALL-SIGNAL CHARACTERISTICS					
Input Capacitance $(V_{DS} = 10 \text{ Vdc}, V_{GS} = 0, f = 1.0 \text{ MHz})$	C _{iss}	-	-	60	pF
SWITCHING CHARACTERISTICS					
Turn-On Time (I _D = 0.2 Adc) See Figure 1	t _{on}	-	4.0	10	ns
Turn-Off Time (I _D = 0.2 Adc) See Figure 1	t _{off}	-	4.0	10	ns

^{1.} Pulse Test: Pulse Width $\leq 300 \,\mu\text{s}$, Duty Cycle $\leq 2.0\%$.

ORDERING INFORMATION

Device	Package	Shipping [†]	
BS170	TO-92 (TO-226)	1000 Unit/Tube	
BS170G	TO-92 (TO-226) (Pb-Free)	1000 Unit/Tube	
BS170RLRA	TO-92 (TO-226)	2000 Tape & Reel	
BS170RLRAG	TO-92 (TO-226) (Pb-Free)	2000 Tape & Reel	
BS170RLRM	TO-92 (TO-226)	2000 Tape & Reel	
BS170RLRMG	TO-92 (TO-226) (Pb-Free)	2000 Tape & Reel	
BS170RLRP	TO-92 (TO-226)	2000 Tape & Reel	
BS170RLRPG	TO-92 (TO-226) (Pb-Free)	2000 Tape & Reel	
BS170RL1	TO-92 (TO-226)	2000 Tape & Reel	
BS170RL1G	TO-92 (TO-226) (Pb-Free)	2000 Tape & Reel	
BS170ZL1	TO-92 (TO-226)	2000 Tape & Reel	
BS170ZL1G	TO-92 (TO-226) (Pb-Free)	2000 Tape & Reel	

[†]For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

RESISTIVE SWITCHING




Figure 1. Switching Test Circuit

Figure 2. Switching Waveforms




Figure 3. V_{GS(th)} Normalized versus Temperature

Figure 4. On-Region Characteristics




Figure 5. Output Characteristics





Figure 6. Capacitance versus Drain-To-Source Voltage

PACKAGE DIMENSIONS

TO-92 (TO-226) CASE 29-11 **ISSUE AL**





NOTES:

- DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
- CONTROLLING DIMENSION: INCH.
 CONTOUR OF PACKAGE BEYOND DIMENSION R
- IS UNCONTROLLED.
 LEAD DIMENSION IS UNCONTROLLED IN P AND BEYOND DIMENSION K MINIMUM.

	INCHES		MILLIN	IETERS
DIM	MIN	MAX	MIN	MAX
Α	0.175	0.205	4.45	5.20
В	0.170	0.210	4.32	5.33
С	0.125	0.165	3.18	4.19
D	0.016	0.021	0.407	0.533
G	0.045	0.055	1.15	1.39
Н	0.095	0.105	2.42	2.66
J	0.015	0.020	0.39	0.50
K	0.500		12.70	
L	0.250		6.35	
N	0.080	0.105	2.04	2.66
P		0.100		2.54
R	0.115		2.93	
٧	0.135		3.43	

STYLE 30:

- PIN 1. DRAIN
 - 2 GATE
 - 3. SOURCE

ON Semiconductor and una are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice on semiconductor and are registered readerlands of semiconductor Components industries, Ltc (SCILLC). Solitude services the inject to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications. intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor P.O. Box 61312, Phoenix, Arizona 85082-1312 USA Phone: 480-829-7710 or 800-344-3860 Toll Free USA/Canada Fax: 480-829-7709 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com

N. American Technical Support: 800-282-9855 Toll Free

Japan: ON Semiconductor, Japan Customer Focus Center 2-9-1 Kamimeguro, Meguro-ku, Tokyo, Japan 153-0051 Phone: 81-3-5773-3850

ON Semiconductor Website: http://onsemi.com

Order Literature: http://www.onsemi.com/litorder

For additional information, please contact your local Sales Representative.