# Printmount Switch, Short Stroke, 7.5 mm, Vertical Actuator













## Weblinks

html-datasheet, General Product Information, CE declaration of conformity, RoHS, CHINA-RoHS, e-Shop, CAD-Drawings, Product News, Detailed request for product

## **All Variants**

Order Number Description

LPV 6X6 SHORT TRAVEL SWITCH 3.85MM 1301.9501

Most Popular.

Availability for all products can be searched real-time:http://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER



#### DATA LSH, LPH, LPS, LPV, SMS, PMS, MTG SWITCHES-MOMENTARY ACTION



## **BENEFITS**

- Simple assembly, long life time, short lead time
- Reliable tactile feedback
- Various designs with 1/4 and 1/2 inch are possible with different heights
- Variable colour design and lettering
- Available for through hole and SMD assembly
- Tested to degree of protection IP 40 and IP 67

		LSH/LPH LPS//LPV	SMS	PMS	MTG	
Electrical data						
Contact material					gold	silver
Switching voltage max.	[v]	12 DC	30 AC / 42 DC	30 AC / 42 DC	max. 24 DC	max. 48 DC
Switching current max.	[mA]	50	50	50	max. 50	max. 125
Rated breaking capacity	[w]		0.12	0.12	0.48	2.40
Lifetime (at rated breaking capacity)		> 105	>106	> 106	>10 <sup>6</sup>	>106
Initial contact resistance, new [m\Omega]		max. 100	<50	< 50	<50	<50
Initial contact resistance, after	r lifetime [mΩ]	max. 100	< 150	< 150	< 50	<50
Insulation resistance	[m $\Omega$ ]		>10 <sup>8</sup>	>10 <sup>8</sup>	>108	>108
Contact bounce time	[ms]	typ. 0.1	typ. 0.15	typ. 0.15	typ. 0.1	typ. 0.1
Mechanical data						
Actuating force	IP 40 [N]	1.6 ± 0.5	1.6 ± 0.4	1.6 ± 0.4	2.5 ± 0.5	2.5 ± 0.5
	IP 67 [N]		1.8 ± 0.4	1.8 ± 0.4		
Contact travel	[mm]	0.25 + 0.2/-0.1	0.35 ± 0.1	0.35 ± 0.1	0.45 ± 0.1	0.45 ± 0.1
End stop strength	[N]	50 N/3s	> 100	>100	> 50	> 50
Lifetime	[operations]	>105	> 10 <sup>8</sup>	> 106	>106	>10 <sup>6</sup>
Other data		ID 40	ID 40 UD 07	ID 40 / ID 47	ID 40	ID 10
Degree of protection		IP 40	IP 40/IP 67	IP 40/IP 67	IP 40	IP 40
Soldering method		IR-Reflow	IR-Reflow	Wave	Wave	Wave
Soldering heat resistance	(LSH) IR Reflow [°C/s]	240/20				
	(LPV/LPS/LPH) [°C/s]	260/3				
	Jedec J-STD-020C		245/5	248.5/1	248.5/1	248,5/1
				240,01	240,0/1	240,0/1
Ambient temperature	[°C]	-20 – +70	-40 – +85	-40 - +85	-25 - +85	-25 – +85
•	[0]	-30 - +85	-40 - +85	-40 - +85	-25 - +85	-25 - +85
Storage temperature  Cleaning agent proof	[10]	-30 - +65	-40 = +65 Zestron	Zestron	-25 - +85	-25 - +65
Flux - proof			IP67	IP67		
Materials			IP6/	IP67		
Sealing membrane IP 67			VMQ		VMQ	
Contact material gold			CuZn37 Ni + Au		CuZn -3 µm Ni +2 µm Au	
Contact material silver			VILIU/ IN TIN		CuZn -2.5µm Ag passivated	
Terminals		CuZn+Cu+Ag 0,7µm	CuZn37 - Sn			
Socket		, , , ,	Thermoplast PA 4.6		Thermoplast PES	
Actuator			Thermoplast PPS		Thermoplast PC	
Cover plate			X 12CrNi177			
oorer plate			X 1201	14177		



# **5.SCHURTER**

#### **OVERVIEW**

#### LPS, LPV SWITCHES-MOMENTARY ACTION

# **FEATURES** Degree of protection Models/Leads PART NUMBER \* **Actuator dimensions** 2.40 mm x 2.40 mm 2.80 mm x 2.80 mm Actuator ØA/Overall height h 3.50 mm / 3.85 mm 3.40 mm / 4.30 mm 3.40 mm / 5.00 mm 3.30 mm / 6.15 mm 3.20 mm / 7.00 mm 3.30 mm / 7.30 mm 3.10 mm / 8.00 mm 3.20 mm / 9.50 mm 3.00 mm / 11.35 mm 3.00 mm / 12.50 mm **Packaging** loose in boxes taped and reeled

Circuit diagram:

Solder pads: Drilling diagram:



<sup>\*)</sup> Please see the PCN. The drawings and technical specs are not valid for this variant (1301.9503).



<sup>&#</sup>x27; X in the Part No. must be replaced by the desired version