Preferred Device

SWITCHMODE ™ **Power Rectifier**

These state-of-the-art devices are designed for use in switching power supplies, inverters and as free wheeling diodes.

Features

- Ultrafast 35 Nanosecond Recovery Times
- 150°C Operating Junction Temperature
- Epoxy Meets UL 94 V-0 @ 0.125 in
- High Temperature Glass Passivated Junction
- Low Leakage Specified @ 150°C Case Temperature
- Current Derating @ Both Case and Ambient Temperatures
- Electrically Isolated. No Isolation Hardware Required.
- Pb-Free Package is Available*

Mechanical Characteristics:

- Case: Epoxy, Molded
- Weight: 1.9 Grams (Approximately)
- Finish: All External Surfaces Corrosion Resistant and Terminal Leads are Readily Solderable
- Lead Temperature for Soldering Purposes: 260°C Max. for 10 Seconds

MAXIMUM RATINGS (Per Leg)

| Rating | Symbol | Value | Unit |
|--|--|--------------|------|
| Peak Repetitive Reverse Voltage Working Peak Reverse Voltage DC Blocking Voltage | V _{RRM} V _{RWM} V _R | 200 | V |
| Average Rectified Forward Current Per Diode, (Rated V _R), T _C = 150°C Total Device | I _{F(AV)} | 8 16 | Α |
| Peak Repetitive Forward Current (Rated V _R , Square Wave, 20 kHz), T _C = 150°C | I _{FM} | 16 | Α |
| Non-repetitive Peak Surge Current (Surge applied at rated load conditions halfwave, single phase, 60 Hz) | I _{FSM} | 100 | Α |
| Operating Junction and Storage Temperature | T _J , T _{stg} | - 65 to +150 | °C |
| RMS Isolation Voltage (t = 0.3 second, R.H. \leq 30%, T _A = 25°C) (Note 1) Per Figure 3 | V _{iso1} | 4500 | V |

Stresses exceeding Maximum Ratings may damage the device. Maximum Ratings are stress ratings only. Functional operation above the Recommended Operating Conditions is not implied. Extended exposure to stresses above the Recommended Operating Conditions may affect device reliability.


1. Proper strike and creepage distance must be provided.




ON Semiconductor®

http://onsemi.com

ULTRAFAST RECTIFIER16 AMPERES, 200 VOLTS



MARKING DIAGRAM



A = Assembly Location

′ = Year

WW = Work Week
U1620 = Device Code
G = Pb-Free Package
AKA = Diode Polarity

ORDERING INFORMATION

| Device | Package | Shipping |
|-------------|---------------------|---------------|
| MURF1620CT | TO-220 | 50 Units/Rail |
| MURF1620CTG | TO-220 (Pb-Free) | 50 Units/Rail |

Preferred devices are recommended choices for future use and best overall value.

^{*}For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

THERMAL CHARACTERISTICS (Per Leg)

| Rating | Symbol | Value | Unit |
|---|----------------|-------|------|
| Maximum Thermal Resistance, Junction-to-Case | $R_{	heta JC}$ | 4.2 | °C/W |
| Lead Temperature for Soldering Purposes: 1/8" from the Case for 5 seconds | TL | 260 | °C |

ELECTRICAL CHARACTERISTICS (Per Leg)

| Characteristic | Sy | mbol | Value | Unit |
|---|----|-----------------|----------------|------|
| Maximum Instantaneous Forward Voltage (Note 2) ($i_F = 8.0 \text{ A}, T_C = 150^{\circ}\text{C}$) ($i_F = 8.0 \text{ A}, T_C = 25^{\circ}\text{C}$) | | ٧F | 0.895 0.975 | V |
| Maximum Instantaneous Reverse Current (Note 2) (Rated DC Voltage, T _C = 150°C) (Rated DC Voltage, T _C = 25°C) | | İR | 250 5.0 | μΑ |
| Maximum Reverse Recovery Time (I _F = 1.0 A, di/dt = 50 A/μs) (I _F = 0.5 A, i _R = 1.0 A, I _{REC} = 0.25 A) | | t _{rr} | 35 25 | ns |

^{2.} Pulse Test: Pulse Width = 300 μs, Duty Cycle ≤ 2.0%.




Figure 1. Typical Forward Voltage, Per Leg




Figure 2. Typical Reverse Current, Per Leg*

TEST CONDITION FOR ISOLATION TEST*

FULLY ISOLATED PACKAGE





Figure 3. Mounting Position

* Measurement made between leads and heatsink with all leads shorted together.

MOUNTING INFORMATION




Clip-Mounted

Figure 4. Typical Mounting Technique

PACKAGE DIMENSIONS

TO-220 FULLPAK CASE 221D-03 **ISSUE J**



NOTES:

- DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
 CONTROLLING DIMENSION: INCH
- 221D-01 THRU 221D-02 OBSOLETE, NEW STANDARD 221D-03.

| | INCHES | | MILLIMETERS | |
|-----|-----------|-----------|-------------|-------|
| DIM | MIN | MAX | MIN | MAX |
| Α | 0.617 | 0.635 | 15.67 | 16.12 |
| В | 0.392 | 0.419 | 9.96 | 10.63 |
| С | 0.177 | 0.193 | 4.50 | 4.90 |
| D | 0.024 | 0.039 | 0.60 | 1.00 |
| F | 0.116 | 0.129 | 2.95 | 3.28 |
| G | 0.100 | 0.100 BSC | | BSC |
| Н | 0.118 | 0.135 | 3.00 | 3.43 |
| J | 0.018 | 0.025 | 0.45 | 0.63 |
| K | 0.503 | 0.541 | 12.78 | 13.73 |
| L | 0.048 | 0.058 | 1.23 | 1.47 |
| N | 0.200 BSC | | 5.08 BSC | |
| Q | 0.122 | 0.138 | 3.10 | 3.50 |
| R | 0.099 | 0.117 | 2.51 | 2.96 |
| S | 0.092 | 0.113 | 2.34 | 2.87 |
| U | 0.239 | 0.271 | 6.06 | 6.88 |

PIN 1. ANODE

CATHODE 2. ANODE

SWITCHMODE is a trademark of Semiconductor Components Industries, LLC.

ON Semiconductor and un are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its partner rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor P.O. Box 5163, Denver, Colorado 80217 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada

Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com

N. American Technical Support: 800-282-9855 Toll Free

Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910

Japan Customer Focus Center Phone: 81-3-5773-3850

ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative