


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NO.	PACKAGE QTY.	MIN. BUNDLE DIA.	MAX. BUNDLE DIA.	LENGTH L ±.2 [5]
MLT2.7WH-LP	50	2.0" [50]	2.7" [69]	10.2" [259]
MLT4WH-LP	50	2.0" [50]	4" [102]	14.3" [362]
MLT6WH-LP	50	2.0" [50]	6" [152]	20.5" [521]
MLT8WH-LP	50	2.0" [50]	8" [203]	26.8" [679]
MLT10WH-LP	50	2.0" [50]	10" [254]	33.0" [838]
MLT2.7WH-TL	250	2.0" [50]	2.7" [69]	10.2" [259]
MLT4WH-TL	250	2.0" [50]	4" [102]	14.3" [362]
MLT6WH-TL	250	2.0" [50]	6" [152]	20.5" [521]



NOTES:

- APPLICATION TOOLS - GS4MT, PPTMT, ST2MT, ST3MT, HTMT
- MINIMUM LOOP TENSILE STRENGTH - 450 LBS (2000 NEWTONS) WHEN TESTED ON A 3" MANDREL EXCEPT MLT2.7WH-LP WHEN TESTED ON A 1 1/2" MANDREL.
- BRACKETS [] DENOTE DIMENSIONS IN MILLIMETERS, AND ARE SHOWN FOR REFERENCE ONLY
- TOLERANCES:
 .XXX = $\pm .010$ [.25] .XX = $\pm .02$ [.5]
 .X = $\pm .03$ [.8] ANGLES = $\pm 2^\circ$
- MATERIAL: 304 STAINLESS STEEL

SECTION A-A
4X SCALE
FULLY ROUNDED EDGES ALONG STRAP BODY

05A	2/12	MIM	RGRO	NOTE #3 METRIC DIMENSIONS NOTED AS BEING SHOWN FOR REFERENCE ONLY
REV	DATE	BY	CHK	DESCRIPTION

PANDUIT

CORP.

TINLEY PARK, ILLINOIS

METAL LOCKING TIE
HEAVY SERIES WAVE-TY
304 STAINLESS STEEL CUSTOMER DRAWING

DRAWN BY JAMB	CHK'D DPN	SCALE 2X	DRAWING NO. N41122BS_DC
------------------	--------------	-------------	----------------------------