


# Model 2249 Cable Assembly with BNC (M) on Each End

CE



### **Features**

- The molded strain relief is directly bonded to the cable jacket for superior strength and durability.
- PTFE insulation and nickel tarnish resistant outer shells used in the BNC connector provide long life and reliability.
- Gold-plated center contacts assure the most noise free connection possible.
- The connectors and cable are impedance matched.



# **Cable Designation & Type**

**2249-C**: RG58C/U, 50 Ohm cable makes it ideal for most test and measurement applications, RF transmission systems and Thinnet LAN applications.

**2249-E**: RG59B/U, 75 Ohm cable assembly for use with broadcast, video, and other signal applications.

2249-K: RG174/U, smaller diameter 50 Ohm cable for greater flexibility in tight applications. It is best suited for

use in low power situations where small size and flexibility is important.

**2249-Y**: RG223/U, double-shielded 50 Ohm cable assembly for superior interference rejection.

### **Materials**

BNC male: Body - Brass, Tarnish Resistant Nickel Plating

Center Contact - Brass, Gold Plated

Dielectric - PTFE

Strain Relief: PVC molded directly to cable and connectors

**USA:** Sales: 800-490-2361

Technical Support: <a href="mailto:technicalsupport@pomonatest.com">technicalsupport@pomonatest.com</a>

Fax: 425-446-5844

Europe: 31-(0) 40 2675 150 International: 425-446-5500

Where to Buy: www.pomonaelectronics.com

All dimensions are in inches. Tolerances (except noted):  $.xx = \pm .02$ " (,51 mm),  $.xxx = \pm .005$ " (,127 mm). All specifications are to the latest revisions. Specifications are subject to change without notice. Registered trademarks are the property of their respective companies.



# Model 2249 Cable Assembly with BNC (M) on Each End

CE

# **Ratings**

Cable Designation	Туре	Impedance ohms	Capacitance per 1 foot / 0,304 meters	/100 Ft @	Insulation	AWG	Center Strands X AWG	Wire Type	Jacket Material	Cable OD	Shield	Temperature (w/o connectors) °C
С	RG58C/U	50	32.2 pf	0.44 dB	PE	20	19X33	TC	PVCNC	.195	TCB	-40 to +85
Е	RG59B/U	75	22.0 pf	0.60 dB	PE	23	Solid	BCCS	PVCNC	.242	BCB	-40 to +60
K	RG174/U	50	30.8 pf	1.90 dB	PE	26	7X34	BCCS	PVC	.110	TCB	-40 to +75
Υ	RG223/U	50	30.8 pf	0.35 dB	PE	19	Solid	SPC	PVCNC	.212	SCB / SCB	-40 to +60

AWG = American Wire Gauge

BCB = Bare Copper Braid

BCCS = Bare Copper Covered Steel

PE = Polyethylene

PVC = Polyvinyl Chloride

PVCNC = Polyvinyl Chloride Non-Contaminating

SCB = Silver Coated Braid SPC = Silver Plated Copper

SSPE = Semi-Solid Polyethylene

TC = Tinned Copper

TCB = Tinned Copper Braid

Voltage: 500 Vrms max from center conductor to shield, and 30 Vac / 60 Vdc max from shield to earth in

controlled hands-free testing environments.

For CE compliance: not intended for hand-held use at voltages above 30 Vac / 60 Vdc.

# **Ordering Information**

Model: 2249-type-length\*

Cable type: C, E, K, Y (see table for details)

Ordering Example: 2249-C-72, type "C" cable with a

72" (182,9cm) length.

Length (inches)	Length Tolerance
6 to 24	+/50"
36 to 48	+/- 1.00"
*60+	+/- 2%

<sup>\*</sup>Additional lengths greater than 60" length are subject to a tolerance of +/- 2% of cable length.

#### Cable Length for "C" Type\*:

6" (15,24cm), 12" (30,5cm), 24" (61,0cm), 36" (91,4cm), 48" (121,9cm), 60" (152,4cm), 72" (182,9cm), 96" (243,84cm), 120" (304,8cm), 144" (365,76cm), 180" (457,2cm), 240" (609,6cm), 300" (762cm), 360" (914,4cm), 600" (1524cm)

#### Cable Length for "E" Type\*:

6" (15,24cm), 12" (30,5cm), 24" (61,0cm), 36" (91,4cm), 48" (121,9cm), 60" (152,4cm), 72" (182,9cm), 120" (304,8cm), 144" (365,76cm), 180" (457,2cm), 240" (609,6cm), 300" (762cm), 360" (914,4cm), 480" (1219cm), 600" (1524cm)

## Cable Length for "K" Type\*:

6" (15,24cm), 12" (30,5cm), 24" (61,0cm), 36" (91,4cm), 48" (121,9cm), 60" (152,4cm), 72" (182,9cm), 120" (304,8cm), 180" (457,2cm), 240" (609,6cm), 300" (762cm), 480" (1219cm)

#### Cable Length for "Y" Type\*:

12" (30,5cm), 24" (61,0cm), 36" (91,4cm), 48" (121,9cm), 60" (152,4cm), 72" (182,9cm),120" (304,8cm), 144" (365,76cm), 180" (457,2cm), 240" (609,6cm)

\* Additional lengths are available upon request.

**USA:** Sales: 800-490-2361

Technical Support: <a href="mailto:technicalsupport@pomonatest.com">technicalsupport@pomonatest.com</a>

Fax: 425-446-5844

**Europe:** 31-(0) 40 2675 150 **International:** 425-446-5500

Where to Buy: www.pomonaelectronics.com

All dimensions are in inches. Tolerances (except noted):  $.xx = \pm .02$ " (,51 mm),  $.xxx = \pm .005$ " (,127 mm). All specifications are to the latest revisions. Specifications are subject to change without notice. Registered trademarks are the property of their respective companies.