

Data Sheet

RP013xxVBWN

Page 1/4


P/N

311691xx

xx=number of poles

2013/12/05

Illustration



see enlarged drawing at the end of the document

Product specification

- screw type terminal block, pluggable
- centerline 3.50 mm, direction of connection vertical 0°
- wire protector
- color black
- wire entry codeable side perpendicular to plug direction
- Connection data

cRUUS V / A / AWG 250 / 10 / 28 - 16

S 5 A / 125 V / 2.5 kV / 3 / IEC 61984 / 0.08 - 1 mm²



Data Sheet

RP013xxVBWN

Page 2/4

P/N

311691xx

xx=number of poles



2013/12/05

Technical Data

General Data

Tightening torque SEV	0.15 Nm		
Tightening torque UL	3 lb-in		
min. number of poles	2		
max. number of poles	18		
Insulating material class	CTI 600		
clearance/creepage dist.	2 mm		
protection category	IP 20		
Overvoltage category	III	III	II
Pollution degree	3	2	2
Rated voltage	160 V	400 V	400 V
Rated test voltage	2.5 kV	2.5 kV	2.5 kV

Connection data

 V / A / AWG	250 / 10 / 28 - 16
	5 A / 125 V / 2.5 kV / 3 / IEC 61984 / 0.08 - 1 mm ²

Material

insulating material	PA66
flammability class	V0
terminal body material	CuZn
terminal body surface	Cu + Ni
screw surface	Zn Cr(VI)-frei/free
wire protector material	CuNiZn
screw thread	M2

Climatic properties

upper limit temperature	105 °C
lower limit temperature	-40 °C

General

Tolerance	ISO 2768 -mH
-----------	--------------

Data Sheet

RP013xxVBWN

Page 3/4

P/N

311691xx

xx=number of poles

2013/12/05

Matching Part

P/N	Product name
311801 (on request)	PT013xxHBBN Typ 180
311811 (on request)	PT013xxVBBN Typ 181
311821	PT113xxHBBN Typ 182
311831	PT113xxVBBN Typ 183
311861 (on request)	PT123xxHDBN Typ 186
311871 (on request)	PT123 xxVDBO

Accessories

P/N	Product name
720243-01-3	720243
720243-02-4	720243

Data Sheet

RP013xxVBWN

Page 4/4

P/N


311691xx

xx=number of poles

2013/12/05

Illustration

Drawing



$L = (\text{pole size} - 1) \times \text{centerline} + 3.7 [0.146]$

