## Piezo Switch N.O.







PSE 30 RI red

PSE 30 RI green

PSE 30 RI

### See below:

## **Approvals and Compliances**

## **Description**

- Available in version Standard, lettered, with Point Illumination or Ring Illumination
- RGB, RGY: flexible input voltage from 5 28 VDC at constant brightness
- With color combination RGB and RGY
- 7 possible colors with RGB configuration
- 3 possible colors with RGY configuration Assembly by mounting with nut
- Pins, Wire, Crimp Terminal male or Cable with Faston

## **Unique Selling Proposition**

- Variety of design options regarding size, colour, shape, connection or
- High reliability, long lifetime with more than 20 mill. actuations
- With RGB or RGY ring illumination

## **Characteristics**

- Housing material types: aluminum or stainless steel, ring illuminated version additionally made of polyamide
- For use in harsh environments, both indoors and outdoors (see technical data)

# Other versions on request

- switch for longer switching signal duration, type: PSE IV
- Switch for explosion proof applications, type: PSE EX
- Switch with enhanced vandal proof protection, type: PSE HI

Alternative: switch vandal improved: PSE HI 22

Alternative: switch for EX proved applications: PSE EX 16; PSE EX 19; PSE EX 22

Alternative: Other diameter PSE NO 16; PSE NO 19; PSE NO 22; PSE NO 24; PSE NO 27

Alternative: switch with prolonged signal: PSE AE 16; PSE AE 30

html datasheet, General Product Information, CAD-Drawings, Product News, Detailed request for product, Microsite

## **Technical Data**

| Electrical Data               |  |
|-------------------------------|--|
| Switching Function            | momentary                                |
| Supply Voltage                | 12 / 24 VDC Ring Illumination 24         |
|                               | VDC Point Illumination                   |
|                               | 5 VDC and 12 VDC variants on request     |
|                               | (MOQ 500 pieces)                         |
| Supply Voltage RGB            | 5 - 28 VDC                               |
| Switching Voltage             | max. 42 / 60 VAC/DC                      |
| Switching Current             | max. 100 mA                              |
| Electrical Rating             | 1 W                                      |
| Lifetime                      | 20 million actuations at Rated Switching |
|                               | Capacity                                 |
| Switch Resistance OFF         | > 10 MΩ                                  |
| Switch Resistance ON          | $< 20 \Omega$ actuated (Ta = 25°C)       |
| Capacity                      | 5 nF                                     |
| N.O. Closing Impulse Duration | 20- 1000 ms depending on actuating       |
|                               | force, time and speed                    |
| Contact Configuration         | free polarity                            |
| RGB Illumination              |  |
| Current Consumtion (max per   | 16.5 mA @ 5 VDC                          |
| color)                        |  |
|                               | 8.2 mA @ 12 VDC                          |
|                               | 5.5 mA @ 24 VDC                          |
|                               | 4.8 mA @ 28 VDC                          |

| Actuating Force                                  | ≤ 3 N at ambient temperature                      |
|--|---|
| Actuating Travel                                 | 0.002 mm  |
| Shock Protection                                 | IK 02   |
| Mounting screw torque                            | 2.5 Nm  |
| Climatical Data                                  |   |
| Operating Temperature                            | -40 to 85 °C                                      |
| Storage Temperature                              | -40 to 85 °C                                      |
| IP-Protection                                    | IP67 acc. to IEC 60529, IP69K acc. to DIN 40050-9 |
| Environmental Assessment                         | +55°C / 93% r.h. acc. to DIN EN 60068-2-30        |
| Salt Spray Test (acc. to DIN 50021-SS)           | 24 h / 48 h / 96 h Residence Time                 |
| Material   |   |
| Housing (depending on type)                      | Stainless Steel, Aluminum anodized                |
| Actuating Area / Insert (with Ring Illumination) | Stainless Steel, Aluminum anodized                |
| Illuminated Ring (Ring Illumination)             | Polyamide   |

## **Approvals and Compliances**

Detailed information on product approvals, code requirements, usage instructions and detailed test conditions can be looked up in Details about Approvals

SCHURTER products are designed for use in industrial environments. They have approvals from independent testing bodies according to national and international standards. Products with specific characteristics and requirements such as required in the automotive sector according to IATF 16949, medical technology according to ISO 13485 or in the aerospace industry can be offered exclusively with customer-specific, individual agreements by SCHURTER.

## **Approvals**

Approval Reference Type:

| Appro             | val Logo | Certification Body | Description  |
|-------------------|----------|--------------------|--|
| $\langle \rangle$ |          | EU                 | EMC: EMC directive 2004/108/EWG  |
| •                 |          |                    | DGUV Test Certificate: FW 11040 Requirements for Food Processing Equipment   |
|                   |          |                    | MIL-STD Certificate Number: 202F Method 107G, 202F Method 204D, 202F Method 213B, 416D Method RS103, 810E Method 501.3, 810E Method 502.3, 810E Method 507.3 |
| VDE               |          |                    | VDE Certificate Number: DIN EN 61000-4-2, DIN EN 61000-4-4, DIN EN 61000-4-5   |

## **Application standards**

Application standards where the product can be used

| Organization | Design                         | Standard     | Description   |
|--------------|--------------------------------|--------------|---|
| <u>IEC</u>   | Designed for applications acc. | IEC/UL 60950 | IEC 60950-1 includes the basic requirements for the safety of information technology equipment. $ \\$ |


## Compliances

The product complies with following Guide Lines


| Identification | Details | Initiator   | Description   |
|----------------|---------|-------------|---|
| ROHS           | RoHS    | SCHURTER AG | Directive RoHS 2011/65/EU, Amendment (EU) 2015/836  |
| REACH          | REACH   | SCHURTER AG | On 1 June 2007, Regulation (EC) No 1907/2006 on the Registration, Evaluation, Authorization and Restriction of Chemicals 1 (abbreviated as "REACH") entered into force. |

# Dimension [mm]

PSE 30 RI



# Design actuating area




Legend:
A = Illumination Area
B = Actuating Area
C = Width Across Flats
I = Crimp Terminal male 6.3 x 0.8
PI = Point Illumination
RI = Ring Illumination

- Lettering:
   either with/without lettering
   position of the connections with respect to the position of the lettering is not defined

F) with finger guidance
E) without finger guidance
3) elevated front design: M19 (standard, others on request)

# **Dimension**


# PSE M30




Drilling diagram

# **Diagrams**


# PSE M24 RI / PSE M27 RI / PSE M30 RI, 12/24 V





- A) Cable 1 (color of the LEDs), Supply voltage first LED group B) Cable 3 (color of the LEDs), Supply voltage second LED group
- C) Cable 2 (black), Common mass of both LED groups
- D) Cable 4 and 5 (white), Input and output PSE switch


# PSE M22 / M30 RI RGY






- A) Cable (color of the LED), Supply voltage
- B) Cable (color of the LED), Supply voltage
- C) Cable (color of the LED), Supply voltage
- D) Cable (black), Common mass
- E) Cable (white), Input and output MCS switch
- F) Cable (white), Input and output MCS switch


# PSE M22 / M24 / M27 / M30 RI RGB






- A) Cable 1 (color of the LED), Supply voltage
- B) Cable 2 (color of the LED), Supply voltage
- C) Cable 3 (color of the LED), Supply voltage
- D) Cable 4 (black), Common mass
- E) Cable 5/6 (white), Input and output PSE switch
- F) Cable 5/6 (white), Input and output PSE switch

## PSE M24 RI / PSE M27 RI / PSE M30 RI, 5 V





- A) Cable 1 (color of the LEDs), Supply voltage first LED group B) Cable 2 (black), Common mass of both LED groups
- C) Cable 3 (color of the LEDs), Supply voltage second LED group
- D) Cable 4 and 5 (white), Input and output PSE switch

## Illumination options for RGY


| Lighting type          | Active terminal A) | Active<br>terminal<br>B) | Active terminal C) | Resulting<br>Color |
|------------------------|--------------------|--------------------------|--------------------|--------------------|
| Multicolor Singlecolor | Α                  |                          |                    | Red 🛑              |
| Multicolor Singlecolor |                    | В                        |                    | Green 🛑            |
| Multicolor Singlecolor |                    |                          | С                  | Yellow —           |

# Illumination options for RGB

| Lighting type             | Active terminal A) | Active terminal B) | Active terminal C) | Resulting<br>Color |
|---------------------------|--------------------|--------------------|--------------------|--------------------|
| Multicolor Singlecolor    | A                  |                    |                    | Red                |
| Multicolor Singlecolor    |                    | В                  |                    | Green 🛑            |
| Multicolor Singlecolor    |                    |                    | С                  | Blue               |
| Multicolor RGB Additive 2 | А                  | В                  |                    | Yellow —           |
| Multicolor RGB Additive 2 | A                  |                    | С                  | Magenta            |
| Multicolor RGB Additive 2 |                    | В                  | С                  | Cyan 🔵             |
| Multicolor RGB Additive 3 | А                  | В                  | С                  | White ()           |

## Lettering





# **Lettering Colour of Laser Lettering**

| Material                   | Lettering Colour |                |                                |  |  |  |
|----------------------------|------------------|----------------|--------------------------------|--|--|--|
| Stainless Steel            | black            | Filled letters |                                |  |  |  |
| Aluminum natural anodized  | light grey       | Filled letters | (only after customer approval) |  |  |  |
| Aluminum coloured anodized | light grey       | Filled letters |                                |  |  |  |

# **Order Index Lettering**

| Laser Marking      |                |                     |                     |
|--------------------|----------------|---------------------|---------------------|
| 001 = <b>A</b>     | 021 = <b>U</b> | 041 = ÷             | 061 = <b>EIN</b>    |
| 002 = <b>B</b>     | 022 = <b>V</b> | 042 = ₩             | 062 = <b>AUS</b>    |
| 003 = <b>C</b>     | 023 = <b>W</b> | 043 = <b>=</b>      | 063 = <b>AUF</b>    |
| $004 = \mathbf{D}$ | 024 = <b>X</b> | 044 = #             | 064 = AB            |
| 005 = <b>E</b>     | 025 = <b>Y</b> | 045 = ↔             | 065 = <b>ON</b>     |
| 006 = <b>F</b>     | 026 = <b>Z</b> | 046 = \$            | 066 = <b>OFF</b>    |
| 007 = G            | 027 = <b>0</b> | 047 = →             | 067 = <b>UP</b>     |
| $008 = \mathbf{H}$ | 028 = <b>1</b> | 048 = ←             | 068 = <b>DOWN</b>   |
| 009 = <b>I</b>     | 029 = <b>2</b> | 049 = ↓             | 069 = <b>HIGH</b>   |
| 010 = <b>J</b>     | 030 = <b>3</b> | 050 = ↑             | 070 = <b>LOW</b>    |
| 011 = <b>K</b>     | 031 = <b>4</b> | 051 = %             | 071 = <b>ON/OFF</b> |
| 012 = <b>L</b>     | 032 = <b>5</b> | 052 = √             | 072 = <b>START</b>  |
| 013 = <b>M</b>     | 033 = <b>6</b> | 053 = <b>CTRL</b>   | 073 = <b>RESET</b>  |
| 014 = <b>N</b>     | 034 = <b>7</b> | 054 = <b>RETURN</b> | 074 = 🔱             |
| 015 = <b>O</b>     | 035 = <b>8</b> | 055 = <b>SHIFT</b>  | 075 = 🌣             |
| 016 = <b>P</b>     | 036 = <b>9</b> | 056 = <b>LOCK</b>   | 076 = △             |
| 017 = <b>Q</b>     | 037 = <b>+</b> | 057 = <b>STOP</b>   | 077 = ()            |
| 018 = <b>R</b>     | 038 = -        | 058 = <b>ENTER</b>  |                     |
| 019 = <b>S</b>     | 039 = .        | 059 = <b>BACK</b>   |                     |
| 020 = <b>T</b>     | 040 = x        | 060 = <b>LINE</b>   |                     |

## **All Variants**

| Mounting<br>Diameter | Terminal      | Housing Material,<br>Torsion Protection | Colour of Housing | Actuator area | Illumination, LED              | Config. Code   | Order Number |
|----------------------|---------------|---|-------------------|---------------|--------------------------------|----------------|--------------|
| 30                   | Flexible wire | Aluminum ,no                            | Alu natural       | F             | RI dotted, blue, 24 VDC        | PSE M 30 NO RI | 1241.3189    |
| 30                   | Flexible wire | Aluminum ,no                            | Alu natural       | F             | RI dotted, red / green, 24 VDC | PSE M 30 NO RI | 1241.3012    |
| 30                   | Flexible wire | Stainless Steel ,no                     | -                 | E             | RI dotted, blue, 24 VDC        | PSE M 30 NO RI | 1241.3237    |
| 30                   | Flexible wire | Stainless Steel ,no                     | -                 | F             | RI dotted, blue, 24 VDC        | PSE M 30 NO RI | 1241.3548    |
| 30                   | Flexible wire | Stainless Steel ,no                     | -                 | F             | RI dotted, red / green, 24 VDC | PSE M 30 NO RI | 1241.3057    |

| Mounting<br>Diameter | Terminal      | Housing Material,<br>Torsion Protection | Colour of Housing | Actuator area | Illumination, LED               | Config. Code   | Order Number |  |
|----------------------|---------------|---|-------------------|---------------|---------------------------------|----------------|--------------|--|
| 30                   | Flexible wire | Aluminum ,no                            | Alu natural       | F             | RI homogeneous, RGB, 5 - 28 VDC | PSE M 30 NO RI | 1241.3667    |  |
| 30                   | Flexible wire | Aluminum ,no                            | Alu natural       | F             | RI homogeneous, RGY, 5 - 28 VDC | PSE M 30 NO RI | 1241.3668    |  |
| 30                   | Flexible wire | Stainless Steel ,no                     | -                 | E             | RI homogeneous, RGB, 5 - 28 VDC | PSE M 30 NO RI | 1241.3670    |  |

Nut with gasket are enclosed in the box.

Other mounting diameters, materials, colors, connections, supply voltages possible available on request. Special materials e.g. Marine grade stainless steel for use in salt and chlorinated environment on request.

The MOQ for standard laser lettering on standard variants is 10 pieces.

5 VDC and 12 VDC variants on request (MOQ 500 pieces)

Most Popular.

Availability for all products can be searched real-time:https://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER

Legend:

Type: PSE

NO = normaly open

IV = prolonged signal

RU = PI = Point Illumination

RI = Ring Illumination

LE = Lettered

K = Plastics

Alu = Aluminium

ES = Stainless steel

 $\mathsf{F} = \mathsf{Finger} \ \mathsf{guidance}$ 

E = without finger guidance

## Packaging unit

10 in box with insert or packed in air cushion bags





- Actuating elements in ESD safe packaging
- Screw nuts and sealing rings in a bag (enclosed in the box)

## **Accessories**

## Description



Connecting Terminal PSE Connecting Terminal



**Power Supply** Power Supply IP42 for LED- and Illumination applications indoor 90~264 VAC => 24 VDC 0.34 A 8 W

**Switches**