#### 


## Series FB

A Unit of Teledyne Electronic Technologies


Part Number*	DESC Drawing Number	Relay Description
FB00CDW FB00CDY	89116-006	Solid State Relay ±1.0 A @ ±80 Vdc Output
FB00FCW FB00FCY	89116-002	Solid State Relay ±0.5 A @ ±180 Vdc Output
FB00KBW FB00KBY	89116-004	Solid State Relay ±250 mA @ ±350 Vdc Output

\* The Y suffix denotes parameters tested to MIL-PRF-28750 specifications. The W suffix denotes parameters tested to Teledyne specifications.

### **BLOCK DIAGRAM**



### **MECHANICAL SPECIFICATIONS**



Low Leakage, High Voltage, Bi-Directional & DC Output Bi-Directional Solid-State Relay



### FEATURES

- High voltage output
- Extremely low leakage current (200 nanoamperes)
  - Bi-directional Power FET output
  - · Optical isolation
  - · Fast switching speed
  - Adjustable turn-on times
  - · Low profile 6-pin mini-DIP
  - Built and tested to the requirements of MIL-PRF-28750

### APPLICATIONS

- Ideal for Automatic Test Equipment (ATE)
- Telecommunications applications
- High-voltage instrumentation systems
- High-speed switching with low EMI

### DESCRIPTION

The Series FB relay is an advanced solidstate bi-directional relay designed specifically for high-speed switching in A.T.E. systems. These devices utilize Teledyne state-of-theart solid-state circuit technology and manufacturing techniques to provide high reliability, low life cycle cost and exceptional switch performance. Each device is uniquely characterized by its switching function. The FB00FC is a power instrumentation relay with low ON resistance and leakage current. The FB00KB is a high-voltage instrumentation relay with a quarter ampere current rating. The FB00CD is a power relay with a current rating of 1 ampere and an ON resistance of 0.4 ohm. The FB solid-state relay has very fast turn on times of under 1 msec and can also be controlled and adjusted with the input current for specific requirements. Other features include optical coupling and full military temperature operating range for extreme applications. Optical coupling minimizes EMI generation and isolates and protects delicate input logic circuits from output voltage transients. These devices are packaged and hermetically sealed in a low-profile metal 6- pin mini-DIP with lead spacing on 0.300 centers for standard mounting configurations.

#### TELEDYNE RELAYS

A Unit of Teledyne Electronic Technologies

# **Series FB**

### ELECTRICAL SPECIFICATIONS

(-55°C TO 120°C Ambient Temperature Unless Otherwise Noted) INPUT (CONTROL) SPECIFICATION

### **ENVIRONMENTAL SPECIFICATIONS**

INPUT (CONTROL	) SPECIF	ICATIO	N			Min	Мах	Units
(See Note 1)	Min	Тур	Max	Units	Temperature			
Rated Input Current	10		25	mAdc	Operating	-55	+120	°C
Input Voltage Drop @ 25 mA			3.25	Vdc	Storage	-55	+125	°C
Continuous Input Current			0.20	Vuc	Vibration, 100 g	10	2000	Hz
-55°C < T₄ < 105°C	10		50	mAdc	Constant Acceleration		5000	g
105°C < T <sub>A</sub> < 120°C	10		25	mAdc				9
Reverse Voltage Protection			-5	Vdc	Shock, 0.5 ms pulse		1500	g
Input Current (Guaranteed Off)			10	μAdc				
Input Current (Guaranteed On)	10			mA				
Turn-Off Voltage			1.5	Vdc				

### OUTPUT (LOAD) SPECIFICATIONS BI-DIRECTIONAL AND AC CONFIGURATIONS (PIN 4 TO PIN 6), SEE NOTE 2

	FB00CD		FB0	FB00FC		0KB	
	Min	Мах	Min	Мах	Min	Max	Units
Continuous Load Current (See Fig. 3 & Note 5)		±1.0		±0.5		±0.25	Adc
Leakage Current @ $V_{load}$ = max. operating voltage							
-55°C < T <sub>A</sub> < +25°C		±200		±200		±200	nAdc
+25°C < T <sub>A</sub> < 120°C		±20		±20		±20	μAdc
Output Voltage Drop		±0.75		±1.0		±2.4	Vdc
Continuous Operating Load Voltage		±80		±180		±350	Vdc
Transient Blocking Voltage (5 s max.)		±90		±180		±360	Vdc
ON Resistance $R_{ds}$ (on) at $T_{J} = 25^{\circ}C$		0.6		1.0		8.0	Ohm
I <sub>LOAD</sub> = 100 mAdc (See Fig. 4 & Note 6)							
Turn-On Time @ ${\rm I_{_{\rm IN}}}$ = 25 mA (See Fig. 2 and 5)		800		800		500	μ <b>s</b>
Turn-Off Time (See Fig. 5)		500		500		500	μs
dV/dt	100		100		100		V/µs
Load Surge Current (See Note 3)		±3.5		±1.75		±0.875	Adc
DC Offset Voltage		100		100		100	μV
Output Capacitance at 25 Vdc, 1 MHz		325		250		100	pF



## **Series FB**

OUTPUT (LOAD) SPECIFICATIONS DC Configuration (Pins 4 and 6 connected together referenced to Pin 5) (See Notes 2 & 7)								
	FB00CD Min Max		FB00FC		FB00KB			
			Min	Max	Min Max		Units	
Continuous Load Current (See Fig. 3 & Note 5)		2.0		1.0		0.5	Adc	
Leakage Current @ $V_{load}$ = max. operating voltage								
$-55^{\circ}C < T_{A} < +25^{\circ}C$		400		400		400	nAdc	
+25°C < T <sub>A</sub> < 120°C		40		40		40	μAdc	
Output Voltage Drop		0.4		0.5		1.8	Vdc	
Continuous Operating Load Voltage		80		180		350	Vdc	
Transient Blocking Voltage (5 s max.)		90		180		360	Vdc	
ON Resistance $R_{ds}$ (on) at $T_{J} = 25^{\circ}C$		0.15		0.25		2.0	Ohm	
I <sub>LOAD</sub> = 100 mAdc (See Fig. 4 & Note 6)								
Turn-On Time @ $I_{IN}$ = 25 mA (See Fig. 2 and 5)		800		800		500	μS	
Turn-Off Time (See Fig. 5)		500		500		500	μs	
Load Surge Current (See Note 3)		7.0		3.5		1.75	Adc	
Output Capacitance at 25 Vdc, 1 MHz		650		500		200	pF	

## **OUTPUT (LOAD) SPECIFICATIONS**

	FB00CD		FB00FC		FB00KB		
All Configurations	Min	Max	Min	Max	Min	Max	Units
Input to Output Capacitance		5		5		5	pF
Dielectric Strength	500		500		500		Vac
Insulation Resistance @ 500 Vdc	10 <sup>9</sup>		10 <sup>9</sup>		10 <sup>9</sup>		Ohm
Output Junction Temperature @ $I_{LOAD} = I_{max rated}$		125		125		125	°C
Maximum Junction Temperature ( $T_J$ Max.)		150		150		150	°C
Thermal Resistance Junction to Ambient $(\boldsymbol{\theta}_{_{JA}})$		110		110		110	°C/W
Thermal Resistance Junction to Case $(\boldsymbol{\theta}_{JC})$		20		20		20	°C/W

A Unit of Teledyne Electronic Technologies

# **Series FB**

