



10A, 60Vdc Optically Isolated, Short-Circuit Protected DC Solid-State Relay

Part Number*	Relay Description
KD00CK	5A Solid-State Relay (SSR)
KD02CK	5A SSR with Switch Status
KD20CK	5A SSR with Short-Circuit Protection
KD22CK	5A SSR with Short-Circuit Protection and Switch Status
LD00CM	10A Solid-State Relay
LD02CM	10A SSR with Switch Status
LD20CM	10A SSR with Short-Circuit Protection
LD22CM	10A SSR with Short-Circuit Protection and Switch Status

^{*} The Y suffix denotes parameters tested to MIL-PRF-28750 specifications. The W suffix denotes parameters tested to Teledyne specifications.

ELECTRICAL SPECIFICATIONS

(-55°C TO +105°C UNLESS OTHERWISE NOTED)

INPUT (CONTROL) SPECIFICATION

When used in 2 terminal configuration (TTL or direct control) (See Fig. 1)

Input Current @ $V_{BIAS} = 5 \text{ Vdc (See Fig.)}$	g. 2)		15	mAdc
Turn-Off Voltage (Guaranteed Off)			1.5	Vdc
Turn-On Voltage (Guaranteed On)	3.8			Vdc
Reverse Voltage Protection			-32	Vdc
Input Supply Range (See Note 1)	3.8		32	Vdc
INPUT (CONTROL) SP When used in 3 terminal configuration (CMOS or open collector TTL) (See Fig.		тіон Тур	Max	Units
Control Current				
$V_{CONTROL} = 5 \text{ Vdc}$			250	μ Adc
$V_{CONTROL} = 18 \text{ Vdc}$			1	mAdc
Control Voltage Range	0		18	Vdc
Bias Supply Voltage (See Note 1)	3.8		32	Vdc
Bias Supply Current			16	mAdc
Turn-Off Voltage (Guaranteed Off)	3.2		10	Vdc
Turn-Off Voltage (Guaranteed Off) Turn-On Voltage (Guaranteed On)	3.2		0.3	





FEATURES

- Available with short-circuit/current overload protection
- · Available with switch status output
- TTL and CMOS compatible control
- · Low ON resistance power FET output
- · Fast switching speed
- Meets 28 Vdc system requirements of MIL-STD-704
- · Optical isolation
- · Low profile hermetic package
- Built and tested to the requirements of MIL-PRF-28750

DESCRIPTION

The Series KD and LD solid-state relays are screened utilizing MIL-PRF-28750 test methods and are packaged in low profile hermetically sealed cases. These relays are constructed with state-of-theart solid state techniques and feature fully floating power FET output technology. This allows the load to be connected to either output terminal and provides a low ON resistance. The input (control) and output are optically isolated to protect input logic circuits from output transients. Available options include short circuit and current overload protection, which provides complete protection for both the relay and system wiring. This feature not only provides protection should a short or overload occur while the relay is on, but will also provide protection should the relay be switched into a short. The second option is a status output line. Switch status returns the true status of the output switch and is optically isolated from the load. It provides status indication independent of the control circuit of the relay. The status line provides a logic 0 (low) when the relay output is off with load voltage and continuity present, and a logic 1 (high) when the output is on.


Max Units


Min Typ



	Max	Units					
Continuous Load Current (See Fig. 3)							
KD and LD series without heat sink	5	Adc					
LD series with heat sink	10	Adc					
Leakage Current @ V _{LOAD} =60Vdc							
KD00CK, KD20CK	100	μΑ					
LD00CM, LD20CM	100	μΑ					
KD02CK, KD22CK	2	mΑ					
LD02CM, LD22CM	2	mA					
Output Voltage Drop							
KD00CK, KD02CK	.60	Vdc					
KD20CK, KD22CK	.70	Vdc					
LD00CM, LD02CM @10A	1.2	Vdc					
LD20CM, LD22CM @10A	1.4	Vdc					
Continuous Operating Load Voltage	60	Vdc					
Transient Blocking Voltage @25°C	80	Vdc					
ON Resistance, I _{LOAD} = 100 mA, T _J = 25°C, (See Note 3)							
KD00CK, KD02CK	.075	Ohm					
LD00CM, LD20CM	.075	Ohm					
KD20CK, KD22CK	.100	Ohm					
LD20CM, LD22CM	.100	Ohm					
Turn-On Time (See Fig. 5)	5	ms					
Turn-Off Time (See Fig. 5)	2	ms					
Electrical System Spike @25°C ±600		Vpk					
Output Capacitance at 25 Vdc, 100 KHz	1600	pF					
Isolation (Input to Output)							
KD00CK, KD20CK	10	рF					
ND00CK, ND20CK	10	pF					
LD00CM, LD20CM	15	pF					
		рF					
LD00CM, LD20CM	15	1.					
LD00CM, LD20CM KD02CK, KD22CK	15	Vac					
LD00CM, LD20CM KD02CK, KD22CK LD02CM, LD22CM	15						
LD00CM, LD20CM KD02CK, KD22CK LD02CM, LD22CM Dielectric Strength 1000	15	Vac					
LD00CM, LD20CM KD02CK, KD22CK LD02CM, LD22CM Dielectric Strength 1000 Insulation Resistance @ 500 Vdc 109 Output Junction Temperature		Vac Ohm					
LD00CM, LD20CM KD02CK, KD22CK LD02CM, LD22CM Dielectric Strength 1000 Insulation Resistance @ 500 Vdc 109 Output Junction Temperature @ I _{LOAD} = I _{max rated}	130	Vac Ohm °C					

BLOCK DIAGRAM







NO STATUS

MECHANICAL SPECIFICATION

DIMENSIONS ARE SHOWN IN INCHES (MILLIMETERS)



K PACKAGE



- Enclosure: Hermetically Sealed DIP
- Leak Rate:1 x 10-8 CC/Sec Maximum
 Material: Header: Cold Rolled Steel
- Nickel Plated Pins Copper Core Grade A Nickel Can:
- Weight: 20 grams
 Tolerance: .XXX ± .005

ENVIRONMENTAL SPECIFICATIONS


		Min	Тур	Max	Units
Temperature Range					
	Operating	-55		+105	°C
	Storage	-55		+125	°C
Vibratio	on 100 g	10		3000	Hz
Consta	nt Acceleration			5000	g
Shock	0.5 ms pulse			1500	g

STATUS OUTPUT TRUTH TABLE (KD02CK, LD02CM, KD22CK, LD22CM)


Control Voltage	Relay Output	State Status Output Level
High	Off	Low $(V_{SO} \le 0.4 \text{ Vdc})$
Low	On	$High (V_{SO} = V_{STATUS})$

STATUS OUTPUT SPECIFICATIONS (KD02CK, LD02CM, KD22CK, LD22CM)


	Min	Тур	Max	Units
Status Supply Voltage			30	Vdc
Status Leakage Current				
@16Vdc			10	μAdc
@30Vdc			100	μAdc
Status (sink) Current (V _{SO} < 0.4 Vdc)			600	μAdc
Status Turn-On Time (See Fig. 6)			3.5	ms
Status Turn-Off Time (See Fig. 6)			8.0	ms




BIAS (INPUT) CURRENT VS BIAS (INPUT) VOLTAGE FIGURE 2 (See Note 1)




(A) 3 TERMINAL INPUT WITH STATUS (See Note 5)




(B) 2 TERMINAL INPUT (OPEN COLLECTOR TTL DRIVE)



(C) 2 TERMINAL INPUT (DIRECT DRIVE) WITH STATUS




(D) 2 TERMINAL INPUT (DIRECT DRIVE)




(E) 3 TERMINAL INPUT WITHOUT STATUS

WIRING CONFIGURATIONS FIGURE 1 (See Note 1)



LOAD CURRENT DERATING CURVE FOR **KD/LD SERIES WITHOUT A HEAT SINK**



NORMALIZED ON RESISTANCE VS **JUNCTION TEMPERATURE**


FIGURE 4 (See Note 3)

HIGH

VCONTRO

VOUTPUT


PIN 1




OVERLOAD CURRENT VS TIME TO TRIP (TYPICAL) KD20CK, KD22CK, LD20CM, LD22CM FIGURE 7

LOAD CURRENT DERATING CURVE FOR LD SERIES

(B)



STATUS TURN-ON AND TURN-OFF **TIMING**




THERMAL DERATING CURVES

FIGURE 3

equal to or less than the value found in Figure 8.

FIGURE 6



SERIES LIMIT BIAS RESISTOR VS **BIAS VOLTAGE** FIGURE 8 (See Note 1)

normalized ON resistance factor (NR) from Figure 4. Calculate the new ON resistance as follows: $R_{(ON)} = NR \cdot R_{ON} @ 25^{\circ}C$ (KD00CK, LD00CM, KD02CK, LD02CM)

2. The rated input voltage is 5V for all tests unless otherwise specified.

$$R_{(ON)} = \begin{pmatrix} (KD00CK, LD00CM, KD02CK, LD02CM) \\ NR(R_{ON} @ +25^{\circ}C) + .025 \text{ ohm} \\ (KD20CK, LD20CM, KD22CK, LD22CM) \end{pmatrix}$$

4. Overload testing to the requirements of MIL-PRF-28750 is constrained to the limits imposed by the short circuit protection characteristics as defined in this specification. System series inductance for "shorted-load" mode of operation should be 50 μ H. Maximum repetition rate into a shorted load should not exceed 10 Hz.


1. Control input is compatible with CMOS or open collector TTL (with pull up resistor). For bias voltages above 6V, a series resistor is required. Use the standard resistor value

3. To calculate the maximum ON resistance for a given junction temperature, find the

5. A status pull up resistor is required for proper operation of the status output. Determine the current (Iso) required by the status interface. Calculate the current (Is) through the status resistor such that the sink current through the status output is 0.6 mA. Select the status resistor such that it does not allow more than 0.6 mA to flow through the status output.

$$R_{STATUS} = \frac{V_{STATUS} - 0.4V}{Iso}$$

6. Inductive loads should be diode suppressed. Input transitions should be ≤1 ms duration and the input drive should be a bounceless contact type.



TYPICAL TRIP CURRENT CHARACTERISTICS FOR SHORT **CIRCUIT CONDITIONS** FIGURE 9

NOTES: