


APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	11/26/18	



Poles: 01 thru 15

SPECIFICATIONS:

Material:

Insulator: PBT, rated UL 94V-0

Insulator color: Black

Contacts: Copper Alloy, Tin plated

Screw: M6 Steel, Zinc plated

Electrical:

Voltage rating: 600 V

Current rating: 115 A

Contact resistance: 20 mohms

Insulation resistance: 1000 Mohms / DC500V

Dielectric withstanding voltage: 2,500 VAC for 1 minute

Mechanical:

Wire Range: 8~2 AWG

Torque: 3.0Nm

Temperature Rating:

-40°C to +130°C

Environmental:

Lead free, RoHS compliant.



	linear dimension(Tolerances Standard)											≡	—	□	//	⊥
	to	over	over	over	over	over	over	over	over	over	over					
variable	6	6	10	18	30	50	80	120	160	200	250	all	to	over	over	over
range	to	to	to	to	to	to	to	to	to	to	to	to	to	to	to	to
tolerance	±0.1	±0.14	±0.19	±0.25	±0.32	±0.43	±0.57	±0.72	±0.88	±1.05	±1.25	0.5	0.025	0.06	0.12	0.4

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE MILLIMETERS
TOLERANCES: EXCEPT AS NOTED

SEE CHART

APPROVALS		DATE
DRAWN	AY	11/26/18
CHECKED	AC	11/26/18
APPROVED		

ADAM
TECH
INTERCONNECTS

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE
TERMINAL BLOCK, .827 [21.00] PITCH
W/ CLEAR COVER

SIZE X	PART NO. TBU-XX-W4-CCS	REV. -
REF: S00067C	SCALE: NTS	SHEET 1 OF 1