

Data sheet



Item no.:	280-519
Product description:	DOUBLE DECK TERMINAL BLOCK; CENTRE MARKING; THROUGH/THROUGH; CARRIER RAIL DIN 35; FRONT-ENTRY; CAGE CLAMP®CONNECTION



Packing unit 50 pieces

Cross section from [mm ²]	0,08 mm ²
Cross section to [mm ²]	2,5 mm ²
Cross section from [AWG]	28 AWG
Cross section to [AWG]	14 AWG
Connection method	CAGE CLAMP®CONNECTION
Voltage UL	300 V
Voltage CSA	300/600 V
Current UL	15 A
Current CSA	20/5 A
Measured voltage EN	500 V
Measured shock voltage	6 kV
Pollution degree	3
Current intensity EN	20 A
Weight	10,057 g
Color	grey
Wiring type	Front-entry
No. of connection Points	4
No. of potentials	2
Height	58,5 mm
Height	2,3 in
Width	5 mm
Width	0,197 in
Depth	64 mm
Depth	2,52 in
Strip length from	8 mm
Strip length to	9 mm
Strip length	0,33 in

© WAGO Kontakttechnik GmbH & Co. KG
 Specifications are subject to changes and errors may be expected