

Specifications

Photo is representative

Eaton EFS3190

Eaton Crouse-Hinds series EFS pushbutton control station, With pushbuttons, With one 1" hub, Feraloy iron alloy, Two circuit universal, 2, 2, Single-gang, 2, Dead end, 1", 600 Vac

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series EFS pushbutton control station
CATALOG NUMBER	EFS3190
UPC	782274285702
PRODUCT LENGTH/DEPTH	3.5 in
PRODUCT HEIGHT	5.91 in
PRODUCT WIDTH	5.25 in
PRODUCT WEIGHT	8.4 lb



Powering Business Worldwide

Certifications and compliances

AREA CLASSIFICATION	Hazardous/Classified Locations
STANDARDS TYPE	NEC/CEC
NEC HAZARDOUS RATING	Class I, Division 1 Class I, Division 2 Class II, Division 1 Class II, Division 2 Class III
NEMA RATING	3 7 9

Resources

3D MODELS	SP3D Design Package - EDS and EFS Explosionproof Control Stations
CATALOGS	EFS explosionproof control stations for group B applications - catalog page
CERTIFICATION REPORTS	EDS and EFS Explosionproof Pushbutton, Pilot Light, and Selector Switch Control Stations Canadian certification EDS and EFS Explosionproof Pushbutton, Pilot Light, and Selector Switch Control Stations UL certification
INSTALLATION INSTRUCTIONS	IF 899 - EDSX, EDS, EFS, DSDX and DSD Control Stations IF 328 - EDS, EFS, EDSC and EFSC Single- and Two-gang Device Bodies
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - EFS3190

Product specifications

ENCLOSURE TYPE	With pushbuttons
VOLTAGE RATING	600 Vac
NUMBER OF GANGS	Single-gang
NUMBER OF PUSHBUTTONS	2
NUMBER OF DEVICES	2
NORMAL POSITION	Two circuit universal
STYLE	Dead end
TRADE SIZE	1"
NUMBER OF CIRCUITS	2
HUB STYLE	With one 1" hub
MATERIAL	Feraloy iron alloy

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

