



PANEL MOUNTING

PANEL THICKNESS	(X) DIM.
1.19 TO 2.30	15.70 TO 15.75
2.31 TO 3.18	15.75 TO 15.88




FRAME COLOR: BLACK





SWITCH FUNCTION	
POS. 1	POS. 2
ON	(ON)
1-3, 4-6	1-2, 4-5

(ON)=MOMENTARY



NOTE:

- ALL DIMENSIONS IN MM [INCH]
- GENERAL TOLERANCE: $X.X = \pm 0.4$
 $X.XX = \pm 0.25$
- TERMINAL NUMBERS FOR REF ONLY
- PLATING MATERIAL: GOLD
- RATING: 0.4VA MAX. @ 20VDC OR AC
- ELECTRIC LIFE: 6,000 MAKE-AND-BREAK CYCLES AT FULL LOAD
- MECHANICAL LIFE: 50,000 CYCLES
- INSULATION RESISTANCE: 1,000 MΩ MIN.
- ACTUATION FORCE: $800 \pm 200\text{gf}$
- TRAVEL: $1.0 \pm 0.2\text{mm}$
- CONTACT RESISTANCE: 20 mΩ MAX.
TYPICAL @ 2-4 VDC
- DIELECTRIC STRENGTH: 1,000 V RMS @ SEA LEVEL.
- OPERATING TEMP.: -40°C to 85°C
- ▲ DENOTES CRITICAL PARAMETER.



REV	ECO NO	DESCRIPTION	DATE	BY	E-SWITCH®				OBJECT ID
D	ECO-102897	700 SERIES UPDATE	09/03/24	JS	TITLE 700DP7M1REAP2BLKBLK				000025789
					SCALE 2:1	DATE 7/27/2011	DR PH	DWG T721010	REV D

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED