





RECOMMENDED PANEL CUTOUT
 MAX. PANEL THICKNESS 10mm




SWITCH FUNCTION	
POS. 1	POS. 2
OFF	(ON)
OPEN	1-2

(ON) = MOMENTARY



NOTE:

- ALL DIMENSIONS IN MM [INCH]
- GENERAL TOLERANCE: X.X = ± 0.4
 X.XX = ± 0.25
- TERMINAL NUMBERS FOR REF ONLY
- ▲ 4. CONTACT MATERIAL: SILVER
5. RATING: 2A 48VDC
6. ELECTRICAL LIFE: 50,000 MAKE-AND-BREAK CYCLES
 AT FULL LOAD.
7. INSULATION RESISTANCE: 1,000M Ω MIN.
8. DIELECTRIC STRENGTH: 2,000VAC MIN. FOR 1 MINUTE
9. CONTACT RESISTANCE: 50m Ω MAX. @ 1A 12VDC
10. OPERATING TEMP.: -40°C to 85°C
11. TRAVEL: 1.8mm
12. ▲ DENOTES CRITICAL PARAMETER.
13. ILLUMINATION VOLTAGE: 1.8V
14. INGRESS PROTECTION: IP65
15. HARDWARE SUPPLIED: O-RING AND HEXNUT (NOT SHOWN)



REV	ECO NO	DESCRIPTION	DATE	BY	E-SWITCH®				OBJECT ID
E	ECO-103458	PRINT UPDATE	06/27/25	JS	TITLE PV6F240SS-221				000002855
					SCALE	DATE	DR	DWG	REV
					2:1	10/24/2011	BMA	52-PV6F240SS221	E

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO
 E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED