

Product data sheet

Specifications



Relay, SE Relays, solid state, SPST NO, 25A, 24V to 280V AC, 90V to 280V AC Uc, SCR AC zero cross, screw terminal

6225AXXSZS-AC90

⚠ Discontinued

⚠ Discontinued on: Dec 1, 2023

Product availability: Stock - Normally stocked in distribution facility

Main

Range	Legacy
Product Type	Solid state relay
maximum output current	25 A AC
Mounting Support	Panel
Network Number of Phases	1 phase
Output Voltage	24...280 V AC
Control Circuit Voltage	90...280 V AC

Complementary

Input Impedance	13000 Ohm
Holding Current	120 mA
Input Current Limits	11 mA at 120 V AC typical 20 mA at 240 V AC
Switch Function	SPST
Contacts Type and Composition	NO
Protection Technology	Current limiter
Tightening Torque	10 lb.in for input 20 lb.in for output
Connections Terminals	Input screw clamp terminal, 1 Output screw clamp terminals, 1
Screw Type	M3.5 M6
Local Signalling	1 LED (green) for input status
Switching Device	SCR output Zero voltage switching
Maximum Peak Voltage	600 V
Surge Current	250 A 16.6 ms
Must Release Voltage	10 V
Voltage Drop	<1.6 V on-state AC
Power Factor	1 with maximum load
Insulating Resistance	1 GΩ

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Thermal Resistance	1.02 °C/W
Maximum I²t for fusing	312 A².s 8.3 ms
Leakage Current	8 mA at off-state
DV/dt	500 V/µs off-state at maximum rated voltage
Response Time	8.33 ms (turn-on) 8.33 ms (turn-off)
Dielectric Strength	4000 V between input and ground 4000 V between output and ground 4000 V between input and output
Height	1.4 in (35.3 mm)
Width	1.9 in (47.1 mm)
Depth	2.3 in (58.4 mm)
Product Weight	3.05 oz (86.5 g)

Environment

Product Certifications	UL CSA CE
IP Degree of Protection	IP20
Ambient Air Temperature for Operation	-40...176 °F (-40...80 °C)
Ambient Air Temperature for Storage	-40...257 °F (-40...125 °C)

Ordering and shipping details

Category	US10CP222375
Discount Schedule	0CP2
GTIN	3606480277306
Returnability	Yes
Country of origin	IN

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.28 in (5.791 cm)
Package 1 Width	1.71 in (4.342 cm)
Package 1 Length	1.74 in (4.414 cm)
Package 1 Weight	3.05 oz (86.5 g)

 Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Use Better

 Materials and Substances	
Packaging without single use plastic	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	134201bc-d293-4667-9cca-10a7f11729e0
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Use Again

 Repack and remanufacture	
WEEE	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

