



ELECTRONICS, INC.
44 FARRAND STREET
BLOOMFIELD, NJ 07003
(973) 748-5089
<http://www.nteinc.com>

NTE74HC574 **Integrated Circuit** **TTL – High Speed CMOS,** **Octal D-Type Flip-Flop with 3-State Outputs** **Common Output Control and Common Clock**

Description:

The NTE74HC574 is a high speed octal D-type flip-flop with 3-state outputs in a 20-Lead DIP type package with the capability to drive 15 LS-TTL loads. The eight edge-triggered flip-flops enter data into their registers on the LOW to HIGH transition of clock (CP). The output enable ($\overline{OE}$) controls the 3-state outputs and is independent of the register operation. When $\overline{OE}$ is HIGH, the outputs are in the high-impedance state.

Features:

- Wide Power Supply Range: 2V to 6V
- High Noise Immunity: $N_{IL} = 30\%$, $N_{IH} = 30\%$ of V_{CC} at $V_{CC} = 5V$
- Buffered Inputs
- Common Three-State Output Enable Control
- Three-State Outputs
- Bus Line Driving Capability
- Typical Propagation Delay (Clock to Q): 15ns at $V_{CC} = 5V$, $C_L = 15pF$, $T_A = +25^\circ C$
- Fanout (Over Temperature Range):
 - Standard Outputs . . . 10 LS-TTL Loads
 - Bus Driver Outputs . . 15 LS-TTL Loads

Absolute Maximum Ratings: (Note 1, Note 2)

Supply Voltage, V_{CC}	-0.5 to +7.0V
Clamp Diode Current, I_{IK} , I_{OK}	$\pm 20mA$
DC Drain Current (Per Output), I_{OUT}	$\pm 35mA$
DC Output Source or Sink Current (Per Output), I_{OUT}	$\pm 25mA$
DC V_{CC} or GND Current (Per Pin), I_{CC}	$\pm 50mA$
Maximum Junction, T_J	+150°C
Storage Temperature Range, T_{stg}	-65°C to +150°C
Typical Thermal Resistance, Junction-to-Ambient, R_{thJA}	69°C/W
Lead Temperature (During Soldering, 10sec), T_L	+300°C

Note 1. Absolute Maximum Ratings are those values beyond which damage to the device may occur.

Note 2. Unless otherwise specified, all voltages are referenced to GND.

Recommended Operating Conditions:

Parameter	Symbol	Min	Typ	Max	Unit
Supply Voltage	V_{CC}	2.0	–	6.0	V
DC Input or Output Voltage	V_{IN}, V_{OUT}	0	–	V_{CC}	V
Operating Temperature Range	T_A	–40	–	+85	°C
Input Rise or Fall Times $V_{CC} = 2.0V$	t_r, t_f	–	–	1000	ns
$V_{CC} = 4.5V$		–	–	500	ns
$V_{CC} = 6.0V$		–	–	400	ns

DC Electrical Characteristics:

Parameter	Symbol	Test Conditions		V _{CC}	T _A = +25°C		T _A = −40° to +85°C	Unit
					Typ	Guaranteed Limits		
Minimum HIGH Level Input Voltage	V _{IH}			2.0	–	1.5	1.5	V
				4.5	–	3.15	3.15	V
				6.0	–	4.2	4.2	V
Maximum LOW Level Input Voltage	V _{IL}			2.0	–	0.5	0.5	V
				4.5	–	1.35	1.35	V
				6.0	–	1.8	1.8	V
Minimum HIGH Level Output Voltage	V _{OH}	V _{IN} = V _{IH} or V _{IL}	I _{OUT} = −20μA	–	V _{CC}	V _{CC} ^{−0.1}	V _{CC} ^{−0.1}	V
			I _{OUT} = −6mA	4.5	–	3.98	3.84	V
			I _{OUT} = −7.8mA	6.0	–	5.48	5.34	V
Minimum LOW Level Output Voltage	V _{OL}	V _{IN} = V _{IH} or V _{IL}	I _{OUT} = 20μA	–	–	0.1	0.1	V
			I _{OUT} = 6mA	4.5	0.2	0.26	0.33	V
			I _{OUT} = 7.8mA	6.0	0.2	0.26	0.33	V
Maximum Input Leakage Current	I _{IN}	V _{IN} = V _{CC} or GND		6.0	–	±0.1	±1.0	μA
Maximum Quiescent Supply Current	I _{CC}	V _{IN} = V _{CC} or GND, I _{OUT} = 0μA		6.0	–	8.0	80	μA
Three-State Leakage Current	I _{OZ}	V _{IN} = V _{IH} or V _{IL}		6.0	–	±0.5	±5.0	μA

Prerequisite for Switching Specifications:

Parameter	Symbol	Test Conditions	V _{CC}	T _A = +25°C		T _A = −40° to +85°C	Unit
				Typ	Guaranteed Limits		
Maximum Clock Frequency	f _{MAX}		2.0	–	6	5	MHz
			4.5	–	30	25	MHz
			6.0	–	35	29	MHz
Clock Pulse Width	t _W		2.0	–	80	100	ns
			4.5	–	16	20	ns
			6.0	–	14	17	ns
Setup Time (Data to Clock)	t _{SU}		2.0	–	60	75	ns
			4.5	–	12	15	ns
			6.0	–	10	13	ns
Hold Time (Data to Clock)	t _H		2.0	–	5	5	ns
			4.5	–	5	5	ns
			6.0	–	5	5	ns

Switching Specifications: ($t_r = t_f = 6\text{ns}$ unless otherwise specified)

Parameter	Symbol	Test Conditions	V _{CC}	T _A = +25°C		T _A = −40° to +85°C	Unit
				Typ	Guaranteed Limits		
Propagation Delay Time (Clock to Output)	t _{PLH} , t _{PHL}	C _L = 50pF	2.0	–	165	205	ns
			4.5	–	33	41	ns
		C _L = 15pF	5.0	15	–	–	ns
		C _L = 50pF	6.0	–	28	35	ns
Propagation Delay Time (Disable to Q)	t _{PLZ} , t _{PHZ}	C _L = 50pF	2.0	–	135	170	ns
			4.5	–	27	34	ns
		C _L = 15pF	5.0	11	–	–	ns
		C _L = 50pF	6.0	–	23	29	ns
Propagation Delay Time (Output Enable to Q)	t _{PZL} , t _{PZH}	C _L = 50pF	2.0	–	150	190	ns
			4.5	–	30	38	ns
		C _L = 15pF	5.0	12	–	–	ns
		C _L = 50pF	6.0	–	26	33	ns
Maximum Clock Frequency	f _{MAX}	C _L = 15pF	5.0	60	–	–	MHz
Output Transition Time	t _{TLH} , t _{THL}	C _L = 50pF	2.0	–	60	75	ns
			4.5	–	12	15	ns
			6.0	–	10	13	ns
Maximum Input Capacitance	C _{IN}		–	–	10	10	pF
Minimum Three-State Output Capacitance	C _O		–	–	20	20	pF
Power Dissipation Capacitance	C _{PD}	C _L = 15pF, Note 3	5.0	39	–	–	pF

Note 3. C_{PD} is used to determine the dynamic power consumption, per channel.

$$P_D = C_{PD} V_{CC}^2 f_i + \sum V_{CC}^2 f_o C_L \text{ where } f_i = \text{Input Frequency, } f_o = \text{Output Frequency,}$$

$C_L = \text{Output Load Capacitance, } V_{CC} = \text{Supply Voltage.}$

Truth Table:

Inputs			Output
$\overline{OE}$	CP	Data D_n	Q_n
L	↑	H	H
L	↑	L	L
L	L	X	Q0
H	X	X	Z

H = HIGH Level (Steady State)

L = LOW Level (Steady State)

X = Don't Care

↑ = Transition from LOW to HIGH Level

Q0 = The level of Q before the indicated steady state input conditions were established.

Z = High Impedance State

Pin Connection Diagram

