


SHEET 1 OF 1



RECOMMENDED PANEL CUTOUT MAX. PANEL THICKNESS 10.0 [.315 in]




() = MOMENTARY






- 1. ALL DIMENSIONS IN MM [INCH]
- 2. GENERAL TOLERANCE: X.X = ±0.4 $X.XX = \pm 0.25$
- 3. TERMINAL NUMBERS FOR REF ONLY
- ▲ 4. CONTACT MATERIAL: GOLD PLATED
- 5. RATING: 2A 48VDC
- 6. ELECTRIC LIFE: 200,000 MAKE-AND-BREAK CYCLES AT FULL LOAD.
- 7. INSULATION RESISTANCE: 1.000 MΩ MIN.
- 8. DIELECTRIC STRENGTH: 2.000 VAC MIN. FOR 1 MINUTE
- 9. CONTACT RESISTANCE: 50mΩ MAX. @ 1A 12VDC
- 10. OPERATING TEMP.: -20°C to 55°C
- 11. TRAVEL: 1.8mm
- 12. A DENOTES CRITICAL PARAMETER.
- ▲ 13. ILLLUMINATION VOLTAGE: 1.8V 20mA FORWARD, 2.8V 20mA REVERSE
- ▲ 14. HARDWARE SUPPLIED: O-RING AND HEXNUT (NOT SHOWN)







Α	23014	INITIAL RELEASE	10/2/17	MW			
REV	PCR NO	DESCRIPTION	DATE	BY			
THE INFORMATION CONTAINED IN THIS DOCLIMENT IS PROPRIETARY							

TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

E+SWITCH®									
TITLE PV6F240SSG-3G1-M01									
SCALE 2:1	DATE 10/2/2017	DR MW	DWG 52-PV6S00264	REV A					