

6

5

4

3

2

1

MATERIAL AND FINISH:

Insulator: Polycarbonate, UL-94V-0 rated

Contacts: Brass

Screw: Brass, Nickel Plated over Copper

Nut: Brass, Nickel Plated

ELECTRICAL SPECIFICATIONS:

Current rating: 10 A/15 A

Voltage rating: 250 VAC

Insulation resistance: 100 Mohm min. at 500 VDC

Dielectric withstanding voltage: 2000 VAC for one minute

ORDERING CODE:

43R02-1 $\frac{1}{1}$ $\frac{1}{2}$

1) COLOR

1 = BLACK





2 = GRAY

2) ELECTRICAL CIRCUIT CONFIGURATION

1 = 10A 250V 70°C 15A 250V 70°C  

2+GROUND

2 = 10A 250V 120°C

15A 250V 120°C 2+GROUND RoHS
COMPLIANT

TOLERANCE
UNLESS OTHERWISE SPECIFIED
X ± 1
X.X ± 0.4
X.XX ± 0.20

Power Dynamics, Inc.

Phone: 973 560-0019 Whippary, New Jersey Fax: 973 560-0076

PART: 10A/15A IEC 60320 APPL. OUTLET; SCREW
TERMINALS; SIDE FLANGE, PANEL MOUNTPART #: **43R02-1X1X**SHEET
1 of 1

DRAWN BY GQ DATE: 10/04/01
CHECK BY TD DATE: 10/09/01
APPR BY PB DATE: 10/09/01

SIZE: A
SCALE: NTS
ALL DIMENSIONS FOR REFERENCE ONLY
DIMENSIONS ARE IN MILLIMETERS

REV:

REVISIONS

CHANGE

DATE

REV

CHNG CHECK APPR

6

5

4

3

2

1