#### **Straight Blade Devices**

## 20A, 125V, 2 Pole, 3 Wire Grounding

# **HBL®** Extra Heavy Duty MAX Specification Grade **Duplex Receptacle**

## **Features**

- Back wired ground terminal allows faster, easier installation
- One-piece brass integral ground strap
- Finder Groove Face
- Deep body design with circuit ID face

### **Ordering Information**

Description **Device Color** Deep body design with circuit Blue ID face. Back and side wired.

**UPC Number** 783585357584

Catalog Number HBL5362BL

#### Listings

UL Listed to UL498 File No. E2186 Certified to CSA 22.2, No. 42 File 285 Fed. Spec. W-C-596 **NEMA® WD-6 Compliant** 

#### **Specifications**

Face Nylon **PBT** Base


.036". (.9) Brass By-Pass Power Contacts **Ground Contacts** .031 in. (.8) Brass Clamping Plate Nickel plated brass **Terminal Screws** Plated brass Mounting Strap .050 in. (1.3) Brass Automatic Self-grounding Clip Stainless steel Mounting Screws Zinc plated steel



20A 125V NEMA 5-20R UL CSA 1 HP



HUBBELL



#### **Performance**

## **Electrical**

**Current Interrupting** Certified for current interrupting at full rated

current

Dielectric Voltage Withstands 2,000V minimum

Mechanical

**Product Identification** Ratings are a permanent part of the device #14-#10 AWG copper stranded or solid **Terminal Accommodation** 

conductor only

Terminal Identification Terminals identified in accordance with UL 498

and CSA

**Environmental** 

Flammability Top: UL 94V-2, Base: UL 94V-0

**Operating Temperatures** Maximum continuous 75°C; minimum -40°C (w/o

impact)

## **Complementary Products**

Wallplate or Weatherproof Cover

**Duplex Opening** 

#### **Online Resources**

**Customer Sales Drawings** 

eCatalog

Installation Instructions

