



7/8" MIN Series Size I Receptacles

2, 3, 4, 5 & 6 Conductor MIN Series Size I Receptacles, 18/22AWG



Front Mount Receptacles | M20 x 1.5 Threads | IP69 Rating



A

MIN Series Size I Receptacles

# of Poles	Male Faceview	Color Code	Rating	Wire AWG	Male Receptacles	Female Receptacles
2	 7/8"-16UN2	North American 1. White 2. Black	300V 10A	18 AWG	MIN-2MR-1-18-M20	MIN-2FR-1-18-M20
			300V 4A	22 AWG	MIN-2MR-1-22-M20	MIN-2FR-1-22-M20
3	 7/8"-16UN2	North American 1. Green/Yellow 2. Black 3. White	300V 10A	18 AWG	MIN-3MR-1-18-M20	MIN-3FR-1-18-M20
			300V 4A	22 AWG	MIN-3MR-1-22-M20	MIN-3FR-1-22-M20
4	 7/8"-16UN2	North American 1. Black 2. White 3. Red 4. Green/Yellow	300V 8A	18 AWG	MIN-4MR-1-18-M20	MIN-4FR-1-18-M20
			300V 4A	22 AWG	MIN-4MR-1-22-M20	MIN-4FR-1-22-M20
5	 7/8"-16UN2	North American 1. White 2. Red 3. Green/Yellow 4. Orange 5. Black	300V 5.5A	18 AWG	MIN-5MR-1-18-M20	MIN-5FR-1-18-M20
			300V 4A	22 AWG	MIN-5MR-1-22-M20	MIN-5FR-1-22-M20
6	 7/8"-16UN2	North American 1. White 2. Red 3. Green/Yellow 4. Orange 5. Black 6. Blue	300V 5.5A	18 AWG	MIN-6MR-1-18-M20	MIN-6FR-1-18-M20
			300V 3A	22 AWG	MIN-6MR-1-22-M20	MIN-6FR-1-22-M20

12" leads are standard. Longer lead lengths are available, please consult the factory for part numbers.

Standard shell is anodized aluminum, for stainless steel shell add a "-SS" suffix. (e.g. MIN-3MR-1-18-M20 becomes MIN-3MR-1-18-M20-SS)

Specifications:

Shell: Clear Anodized Aluminum
Insulator: 105°C, Oil Resistant Yellow PVC
Wire: 18 & 22 AWG: UL Style 1007/1569, 300V
Contacts: Copper Alloy with Gold Plating
O-Ring: NBR
Jam Nut: Nickel Plated Brass
Temperature: -40°C to 105°C (-40°F to +221°F)

