

DESCRIPTION: MALE // HD DSUB // CRIMP AND POKE


SPECIFICATIONS:

ELECTRICAL:	
INSULATION RESISTANCE:	1,000 MOhms MIN.
OPERATING TEMPERATURE:	-50°C TO +100°C
VOLTAGE:	500 VAC FOR 1 MINUTE
MATERIALS:	
INSULATOR:	PBT +30% GF, UL94 V-0
PROCESS TEMP:	230°C
SHELL:	NICKEL PLATED STEEL

COMPATIBLE WITH NORCOMP CONTACT PART NUMBERS BELOW:

180-001-170L001	180-101-170L001
180-201-170L002	

****NOTE: CONTACTS MUST BE PURCHASED SEPARATELY****



180-YYY-17YLYY0

SERIES	180-YYY-17YLYY0
POSITIONS	015
	026
	044
	062
	078
GENDER	1 = MALE
TERMINATION	7 = CRIMP & POKE
SHELL PLATING	2 = TIN (DISCONTINUED)
	3 = NICKEL (GROUND INDENTS)
HARDWARE OPTIONS	00 = NO HARDWARE
	01 = .157" CLINCH NUT (SOLDER SIDE)
	02 = .250" CLINCH NUT (SOLDER SIDE)
	03 = .250" CLINCH NUT (MATING SIDE)
PLATING OPTIONS	0 = NO CONTACTS

		DIMENSIONS							
No. OF PINS	UNITS	A	B	C	D	E	F	G	H
15	inch	1.213	0.984	0.666	0.323	0.610	0.759	0.494	0.421
	mm	30.81	24.99	16.92	8.20	15.50	19.28	12.55	10.70
26	inch	1.541	1.312	0.994	0.323	0.964	1.083	0.494	0.421
	mm	39.14	33.32	25.25	8.20	24.50	27.51	12.55	10.70
44	inch	2.088	1.852	1.534	0.323	1.494	1.618	0.494	0.421
	mm	53.04	47.04	38.96	8.20	37.95	41.10	12.55	10.70
62	inch	2.729	2.500	2.182	0.319	2.142	2.272	0.494	0.421
	mm	69.32	63.50	55.42	8.10	54.40	57.71	12.55	10.70
4 ROWS 78	inch	2.644	2.406	2.081	0.439	2.035	2.169	0.605	0.527
	mm	67.16	61.11	52.86	11.15	51.70	55.10	15.37	13.40

RoHS COMPLIANT

DRAWN: P. JENKINS
DATE: 07/19/2005

UNITS = inch [mm]

DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.


NorComp

SCALE: NTS	SHEET 1	OF 2	REV 25
DWG NO.	180-YYY-17YLYY0		


ALL CLINCH-NUTS ARE 4-40 INTERNAL THREADS

TOLERANCE:
ALL DIMENSIONS ARE ±0.010


01 0.157" (SOLDER SIDE)



02 0.250" (SOLDER SIDE)



03 0.250" (MATING SIDE)



RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:
P. JENKINS
DATE:
07/19/2005

UNITS = inch [mm]

DO NOT SCALE FROM DRAWING

NorComp

SCALE: NTS SHEET 2 OF 2 REV 25

DWG NO. 180-YYY-17YLYY0