

# 3-STATE Octal D-Type Latch

## MM74HC573

### General Description

The MM74HC573 high speed octal D-type latches utilize advanced silicon-gate P-well CMOS technology. They possess the high noise immunity and low power consumption of standard CMOS integrated circuits, as well as the ability to drive 15 LS-TTL loads. Due to the large output drive capability and the 3-STATE feature, these devices are ideally suited for interfacing with bus lines in a bus organized system.

When the LATCH ENABLE (LE) input is HIGH, the Q outputs will follow the D inputs. When the LATCH ENABLE goes LOW, data at the D inputs will be retained at the outputs until LATCH ENABLE returns HIGH again. When a high logic level is applied to the OUTPUT CONTROL OC input, all outputs go to a high impedance state, regardless of what signals are present at the other inputs and the state of the storage elements.

The 74HC logic family is speed, function, and pinout compatible with the standard 74LS logic family. All inputs are protected from damage due to static discharge by internal diode clamps to  $V_{CC}$  and ground.

### Features

- Typical Propagation Delay: 16 ns
- Wide Operating Voltage Range: 2 to 6 V
- Low Input Current: 1  $\mu$ A Maximum
- Low Quiescent Current: 160  $\mu$ A Maximum (74HC Series)
- Compatible with Bus-oriented Systems
- Output Drive Capability: 15 LS-TTL Loads
- This is a Pb-Free Device

### TRUTH TABLE

| Output Control | Latch Enable | Data | Output |
|----------------|--------------|------|--------|
| L              | H            | H    | H      |
| L              | H            | L    | L      |
| L              | L            | X    | $Q_0$  |
| H              | X            | X    | Z      |

NOTES: H = HIGH Level

L = LOW Level

$Q_0$  = Level of output before steady-state input conditions were established.

Z = High Impedance

X = Don't Care



SOIC-20 WB  
CASE 751D-05




SOIC-20, 300 mils  
CASE 751BJ



TSSOP-20 WB  
CASE 948E

### MARKING DIAGRAMS



XXXXX = Specific Device Code

A = Assembly Location

WL, L = Wafer Lot


YY, Y = Year

WW, W = Work Week

G, ■ = Pb-Free Package

(Note: Microdot may be in either location)

### CONNECTION DIAGRAM



(Top View)

### ORDERING INFORMATION

See detailed ordering and shipping information on page 5 of this data sheet.

# MM74HC573

## ABSOLUTE MAXIMUM RATINGS (Note 1)

| Symbol           | Rating                                  | Value                  | Unit |
|------------------|-----------------------------------------|------------------------|------|
| $V_{CC}$         | Supply Voltage                          | -0.5 to +6.5           | V    |
| $V_{IN}$         | DC Input Voltage                        | -0.5 to $V_{CC} + 0.5$ | V    |
| $V_{OUT}$        | DC Output Voltage                       | -0.5 to $V_{CC} + 0.5$ | V    |
| $I_{IK}, I_{OK}$ | Clamp Diode Current                     | $\pm 20$               | mA   |
| $I_{OUT}$        | DC Output Current, per pin              | $\pm 35$               | mA   |
| $I_{CC}$         | DC $V_{CC}$ or GND Current, per pin     | $\pm 70$               | mA   |
| $T_{STG}$        | Storage Temperature Range               | -65 to +150            | °C   |
| $P_D$            | Power Dissipation<br>SOIC<br>TSSOP      | 1302<br>833            | mW   |
| $T_L$            | Lead Temperature (Soldering 10 seconds) | 260                    | °C   |

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1. Unless otherwise specified all voltages are referenced to ground.

## RECOMMENDED OPERATING CONDITIONS

| Symbol            | Parameter                   | Min                     | Max      | Unit |
|-------------------|-----------------------------|-------------------------|----------|------|
| $V_{CC}$          | Supply Voltage              | 2                       | 6        | V    |
| $V_{IN}, V_{OUT}$ | DC Input or Output Voltage  | 0                       | $V_{CC}$ | V    |
| $T_A$             | Operating Temperature Range | -55                     | +125     | °C   |
| $t_r, t_f$        | Input Rise or Fall Times    | $V_{CC} = 2.0\text{ V}$ | 1000     | ns   |
|                   |                             | $V_{CC} = 4.5\text{ V}$ | 500      | ns   |
|                   |                             | $V_{CC} = 6.0\text{ V}$ | 400      | ns   |

Functional operation above the stresses listed in the Recommended Operating Ranges is not implied. Extended exposure to stresses beyond the Recommended Operating Ranges limits may affect device reliability.

# MM74HC573

## DC ELECTRICAL CHARACTERISTICS (Note 2)

| Symbol           | Parameter                              | Conditions                                                                                                           | V <sub>CC</sub> | T <sub>A</sub> = 25°C |                   | T <sub>A</sub> = -40 to 85°C | T <sub>A</sub> = -55 to 125°C | Unit |
|------------------|----------------------------------------|----------------------------------------------------------------------------------------------------------------------|-----------------|-----------------------|-------------------|------------------------------|-------------------------------|------|
|                  |                                        |                                                                                                                      |                 | Typ                   | Guaranteed Limits |                              |                               |      |
| V <sub>IH</sub>  | Minimum HIGH Level Input Voltage       |                                                                                                                      | 2.0 V           |                       | 1.5               | 1.5                          | 1.5                           | V    |
|                  |                                        |                                                                                                                      | 4.5 V           |                       | 3.15              | 3.15                         | 3.15                          | V    |
|                  |                                        |                                                                                                                      | 6.0 V           |                       | 4.2               | 4.2                          | 4.2                           | V    |
| V <sub>IL</sub>  | Maximum LOW Level Input Voltage        |                                                                                                                      | 2.0 V           |                       | 0.5               | 0.5                          | 0.5                           | V    |
|                  |                                        |                                                                                                                      | 4.5 V           |                       | 1.35              | 1.35                         | 1.35                          | V    |
|                  |                                        |                                                                                                                      | 6.0 V           |                       | 1.8               | 1.8                          | 1.8                           | V    |
| V <sub>OH</sub>  | Minimum HIGH Level Output Voltage      | V <sub>IN</sub> = V <sub>IH</sub> or V <sub>IL</sub><br> I <sub>OUT</sub>   ≤ 20 μA                                  | 2.0 V           | 2.0                   | 1.9               | 1.9                          | 1.9                           | V    |
|                  |                                        |                                                                                                                      | 4.5 V           | 4.5                   | 4.4               | 4.4                          | 4.4                           | V    |
|                  |                                        |                                                                                                                      | 6.0 V           | 6.0                   | 5.9               | 5.9                          | 5.9                           | V    |
|                  |                                        | V <sub>IN</sub> = V <sub>IH</sub> or V <sub>IL</sub><br> I <sub>OUT</sub>   ≤ 6.0 mA<br> I <sub>OUT</sub>   ≤ 7.8 mA | 4.5 V           | 4.2                   | 3.98              | 3.84                         | 3.7                           | V    |
|                  |                                        |                                                                                                                      | 6.0 V           | 5.7                   | 5.48              | 5.34                         | 5.2                           | V    |
|                  |                                        |                                                                                                                      |                 |                       |                   |                              |                               |      |
| V <sub>OL</sub>  | Maximum LOW Level Output Voltage       | V <sub>IN</sub> = V <sub>IH</sub> or V <sub>IL</sub><br> I <sub>OUT</sub>   ≤ 20 μA                                  | 2.0 V           | 0                     | 0.1               | 0.1                          | 0.1                           | V    |
|                  |                                        |                                                                                                                      | 4.5 V           | 0                     | 0.1               | 0.1                          | 0.1                           | V    |
|                  |                                        |                                                                                                                      | 6.0 V           | 0                     | 0.1               | 0.1                          | 0.1                           | V    |
|                  |                                        | V <sub>IN</sub> = V <sub>IH</sub> or V <sub>IL</sub><br> I <sub>OUT</sub>   ≤ 6.0 mA<br> I <sub>OUT</sub>   ≤ 7.8 mA | 4.5 V           | 0.2                   | 0.26              | 0.33                         | 0.4                           | V    |
|                  |                                        |                                                                                                                      | 6.0 V           | 0.2                   | 0.26              | 0.33                         | 0.4                           | V    |
|                  |                                        |                                                                                                                      |                 |                       |                   |                              |                               |      |
| I <sub>IN</sub>  | Maximum Input Current                  | V <sub>IN</sub> = V <sub>CC</sub> or GND                                                                             | 6.0 V           |                       | ±0.1              | ±1.0                         | ±1.0                          | μA   |
| I <sub>OZ</sub>  | Maximum 3-STATE Output Leakage Current | V <sub>OUT</sub> = V <sub>CC</sub> or GND<br>OC = V <sub>IH</sub>                                                    | 6.0 V           |                       | ±0.5              | ±5.0                         | ±10                           | μA   |
| I <sub>CC</sub>  | Maximum Quiescent Supply Current       | V <sub>IN</sub> = V <sub>CC</sub> or GND<br>I <sub>OUT</sub> = 0 μA                                                  | 6.0 V           |                       | 8.0               | 80                           | 160                           | μA   |
| ΔI <sub>CC</sub> | Quiescent Supply Current per Input Pin | V <sub>CC</sub> = 5.5 V<br>V <sub>IN</sub> = 2.4 V or 0.4 V (Note 2)                                                 | OE              | 1.0                   | 1.5               | 1.8                          | 2.0                           | mA   |
|                  |                                        |                                                                                                                      | LE              | 0.6                   | 0.8               | 1.0                          | 1.1                           | mA   |
|                  |                                        |                                                                                                                      | DATA            | 0.4                   | 0.5               | 0.6                          | 0.7                           | mA   |

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

2. For a power supply of 5 V ±10% the worst case output voltages (V<sub>OH</sub>, and V<sub>OL</sub>) occur for HC at 4.5 V. Thus the 4.5 V values should be used when designing with this supply. Worst case V<sub>IH</sub> and V<sub>IL</sub> occur at V<sub>CC</sub> = 5.5 V and 4.5 V respectively. (The V<sub>IH</sub> value at 5.5 V is 3.85 V.) The worst case leakage current (I<sub>IN</sub>, I<sub>CC</sub>, and I<sub>OZ</sub>) occur for CMOS at the higher voltage and so the 6.0 V values should be used.

## AC ELECTRICAL CHARACTERISTICS

(V<sub>CC</sub> = 5 V, T<sub>A</sub> = 25°C, t<sub>r</sub> = t<sub>f</sub> = 6 ns)

| Symbol                              | Parameter                            | Conditions                                    | Typ | Guaranteed Limit | Unit |
|-------------------------------------|--------------------------------------|-----------------------------------------------|-----|------------------|------|
| t <sub>PHL</sub> , t <sub>PLH</sub> | Maximum Propagation Delay, Data to Q | C <sub>L</sub> = 45 pF                        | 16  | 20               | ns   |
| t <sub>PHL</sub> , t <sub>PLH</sub> | Maximum Propagation Delay, LE to Q   | C <sub>L</sub> = 45 pF                        | 14  | 22               | ns   |
| t <sub>PZH</sub> , t <sub>PZL</sub> | Maximum Output Enable Time           | R <sub>L</sub> = 1 kΩ, C <sub>L</sub> = 45 pF | 15  | 27               | ns   |
| t <sub>PHZ</sub> , t <sub>PLZ</sub> | Maximum Output Disable Time          | R <sub>L</sub> = 1 kΩ, C <sub>L</sub> = 5 pF  | 13  | 23               | ns   |
| t <sub>s</sub>                      | Minimum Set Up Time, Data to LE      |                                               | 10  | 15               | ns   |
| t <sub>H</sub>                      | Minimum Hold Time, LE to Data        |                                               | 2   | 5                | ns   |
| t <sub>W</sub>                      | Minimum Pulse Width, LE or Data      |                                               | 10  | 16               | ns   |

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

# MM74HC573

## AC ELECTRICAL CHARACTERISTICS

| Symbol                              | Parameter                                          | Conditions              | V <sub>CC</sub> | T <sub>A</sub> = 25°C |                   | T <sub>A</sub> = –40 to 85°C | T <sub>A</sub> = –55 to 125°C | Unit |
|-------------------------------------|----------------------------------------------------|-------------------------|-----------------|-----------------------|-------------------|------------------------------|-------------------------------|------|
|                                     |                                                    |                         |                 | Typ                   | Guaranteed Limits |                              |                               |      |
| t <sub>PHL</sub> , t <sub>PLH</sub> | Maximum Propagation Delay, Data to Q               | C <sub>L</sub> = 50 pF  | 2.0 V           | 45                    | 110               | 138                          | 165                           | ns   |
|                                     |                                                    | C <sub>L</sub> = 150 pF | 2.0 V           | 55                    | 150               | 188                          | 225                           | ns   |
|                                     |                                                    | C <sub>L</sub> = 50 pF  | 4.5 V           | 17                    | 22                | 28                           | 33                            | ns   |
|                                     |                                                    | C <sub>L</sub> = 150 pF | 4.5 V           | 21                    | 30                | 38                           | 40                            | ns   |
|                                     |                                                    | C <sub>L</sub> = 50 pF  | 6.0 V           | 15                    | 19                | 24                           | 29                            | ns   |
|                                     |                                                    | C <sub>L</sub> = 150 pF | 6.0 V           | 19                    | 26                | 33                           | 39                            | ns   |
| t <sub>PHL</sub> , t <sub>PLH</sub> | Maximum Propagation Delay, LE to Q                 | C <sub>L</sub> = 50 pF  | 2.0 V           | 46                    | 115               | 138                          | 165                           | ns   |
|                                     |                                                    | C <sub>L</sub> = 150 pF | 2.0 V           | 60                    | 155               | 194                          | 233                           | ns   |
|                                     |                                                    | C <sub>L</sub> = 50 pF  | 4.5 V           | 14                    | 23                | 29                           | 35                            | ns   |
|                                     |                                                    | C <sub>L</sub> = 150 pF | 4.5 V           | 21                    | 31                | 47                           | 47                            | ns   |
|                                     |                                                    | C <sub>L</sub> = 50 pF  | 6.0 V           | 12                    | 20                | 25                           | 30                            | ns   |
|                                     |                                                    | C <sub>L</sub> = 150 pF | 6.0 V           | 19                    | 27                | 34                           | 41                            | ns   |
| t <sub>PZH</sub> , t <sub>PZL</sub> | Maximum Output Enable Time                         | R <sub>L</sub> = 1 kΩ   |                 |                       |                   |                              |                               |      |
|                                     |                                                    | C <sub>L</sub> = 50 pF  | 2.0 V           | 55                    | 140               | 175                          | 210                           | ns   |
|                                     |                                                    | C <sub>L</sub> = 150 pF | 2.0 V           | 67                    | 180               | 225                          | 270                           | ns   |
|                                     |                                                    | C <sub>L</sub> = 50 pF  | 4.5 V           | 15                    | 28                | 35                           | 42                            | ns   |
|                                     |                                                    | C <sub>L</sub> = 150 pF | 4.5 V           | 24                    | 36                | 45                           | 54                            | ns   |
|                                     |                                                    | C <sub>L</sub> = 50 pF  | 6.0 V           | 14                    | 24                | 30                           | 36                            | ns   |
| t <sub>PHZ</sub> , t <sub>PLZ</sub> | Maximum Output Disable Time                        | R <sub>L</sub> = 1 kΩ   | 2.0 V           | 40                    | 125               | 156                          | 188                           | ns   |
|                                     |                                                    | C <sub>L</sub> = 50 pF  | 4.5 V           | 13                    | 25                | 31                           | 38                            | ns   |
|                                     |                                                    |                         | 6.0 V           | 12                    | 21                | 27                           | 32                            | ns   |
| t <sub>s</sub>                      | Minimum Set Up Time Data to LE                     |                         | 2.0 V           | 30                    | 75                | 95                           | 110                           | ns   |
|                                     |                                                    |                         | 4.5 V           | 10                    | 15                | 19                           | 22                            | ns   |
|                                     |                                                    |                         | 6.0 V           | 9                     | 13                | 16                           | 19                            | ns   |
| t <sub>H</sub>                      | Minimum Hold Time LE to Data                       |                         | 2.0 V           | –                     | 25                | 31                           | 38                            | ns   |
|                                     |                                                    |                         | 4.5 V           | –                     | 5                 | 6                            | 7                             | ns   |
|                                     |                                                    |                         | 6.0 V           | –                     | 4                 | 5                            | 6                             | ns   |
| t <sub>w</sub>                      | Minimum Pulse Width LE, or Data                    |                         | 2.0 V           | 30                    | 80                | 100                          | 120                           | ns   |
|                                     |                                                    |                         | 4.5 V           | 9                     | 16                | 20                           | 24                            | ns   |
|                                     |                                                    |                         | 6.0 V           | 8                     | 14                | 18                           | 20                            | ns   |
| t <sub>THL</sub> , t <sub>TLH</sub> | Maximum Output Rise and Fall Time, Clock           | C <sub>L</sub> = 50 pF  | 2.0 V           | 25                    | 60                | 75                           | 90                            | ns   |
|                                     |                                                    |                         | 4.5 V           | 7                     | 12                | 15                           | 18                            | ns   |
|                                     |                                                    |                         | 6.0 V           | 6                     | 10                | 13                           | 15                            | ns   |
| C <sub>PD</sub>                     | Power Dissipation Capacitance (Note 3) (per latch) | OC = V <sub>CC</sub>    | –               | 5                     | –                 | –                            | –                             | pF   |
|                                     |                                                    | OC = GND                | –               | 52                    | –                 | –                            | –                             | pF   |
| C <sub>IN</sub>                     | Maximum Input Capacitance                          |                         | –               | 5                     | 10                | 10                           | 10                            | pF   |
| C <sub>OUT</sub>                    | Maximum Output Capacitance                         |                         | –               | 15                    | 20                | 20                           | 20                            | pF   |

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

3. C<sub>PD</sub> determines the no load dynamic power consumption, P<sub>D</sub> = C<sub>PD</sub> V<sub>CC</sub><sup>2</sup>f + I<sub>CC</sub> V<sub>CC</sub>, and the no load dynamic current consumption, I<sub>S</sub> = C<sub>PD</sub> V<sub>CC</sub> f + I<sub>CC</sub>.

## MM74HC573


### ORDERING INFORMATION

| Device        | Marking    | Package                                        | Shipping <sup>†</sup>    |
|---------------|------------|------------------------------------------------|--------------------------|
| MM74HC573WM   | HC573A     | SOIC-20 WB<br>(Pb-Free and Halide Free)        | 38 Units / Tube          |
| MM74HC573WMX  | HC573A     | SOIC-20, 300 mils<br>(Pb-Free and Halide Free) | 1000 Units / Tape & Reel |
| MM74HC573MTC  | HC<br>573A | TSSOP-20 WB<br>(Pb-Free)                       | 75 Units / Tube          |
| MM74HC573MTCX | HC<br>573A | TSSOP-20 WB<br>(Pb-Free)                       | 2500 Units / Tape & Reel |

<sup>†</sup>For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, [BRD8011/D](#).


**SOIC-20, 300 mils**  
**CASE 751BJ**  
**ISSUE O**

DATE 19 DEC 2008




**TOP VIEW**

| SYMBOL     | MIN      | NOM   | MAX   |
|------------|----------|-------|-------|
| A          | 2.36     | 2.49  | 2.64  |
| A1         | 0.10     |       | 0.30  |
| A2         | 2.05     |       | 2.55  |
| b          | 0.31     | 0.41  | 0.51  |
| c          | 0.20     | 0.27  | 0.33  |
| D          | 12.60    | 12.80 | 13.00 |
| E          | 10.01    | 10.30 | 10.64 |
| E1         | 7.40     | 7.50  | 7.60  |
| e          | 1.27 BSC |       |       |
| h          | 0.25     |       | 0.75  |
| L          | 0.40     | 0.81  | 1.27  |
| $\theta$   | 0°       |       | 8°    |
| $\theta 1$ | 5°       |       | 15°   |



**SIDE VIEW**




**END VIEW**

**Notes:**

- (1) All dimensions are in millimeters. Angles in degrees.
- (2) Complies with JEDEC MS-013.

|                         |                          |                                                                                                                                                                                     |
|-------------------------|--------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>DOCUMENT NUMBER:</b> | <b>98AON34287E</b>       | Electronic versions are uncontrolled except when accessed directly from the Document Repository.<br>Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red. |
| <b>DESCRIPTION:</b>     | <b>SOIC-20, 300 MILS</b> | <b>PAGE 1 OF 1</b>                                                                                                                                                                  |



**onsemi** and **onsemi** are trademarks of Semiconductor Components Industries, LLC dba **onsemi** or its subsidiaries in the United States and/or other countries. **onsemi** reserves the right to make changes without further notice to any products herein. **onsemi** makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. **onsemi** does not convey any license under its patent rights nor the rights of others.



SCALE 1:1

SOIC-20 WB  
CASE 751D-05  
ISSUE H

DATE 22 APR 2015




NOTES:

1. DIMENSIONS ARE IN MILLIMETERS.
2. INTERPRET DIMENSIONS AND TOLERANCES PER ASME Y14.5M, 1994.
3. DIMENSIONS D AND E DO NOT INCLUDE MOLD PROTRUSION.
4. MAXIMUM MOLD PROTRUSION 0.15 PER SIDE.
5. DIMENSION B DOES NOT INCLUDE DAMBAR PROTRUSION. ALLOWABLE PROTRUSION SHALL BE 0.13 TOTAL IN EXCESS OF B DIMENSION AT MAXIMUM MATERIAL CONDITION.

| DIM | MILLIMETERS |       |
|-----|-------------|-------|
|     | MIN         | MAX   |
| A   | 2.35        | 2.65  |
| A1  | 0.10        | 0.25  |
| b   | 0.35        | 0.49  |
| c   | 0.23        | 0.32  |
| D   | 12.65       | 12.95 |
| E   | 7.40        | 7.60  |
| e   | 1.27 BSC    |       |
| H   | 10.05       | 10.55 |
| h   | 0.25        | 0.75  |
| L   | 0.50        | 0.90  |
| θ   | 0°          | 7°    |


RECOMMENDED  
SOLDERING FOOTPRINT\*



DIMENSIONS: MILLIMETERS

\*For additional information on our Pb-Free strategy and soldering details, please download the **onsemi** Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

GENERIC  
MARKING DIAGRAM\*




XXXXXX = Specific Device Code  
A = Assembly Location  
WL = Wafer Lot  
YY = Year  
WW = Work Week  
G = Pb-Free Package


\*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot "▪", may or may not be present. Some products may not follow the Generic Marking.

|                  |             |                                                                                                                                                                                     |
|------------------|-------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| DOCUMENT NUMBER: | 98ASB42343B | Electronic versions are uncontrolled except when accessed directly from the Document Repository.<br>Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red. |
| DESCRIPTION:     | SOIC-20 WB  | PAGE 1 OF 1                                                                                                                                                                         |

onsemi and onsemi are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.



**TSSOP-20 WB**  
**CASE 948E**  
**ISSUE D**

DATE 17 FEB 2016


**NOTES:**

1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
2. CONTROLLING DIMENSION: MILLIMETER.
3. DIMENSION A DOES NOT INCLUDE MOLD FLASH, PROTRUSIONS OR GATE BURRS. MOLD FLASH OR GATE BURRS SHALL NOT EXCEED 0.15 (0.006) PER SIDE.
4. DIMENSION B DOES NOT INCLUDE INTERLEAD FLASH OR PROTRUSION. INTERLEAD FLASH OR PROTRUSION SHALL NOT EXCEED 0.25 (0.010) PER SIDE.
5. DIMENSION K DOES NOT INCLUDE DAMBAR PROTRUSION. ALLOWABLE DAMBAR PROTRUSION SHALL BE 0.08 (0.003) TOTAL IN EXCESS OF THE K DIMENSION AT MAXIMUM MATERIAL CONDITION.
6. TERMINAL NUMBERS ARE SHOWN FOR REFERENCE ONLY.
7. DIMENSION A AND B ARE TO BE DETERMINED AT DATUM PLANE -W-.

| DIM | MILLIMETERS |      | INCHES    |       |
|-----|-------------|------|-----------|-------|
|     | MIN         | MAX  | MIN       | MAX   |
| A   | 6.40        | 6.60 | 0.252     | 0.260 |
| B   | 4.30        | 4.50 | 0.169     | 0.177 |
| C   | ---         | 1.20 | ---       | 0.047 |
| D   | 0.05        | 0.15 | 0.002     | 0.006 |
| F   | 0.50        | 0.75 | 0.020     | 0.030 |
| G   | 0.65 BSC    |      | 0.026 BSC |       |
| H   | 0.27        | 0.37 | 0.011     | 0.015 |
| J   | 0.09        | 0.20 | 0.004     | 0.008 |
| J1  | 0.09        | 0.16 | 0.004     | 0.006 |
| K   | 0.19        | 0.30 | 0.007     | 0.012 |
| K1  | 0.19        | 0.25 | 0.007     | 0.010 |
| L   | 6.40 BSC    |      | 0.252 BSC |       |
| M   | 0°          | 8°   | 0°        | 8°    |

**GENERIC MARKING DIAGRAM\***


- A = Assembly Location  
L = Wafer Lot  
Y = Year  
W = Work Week  
▪ = Pb-Free Package

(Note: Microdot may be in either location)

\*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot "▪", may or may not be present. Some products may not follow the Generic Marking.

\*For additional information on our Pb-Free strategy and soldering details, please download the onsemi Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

|                         |                    |                                                                                                                                                                                  |
|-------------------------|--------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>DOCUMENT NUMBER:</b> | <b>98ASH70169A</b> | Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red. |
| <b>DESCRIPTION:</b>     | <b>TSSOP-20 WB</b> | <b>PAGE 1 OF 1</b>                                                                                                                                                               |

onsemi and onsemi are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.



**onsemi**, **Onsemi**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at [www.onsemi.com/site/pdf/Patent-Marking.pdf](http://www.onsemi.com/site/pdf/Patent-Marking.pdf). **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

## ADDITIONAL INFORMATION

### TECHNICAL PUBLICATIONS:

Technical Library: [www.onsemi.com/design/resources/technical-documentation](http://www.onsemi.com/design/resources/technical-documentation)  
onsemi Website: [www.onsemi.com](http://www.onsemi.com)

### ONLINE SUPPORT: [www.onsemi.com/support](http://www.onsemi.com/support)

For additional information, please contact your local Sales Representative at  
[www.onsemi.com/support/sales](http://www.onsemi.com/support/sales)