



1610 Protector

Sensitive equipment needs protection, and since 1976 the answer has been the Pelican™ Protector Case. These cases are designed rugged, and travel the harshest environments on earth. Against the extreme cold of the arctic or the heat of battle, Pelican cases have survived. Made in the USA, these tough cases are designed with an automatic purge valve, that equalizes air pressure, a watertight silicone O-ring lid, over-molded rubber handles and stainless steel hardware.

- Personalized nameplate service available
- **Strong polyurethane wheels with stainless steel bearings**
- **Watertight, crushproof, and dustproof**
- 3 level Pick N Pluck™ with convoluted lid foam
- Automatic pressure equalization valve - balances interior pressure, keeps water out
- Easy open double-throw latches
- Fold down handles
- O-ring seal
- Open cell core with solid wall design - strong, light weight
- Retractable extension trolley handle
- Stainless steel hardware and padlock protectors



CONFIGURATIONS



1610
Standard



1614
With Padded Dividers



1610NF
No Foam



1610TP
With TrekPak Divider System



1610WF
With Foam

DIMENSIONS

Interior (L×W×D)	21.78 x 16.69" x 10.62 (55.3 x 42.4 x 27 cm)
Exterior (L×W×D)	24.83 x 19.69" x 11.88 (63.1 x 50 x 30.2 cm)
Lid Depth	2.05" (5.2 cm)
Bottom Depth	8.57" (21.8 cm)
Total Depth	10.62" (27 cm)
Int Volume	2.23 ft ³ (0.063 m ³)
Padlock Hole Diameter	0.31" (0.8 cm)

MATERIALS

Body	Polypropylene
Latch	ABS
O-Ring	Polymer
Pins	Stainless Steel
Foam	1.3 lb Polyurethane
Purge Body	ABS
Purge Vent	3 Micron Hydrophobic Non-Woven

COLORS

 Black	 Desert Tan
---	--

WEIGHT

Weight With Foam	22.30 lbs (10.1 kg)
Weight Empty	19.50 lbs (8.8 kg)
Buoyancy	119.93 lbs (54.4 kg)
Master Pack Weight	25.55 lbs (11.6 kg)

TEMPERATURE

Minimum Temperature	-40°F (-40 °C)
Maximum Temperature	190°F (87.8 °C)

CERTIFICATIONS

IP67
Def Stan 81-41

OTHER

Wheels	2
Extendable Handle	yes
Master Pack	1
Nameplate	yes
Military	yes

ACCESSORIES

				
1609 Lid Organizer	1611 5 pc. Replacement Foam Set	1612 Pick N Pluck™ Sections Only (set of 3)	1615 Padded Divider Set	1623 Replacement O-ring
				
1610TPKIT TrekPak Case Divider Kit	1610TPDIV Extra TrekPak Dividers	1507 Quick Mounts - set of 4	1506TSA TSA Lock	1500D Desiccant Silica Gel



1610MP
EZ-Click™ MOLLE Panel



1500CI
Corrosion Intercept Kit

Pelican

23215 Early Ave • Torrance, CA 90505 USA • Phone: (310) 326-4700 • (800) 473-5422 • Fax: (310) 326-3311
sales@pelican.com • www.pelican.com

Document created on 07-08-25