

Active

Not ELV or RoHS Compliant

- ? 2100 Miniature Timing Series
- ? Time Delay Relay
- ? Input Voltage = 120 VAC
- ? Contact Arrangement = 2 Form C, DPDT, 2 C/O
- ? Contact Rating = 10A @ 120 VAC

[View all Features](#)

[Check Pricing & Availability](#)

[Search for Tooling](#)

[Product Feature Selector](#)

[Contact Us About This Product](#)

2 None Available

? None Available

? None Available

? None Available

[2100 Series Miniature Timing Relays](#) (PDF, English)

? None Available

List all Documents

? Product Line Information

? Tooling

(Please use the Product Drawing for all design activity)

Product Type = Time Delay Relay
Termination Type = 8-Pin Octal
Style Plug

- ? Input Voltage (VAC) = 120
- ? Contact Rating = 10A @ 120 VAC

? **Series** = 2100 Miniature Timing

- Mounting Options = Chassis Mount, Socket
- Mode of Operation = On-Delay
- Delay Time = 2 seconds to 60 seconds
- Type of Control = Knob
- Repeatability, Max. = $\pm 5\%$ @ 25 °C, $\pm 7\%$ @ 85 °C, $\pm 8\%$ @ 55 °C
- Approved Standards = CE Approved
- Approx. Dimensions (L x W x H) (mm [in]) = 63.50 x 38.60 x 123.90 [2.501 x 1.520 x 4.881]

? Contact Arrangement = 2 Form C,
DPDT, 2 C/O

? Multiple Timing Ranges = Without

? RoHS/ELV Compliance = Not
ELV/RoHS compliant

? Lead Free Solder Processes = Not
suitable for lead free processing

? Temperature Range (°C) = -55 – +85

? Brand = Agastat